

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563156

Luminaire Tested: **SQ4-PC3-150U-125D-830-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563156  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3000K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 20660.1 lumens  
Efficiency: N/A  
Efficacy: 123.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 167.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563156  
CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563156

CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	65	65	65	51	51	51	45
1	97	92	89	85	88	85	82	79	71	68	66	58	56	55	46	45	44	38
2	88	81	75	70	80	74	69	65	62	58	55	51	48	46	40	38	37	32
3	80	71	64	58	73	65	59	54	55	50	46	45	41	38	36	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	29	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	24	20	17	20	17	15	12
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	15	13	11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15693	15693	15693
5°	15812	15710	15651
10°	15773	15699	15655
15°	15691	15691	15675
20°	15587	15634	15634
25°	15440	15552	15504
30°	15252	15436	15369
35°	15025	15255	15149
40°	14777	14985	14833
45°	14508	14611	14385
50°	14129	14129	13903
55°	13681	13503	13300
60°	13020	12758	12555
65°	12034	11793	11691
70°	10537	10622	10578
75°	8477	9375	9432
80°	6025	7948	8033
85°	3668	6669	6669



TEST NUMBER: P563156

CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	322.0	1.6
10°-20°	923.9	4.5
20°-30°	1399.2	6.8
30°-40°	1677.4	8.1
40°-50°	1710.4	8.3
50°-60°	1493.0	7.2
60°-70°	1068.9	5.2
70°-80°	550.5	2.7
80°-90°	142.9	0.7
90°-100°	819.7	4.0
100°-110°	2216.3	10.7
110°-120°	2330.1	11.3
120°-130°	1892.7	9.2
130°-140°	1484.7	7.2
140°-150°	1139.5	5.5
150°-160°	819.5	4.0
160°-170°	500.6	2.4
170°-180°	168.8	0.8
0°-30°	2645.0	12.8
0°-40°	4322.4	20.9
0°-60°	7525.8	36.4
0°-90°	9288.2	45.0
90°-120°	5366.2	26.0
90°-150°	9883.0	47.8
90°-180°	11372.0	55.0
0°-180°	20660.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3402	3402	3402	3402	3402	
5°	3414	3381	3392	3383	3380	324
15°	3285	3258	3285	3285	3282	926
25°	3033	3012	3055	3046	3046	1396
35°	2668	2662	2709	2690	2690	1669
45°	2224	2218	2240	2211	2205	1712
55°	1701	1679	1679	1654	1654	1516
65°	1102	1078	1080	1071	1071	1090
75°	476	497	526	529	529	514
85°	69	106	126	129	126	94
90°	4	11	25	26	25	11
95°	127	446	1363	706	420	133
105°	412	637	2459	3627	3478	434
115°	725	887	2039	3947	4456	716
125°	993	1138	1838	3101	3643	885
135°	1190	1332	1788	2504	2835	920
145°	1384	1488	1764	2143	2307	866
155°	1563	1624	1749	1923	1986	721
165°	1701	1718	1756	1825	1834	479
175°	1766	1764	1758	1781	1777	168
180°	1764	1764	1764	1764	1764	

TEST NUMBER: P563156

CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3401.9	3401.9	3401.9	3401.9	3401.9
2.5°	3422.1	3392.5	3401.9	3394.1	3381.7
5°	3414.5	3380.6	3392.5	3382.9	3379.9
7.5°	3389.9	3356.1	3371.7	3365.3	3362.2
10°	3367.3	3333.4	3351.5	3345.1	3342.1
12.5°	3337.0	3305.6	3326.3	3320.0	3319.4
15°	3285.4	3257.6	3285.4	3285.3	3282.2
17.5°	3220.5	3195.2	3224.9	3226.7	3224.9
20°	3175.1	3147.4	3184.6	3181.5	3184.6
22.5°	3119.7	3096.9	3136.7	3128.6	3131.6
25°	3033.4	3011.8	3055.4	3046.0	3046.0
27.5°	2931.3	2915.9	2963.4	2953.4	2953.4
30°	2863.3	2847.9	2897.9	2885.3	2885.3
32.5°	2787.7	2777.2	2824.8	2809.7	2809.7
35°	2668.0	2661.8	2708.9	2690.0	2690.0
37.5°	2544.5	2539.0	2581.7	2558.8	2551.4
40°	2453.8	2450.7	2488.4	2463.2	2463.2
42.5°	2363.1	2360.0	2392.7	2362.4	2362.4
45°	2223.8	2217.7	2239.6	2211.1	2204.9
47.5°	2072.0	2065.9	2079.6	2048.6	2045.6
50°	1968.7	1962.5	1968.7	1940.3	1937.2
52.5°	1862.9	1851.8	1852.8	1824.4	1823.8
55°	1701.0	1679.4	1678.9	1653.7	1653.7
57.5°	1529.6	1501.3	1503.8	1482.3	1479.2
60°	1411.2	1380.4	1382.8	1363.8	1360.8
62.5°	1295.2	1259.5	1266.9	1245.5	1244.8
65°	1102.5	1077.8	1080.4	1071.0	1071.0
67.5°	917.3	894.5	911.0	903.4	902.8
70°	781.2	765.8	787.5	787.4	784.3
72.5°	655.2	654.6	681.6	681.7	683.5
75°	475.6	497.2	526.0	529.2	529.2
77.5°	317.5	355.7	387.4	388.7	388.1
80°	226.8	269.9	299.2	305.5	302.4
82.5°	153.7	199.3	223.6	229.9	226.8
85°	69.3	106.3	126.0	129.1	126.0
87.5°	20.9	44.6	55.3	55.6	50.3
90°	3.8	11.2	24.7	26.5	24.7
92.5°	53.9	196.5	387.7	168.3	121.9
95°	127.2	446.5	1363.2	705.5	419.6
97.5°	204.3	512.1	2124.9	1758.5	1291.4
100°	262.0	538.6	2361.9	2463.2	1991.6
102.5°	315.2	575.4	2445.4	2997.5	2644.8
105°	412.0	636.6	2458.7	3626.8	3478.3
107.5°	501.6	706.6	2351.2	4019.3	4068.7
110°	571.5	757.1	2255.5	4124.7	4334.5



TEST NUMBER: P563156

CATALOG NUMBER: SQ4-PC3-150U-125D-830-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	633.8	807.5	2167.5	4103.7	4456.0
115°	725.3	886.8	2039.1	3947.4	4456.0
117.5°	814.9	966.4	1954.4	3708.6	4285.2
120°	869.6	1018.1	1904.3	3537.2	4125.7
122.5°	921.2	1066.7	1873.9	3353.5	3946.4
125°	993.0	1137.8	1837.9	3101.4	3643.4
127.5°	1059.0	1201.2	1816.6	2895.6	3372.3
130°	1095.5	1242.2	1807.5	2768.5	3199.2
132.5°	1133.5	1278.6	1798.4	2653.8	3050.3
135°	1190.4	1331.5	1788.5	2504.2	2834.6
137.5°	1247.8	1381.1	1780.1	2382.8	2652.0
140°	1287.3	1411.6	1777.1	2304.7	2544.1
142.5°	1325.2	1442.2	1771.0	2234.1	2443.9
145°	1384.1	1488.0	1763.8	2143.4	2306.8
147.5°	1437.6	1529.7	1755.5	2061.3	2186.8
150°	1477.1	1558.8	1752.4	2016.7	2116.9
152.5°	1513.6	1584.9	1750.9	1975.3	2057.7
155°	1562.6	1623.8	1748.6	1922.8	1985.9
157.5°	1613.4	1656.1	1749.0	1886.3	1927.8
160°	1642.3	1677.6	1750.5	1863.2	1892.9
162.5°	1665.1	1694.4	1752.0	1844.8	1867.1
165°	1701.2	1717.9	1756.2	1824.8	1834.1
167.5°	1725.8	1737.3	1756.6	1807.6	1812.0
170°	1741.0	1746.6	1758.1	1799.9	1799.9
172.5°	1753.2	1754.3	1758.1	1790.7	1789.2
175°	1765.7	1763.9	1758.1	1780.8	1777.1
177.5°	1769.9	1765.4	1757.7	1772.8	1768.4
180°	1763.8	1763.8	1763.8	1763.8	1763.8

(END OF REPORT)