

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563736

Luminaire Tested: **SQ4-PP3-125U-125D-835-1D-UNV-STD-W-8**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563736  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2103-172-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PRISM CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 19745.5 lumens  
Efficiency: N/A  
Efficacy: 129.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 8' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 152.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563736  
CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P563736

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	49				
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	49	48	47	42				
2	89	82	76	71	82	76	71	66	64	60	57	54	51	48	44	42	40	35				
3	81	72	65	59	75	67	60	55	57	52	48	47	44	41	39	36	34	30				
4	75	64	56	50	69	59	52	47	50	45	41	42	38	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	31	28	26	23				
6	63	51	43	37	58	48	40	35	41	35	31	34	30	27	28	25	23	20				
7	58	46	38	33	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17561	17561	17561
5°	17690	17582	17520
10°	17660	17535	17457
15°	17543	17448	17352
20°	17427	17329	17198
25°	17220	17101	16931
30°	16901	16812	16599
35°	16459	16346	16139
40°	15932	15832	15651
45°	15498	15389	15237
50°	14941	14845	14701
55°	14168	13980	13873
60°	12897	12528	12466
65°	11362	10889	10852
70°	9810	9405	9405
75°	8445	8325	8206
80°	7446	7534	7356
85°	5828	6357	6357



TEST NUMBER: P563736

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	360.0	1.8
10°-20°	1027.8	5.2
20°-30°	1539.5	7.8
30°-40°	1805.8	9.1
40°-50°	1811.5	9.2
50°-60°	1545.3	7.8
60°-70°	1007.8	5.1
70°-80°	505.6	2.6
80°-90°	143.6	0.7
90°-100°	724.6	3.7
100°-110°	1951.8	9.9
110°-120°	2048.3	10.4
120°-130°	1662.1	8.4
130°-140°	1303.6	6.6
140°-150°	1000.8	5.1
150°-160°	719.6	3.6
160°-170°	439.6	2.2
170°-180°	148.3	0.8
0°-30°	2927.3	14.8
0°-40°	4733.2	24.0
0°-60°	8089.9	41.0
0°-90°	9746.9	49.4
90°-120°	4724.6	23.9
90°-150°	8691.2	44.0
90°-180°	9999.0	50.6
0°-180°	19745.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3807	3807	3807	3807	3807	
5°	3820	3784	3797	3783	3783	363
15°	3673	3638	3653	3640	3633	1036
25°	3383	3344	3360	3330	3326	1556
35°	2923	2893	2903	2869	2866	1826
45°	2376	2359	2359	2336	2336	1829
55°	1762	1755	1738	1728	1725	1566
65°	1041	1021	998	991	994	1039
75°	474	474	467	464	460	514
85°	110	120	120	120	120	129
90°	4	12	24	26	26	12
95°	110	394	1188	607	420	115
105°	361	562	2158	3229	3031	380
115°	637	780	1797	3473	3928	627
125°	870	999	1614	2728	3210	777
135°	1048	1169	1569	2201	2492	809
145°	1211	1306	1549	1882	2020	760
155°	1375	1425	1535	1688	1742	633
165°	1492	1509	1541	1602	1610	421
175°	1551	1549	1543	1564	1561	147
180°	1549	1549	1549	1549	1549	

TEST NUMBER: P563736

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3806.8	3806.8	3806.8	3806.8	3806.8
2.5°	3830.8	3799.5	3806.8	3801.1	3785.4
5°	3820.1	3784.3	3796.8	3783.4	3783.4
7.5°	3794.1	3755.0	3767.4	3754.1	3753.4
10°	3770.1	3730.9	3743.4	3730.0	3726.7
12.5°	3735.4	3696.2	3711.4	3695.3	3694.7
15°	3673.3	3637.5	3653.3	3639.8	3633.3
17.5°	3603.3	3564.1	3583.3	3564.5	3561.9
20°	3549.9	3510.7	3529.9	3503.2	3503.2
22.5°	3485.8	3446.7	3468.5	3433.8	3433.8
25°	3383.1	3343.9	3359.7	3329.6	3326.4
27.5°	3261.0	3222.5	3238.9	3204.9	3204.2
30°	3172.9	3137.0	3156.2	3119.4	3116.2
32.5°	3076.8	3043.5	3057.4	3020.7	3017.4
35°	2922.7	2893.3	2902.6	2869.2	2865.9
37.5°	2760.5	2730.5	2741.2	2712.4	2711.1
40°	2645.7	2626.2	2629.1	2605.6	2599.0
42.5°	2539.0	2516.8	2519.6	2496.2	2494.9
45°	2375.5	2359.2	2358.8	2335.5	2335.5
47.5°	2202.0	2189.6	2186.0	2166.6	2166.0
50°	2081.9	2072.1	2068.5	2051.8	2048.5
52.5°	1956.4	1951.9	1940.4	1926.4	1925.8
55°	1761.6	1755.1	1738.2	1728.2	1724.9
57.5°	1550.1	1537.0	1518.0	1503.4	1506.0
60°	1397.9	1384.9	1357.9	1351.2	1351.2
62.5°	1251.1	1235.5	1208.4	1199.2	1204.4
65°	1040.9	1021.4	997.6	991.0	994.2
67.5°	850.1	832.5	806.7	806.7	804.1
70°	727.3	717.5	697.3	697.3	697.3
72.5°	617.9	613.3	598.5	598.5	595.9
75°	473.8	473.8	467.1	463.7	460.4
77.5°	355.0	356.3	353.0	349.5	343.6
80°	280.3	286.8	283.6	280.2	276.9
82.5°	210.9	217.4	216.9	210.8	210.2
85°	110.1	119.9	120.1	120.1	120.1
87.5°	30.1	42.1	47.4	47.9	50.5
90°	3.9	11.7	23.7	25.6	25.6
92.5°	48.1	170.1	336.2	161.9	112.5
95°	110.5	394.1	1187.8	607.4	420.3
97.5°	176.4	451.1	1862.9	1556.3	1173.6
100°	226.9	473.8	2077.6	2173.8	1803.4
102.5°	275.8	505.8	2148.6	2636.2	2332.1
105°	361.1	561.7	2158.5	3229.3	3030.6
107.5°	441.6	620.6	2066.6	3534.1	3585.4
110°	495.2	665.0	1982.9	3628.7	3815.9

TEST NUMBER: P563736

CATALOG NUMBER: SQ4-PP3-125U-125D-835-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	552.1	709.5	1902.4	3607.8	3915.3
115°	637.3	780.1	1797.4	3473.0	3928.3
117.5°	715.0	848.9	1716.2	3258.0	3765.0
120°	765.5	894.8	1675.1	3103.6	3624.5
122.5°	809.7	937.4	1645.1	2945.7	3465.1
125°	870.1	999.4	1613.9	2727.8	3210.1
127.5°	928.1	1055.4	1594.2	2535.7	2966.3
130°	962.8	1090.2	1586.3	2425.6	2803.7
132.5°	997.6	1123.4	1578.4	2328.6	2675.8
135°	1047.7	1169.2	1568.6	2200.6	2491.9
137.5°	1095.4	1212.0	1563.4	2092.1	2331.3
140°	1128.6	1240.5	1558.7	2025.3	2241.4
142.5°	1163.3	1267.5	1555.5	1963.0	2145.1
145°	1211.4	1306.0	1548.8	1881.5	2020.4
147.5°	1263.5	1345.7	1542.1	1812.9	1922.1
150°	1298.3	1369.6	1539.0	1769.9	1860.6
152.5°	1329.8	1391.9	1537.4	1734.8	1808.5
155°	1375.2	1425.4	1535.0	1688.2	1742.2
157.5°	1415.1	1454.0	1535.4	1655.4	1691.7
160°	1440.3	1473.1	1537.0	1636.3	1663.3
162.5°	1462.4	1489.0	1538.6	1620.3	1639.6
165°	1491.6	1509.0	1540.9	1602.3	1610.0
167.5°	1515.3	1525.3	1542.9	1588.4	1591.5
170°	1531.1	1534.9	1542.9	1580.4	1580.4
172.5°	1540.5	1541.3	1544.5	1572.5	1572.5
175°	1550.8	1548.9	1542.9	1564.5	1560.7
177.5°	1555.2	1552.1	1544.1	1556.7	1553.6
180°	1548.8	1548.8	1548.8	1548.8	1548.8

(END OF REPORT)