

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562581

Luminaire Tested: **SQ4-PC3-025U-125D-835-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562581  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-32, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3500K CCT, 80 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 17654.7 lumens  
Efficiency: N/A  
Efficacy: 113.0 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 156.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562581  
CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P562581

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	115	115	115	115	111	111	111	111	102	102	102	94	94	94	87	87	87	84				
1	105	101	97	93	101	97	93	90	90	87	84	83	81	79	77	75	74	71				
2	96	88	82	76	92	85	79	74	79	74	70	73	69	66	68	65	62	59				
3	88	78	70	64	84	75	68	62	70	64	59	65	60	56	60	56	53	50				
4	80	69	60	54	77	66	59	53	62	55	50	58	52	48	54	49	46	43				
5	74	61	53	46	71	59	51	45	55	49	43	52	46	42	48	44	40	37				
6	68	55	47	40	65	53	45	40	50	43	38	47	41	36	44	39	35	33				
7	63	50	42	36	60	48	41	35	45	39	34	43	37	32	40	35	31	29				
8	59	46	37	32	56	44	37	31	42	35	30	39	33	29	37	32	28	26				
9	55	42	34	28	53	41	33	28	38	32	27	36	30	26	34	29	25	23				
10	51	38	31	26	49	37	30	25	35	29	24	33	28	24	31	26	23	21				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16626	16626	16626
5°	16751	16643	16582
10°	16711	16633	16586
15°	16623	16623	16607
20°	16514	16563	16563
25°	16358	16477	16425
30°	16159	16354	16283
35°	15918	16162	16050
40°	15655	15876	15715
45°	15370	15479	15240
50°	14969	14969	14729
55°	14493	14306	14091
60°	13794	13516	13301
65°	12749	12495	12385
70°	11163	11252	11207
75°	8982	9934	9993
80°	6383	8421	8512
85°	3885	7064	7064



TEST NUMBER: P562581

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	511.6	2.9
10°-20°	1468.3	8.3
20°-30°	2223.5	12.6
30°-40°	2665.7	15.1
40°-50°	2718.1	15.4
50°-60°	2372.7	13.4
60°-70°	1698.6	9.6
70°-80°	874.9	5.0
80°-90°	223.6	1.3
90°-100°	217.9	1.2
100°-110°	572.8	3.2
110°-120°	594.0	3.4
120°-130°	476.5	2.7
130°-140°	373.8	2.1
140°-150°	286.9	1.6
150°-160°	206.7	1.2
160°-170°	126.4	0.7
170°-180°	42.7	0.2
0°-30°	4203.4	23.8
0°-40°	6869.0	38.9
0°-60°	11959.8	67.7
0°-90°	14756.9	83.6
90°-120°	1384.7	7.8
90°-150°	2521.9	14.3
90°-180°	2898.0	16.4
0°-180°	17654.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	5406	5406	5406	5406	5406	
5°	5426	5372	5391	5376	5371	515
15°	5221	5177	5221	5221	5216	1472
25°	4820	4786	4856	4840	4840	2218
35°	4240	4230	4305	4275	4275	2652
45°	3534	3524	3559	3514	3504	2720
55°	2703	2669	2668	2628	2628	2410
65°	1752	1713	1717	1702	1702	1733
75°	756	790	836	841	841	817
85°	110	169	200	205	200	150
90°	3	8	23	12	12	7
95°	29	113	375	194	132	32
105°	103	156	633	962	897	109
115°	183	223	507	1012	1155	181
125°	255	286	461	780	920	226
135°	304	335	447	630	714	235
145°	352	375	441	537	579	221
155°	398	410	441	485	499	183
165°	430	436	441	459	464	121
175°	447	447	444	450	450	42
180°	447	447	447	447	447	

TEST NUMBER: P562581

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	5406.2	5406.2	5406.2	5406.2	5406.2
2.5°	5438.2	5391.2	5406.2	5393.7	5374.2
5°	5426.2	5372.4	5391.2	5376.0	5371.2
7.5°	5387.2	5333.3	5358.1	5348.0	5343.1
10°	5351.1	5297.3	5326.1	5316.0	5311.1
12.5°	5303.1	5253.2	5286.1	5276.0	5275.0
15°	5221.0	5176.9	5221.0	5220.9	5216.0
17.5°	5117.9	5077.7	5124.9	5127.8	5124.9
20°	5045.8	5001.7	5060.8	5055.9	5060.8
22.5°	4957.7	4921.5	4984.7	4971.8	4976.7
25°	4820.5	4786.3	4855.6	4840.5	4840.5
27.5°	4658.3	4633.9	4709.4	4693.4	4693.4
30°	4550.2	4525.7	4605.3	4585.3	4585.3
32.5°	4430.1	4413.4	4489.1	4465.1	4465.1
35°	4239.9	4230.1	4304.9	4274.9	4274.9
37.5°	4043.6	4034.8	4102.7	4066.4	4054.6
40°	3899.5	3894.6	3954.5	3914.5	3914.5
42.5°	3755.3	3750.4	3802.4	3754.3	3754.3
45°	3534.0	3524.3	3559.1	3513.8	3504.0
47.5°	3292.8	3283.0	3304.8	3255.6	3250.7
50°	3128.6	3118.8	3128.6	3083.4	3078.5
52.5°	2960.4	2942.8	2944.4	2899.3	2898.3
55°	2703.1	2668.8	2668.1	2628.0	2628.0
57.5°	2430.8	2385.8	2389.7	2355.6	2350.7
60°	2242.6	2193.6	2197.5	2167.4	2162.5
62.5°	2058.4	2001.6	2013.3	1979.2	1978.3
65°	1752.0	1712.9	1717.0	1701.9	1701.9
67.5°	1457.7	1421.5	1447.7	1435.6	1434.6
70°	1241.4	1216.9	1251.4	1251.3	1246.4
72.5°	1041.2	1040.2	1083.2	1083.3	1086.2
75°	755.9	790.1	836.0	841.0	841.0
77.5°	504.6	565.3	615.7	617.7	616.7
80°	360.4	428.9	475.5	485.4	480.6
82.5°	244.3	316.7	355.4	365.3	360.4
85°	110.1	168.9	200.2	205.1	200.2
87.5°	32.6	69.0	84.7	82.2	74.4
90°	2.9	8.5	22.9	11.5	11.5
92.5°	12.0	58.0	128.4	56.9	36.7
95°	28.7	112.7	375.4	193.5	131.8
97.5°	49.9	123.8	561.7	446.7	329.0
100°	65.9	133.2	619.0	627.3	487.2
102.5°	79.7	142.4	635.1	781.4	661.4
105°	103.2	156.4	633.4	961.5	897.0
107.5°	127.2	176.6	597.2	1055.0	1070.7
110°	143.3	188.1	567.4	1079.1	1146.3

TEST NUMBER: P562581

CATALOG NUMBER: SQ4-PC3-025U-125D-835-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	159.3	201.9	539.9	1063.9	1167.0
115°	183.4	222.6	507.3	1012.0	1154.9
117.5°	206.9	242.8	484.9	940.2	1098.8
120°	220.7	254.3	475.7	891.9	1046.0
122.5°	234.4	268.1	468.9	843.7	995.6
125°	255.1	285.9	461.4	779.8	919.9
127.5°	271.7	303.1	455.1	728.3	846.6
130°	280.9	314.5	452.8	696.0	805.3
132.5°	290.0	323.7	450.5	668.3	766.3
135°	303.8	334.6	447.1	629.5	713.6
137.5°	318.1	348.4	446.5	600.5	669.5
140°	329.6	357.6	444.2	577.5	642.0
142.5°	338.7	364.5	444.2	561.3	616.7
145°	352.5	374.9	441.3	536.9	578.9
147.5°	366.3	388.1	441.3	516.6	551.4
150°	375.4	395.0	441.3	505.0	533.1
152.5°	384.6	399.7	441.3	495.7	517.0
155°	398.4	409.6	441.3	484.6	498.7
157.5°	408.7	419.3	441.3	474.8	484.9
160°	415.5	424.0	441.3	470.1	475.7
162.5°	422.4	428.6	441.3	465.5	471.1
165°	429.9	435.5	441.3	458.7	464.3
167.5°	436.8	439.6	444.2	455.7	458.0
170°	441.3	444.1	444.2	455.7	455.7
172.5°	443.6	444.2	444.2	453.3	451.1
175°	447.1	447.1	444.2	449.9	449.9
177.5°	447.1	447.1	444.8	449.3	447.1
180°	447.1	447.1	447.1	447.1	447.1

(END OF REPORT)