

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P562691

Luminaire Tested: **SQ4-PC3-050U-125D-935-1D-UNV-STD-W-6**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P562691  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-21, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-050U-125D-935-1D-UNV-STD-W-6  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 9007.7 lumens  
Efficiency: N/A  
Efficacy: 102.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 6' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 87.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P562691  
CATALOG NUMBER: SQ4-PC3-050U-125D-935-1D-UNV-STD-W-6

### Luminous Intensity Polar Plot





TEST NUMBER: P562691

CATALOG NUMBER: SQ4-PC3-050U-125D-935-1D-UNV-STD-W-6

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	71	
1	103	98	94	91	97	93	90	86	84	81	79	75	73	71	67	65	64	64	64	64	60	
2	93	86	79	74	88	81	76	71	73	69	65	66	62	59	59	56	54	54	54	54	50	
3	85	75	68	62	80	72	65	59	65	59	55	58	54	50	52	49	46	46	46	46	43	
4	78	67	59	52	74	64	56	50	58	51	47	52	47	43	47	43	40	40	40	40	37	
5	72	60	51	45	68	57	49	43	52	45	40	47	41	37	42	38	34	34	34	34	32	
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	34	30	30	30	30	28	
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	35	30	27	27	27	27	25	
8	57	44	36	30	54	42	35	30	39	32	28	35	30	26	32	27	24	24	24	24	22	
9	53	40	33	27	50	39	31	26	35	29	25	32	27	23	29	25	22	22	22	22	20	
10	50	37	30	25	47	36	29	24	33	27	22	30	25	21	27	23	20	20	20	20	18	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14446	14446	14446
5°	14555	14461	14408
10°	14520	14452	14411
15°	14443	14443	14430
20°	14348	14391	14391
25°	14213	14316	14272
30°	14040	14210	14148
35°	13831	14044	13945
40°	13602	13794	13655
45°	13356	13450	13242
50°	13006	13006	12798
55°	12594	12430	12243
60°	11985	11744	11557
65°	11079	10856	10761
70°	9699	9778	9738
75°	7804	8631	8684
80°	5547	7318	7396
85°	3373	6140	6140



TEST NUMBER: P562691

CATALOG NUMBER: SQ4-PC3-050U-125D-935-1D-UNV-STD-W-6

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	222.3	2.5
10°-20°	637.9	7.1
20°-30°	966.0	10.7
30°-40°	1158.1	12.9
40°-50°	1180.8	13.1
50°-60°	1030.8	11.4
60°-70°	738.0	8.2
70°-80°	380.1	4.2
80°-90°	97.6	1.1
90°-100°	190.9	2.1
100°-110°	518.5	5.8
110°-120°	533.1	5.9
120°-130°	426.2	4.7
130°-140°	334.9	3.7
140°-150°	256.8	2.9
150°-160°	184.7	2.1
160°-170°	112.9	1.3
170°-180°	38.1	0.4
0°-30°	1826.1	20.3
0°-40°	2984.2	33.1
0°-60°	5195.9	57.7
0°-90°	6411.6	71.2
90°-120°	1242.5	13.8
90°-150°	2260.4	25.1
90°-180°	2596.0	28.8
0°-180°	9007.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2349	2349	2349	2349	2349	
5°	2357	2334	2342	2336	2334	224
15°	2268	2249	2268	2268	2266	640
25°	2094	2079	2110	2103	2103	964
35°	1842	1838	1870	1857	1857	1152
45°	1535	1531	1546	1527	1522	1182
55°	1174	1160	1159	1142	1142	1047
65°	761	744	746	739	739	753
75°	328	343	363	365	365	355
85°	48	73	87	89	87	65
90°	1	5	9	12	12	4
95°	28	104	332	145	97	30
105°	92	143	570	868	817	98
115°	164	199	456	908	1034	161
125°	225	256	413	696	821	201
135°	271	301	402	567	639	210
145°	313	336	396	482	518	197
155°	354	367	394	432	445	163
165°	384	389	395	412	413	108
175°	398	399	396	401	400	38
180°	398	398	398	398	398	

TEST NUMBER: P562691

CATALOG NUMBER: SQ4-PC3-050U-125D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2348.7	2348.7	2348.7	2348.7	2348.7
2.5°	2362.6	2342.2	2348.7	2343.3	2334.8
5°	2357.4	2334.0	2342.2	2335.6	2333.5
7.5°	2340.4	2317.0	2327.8	2323.4	2321.3
10°	2324.8	2301.4	2313.9	2309.5	2307.4
12.5°	2303.9	2282.2	2296.5	2292.1	2291.7
15°	2268.2	2249.1	2268.2	2268.2	2266.1
17.5°	2223.4	2206.0	2226.5	2227.8	2226.5
20°	2192.1	2173.0	2198.6	2196.5	2198.6
22.5°	2153.8	2138.1	2165.6	2160.0	2162.1
25°	2094.3	2079.4	2109.5	2103.0	2103.0
27.5°	2023.8	2013.2	2046.0	2039.0	2039.0
30°	1976.8	1966.2	2000.7	1992.0	1992.0
32.5°	1924.6	1917.4	1950.3	1939.9	1939.9
35°	1842.0	1837.7	1870.3	1857.2	1857.2
37.5°	1756.7	1752.9	1782.4	1766.6	1761.5
40°	1694.1	1692.0	1718.0	1700.6	1700.6
42.5°	1631.5	1629.4	1651.9	1631.0	1631.0
45°	1535.4	1531.1	1546.2	1526.6	1522.3
47.5°	1430.5	1426.3	1435.8	1414.4	1412.3
50°	1359.2	1354.9	1359.2	1339.6	1337.5
52.5°	1286.1	1278.5	1279.2	1259.6	1259.2
55°	1174.4	1159.5	1159.1	1141.7	1141.7
57.5°	1056.0	1036.5	1038.2	1023.4	1021.3
60°	974.3	953.0	954.7	941.6	939.5
62.5°	894.2	869.6	874.7	859.9	859.5
65°	761.2	744.1	745.9	739.4	739.4
67.5°	633.3	617.5	628.9	623.7	623.3
70°	539.3	528.7	543.7	543.6	541.5
72.5°	452.3	451.9	470.6	470.6	471.9
75°	328.4	343.3	363.2	365.4	365.4
77.5°	219.2	245.6	267.5	268.4	267.9
80°	156.6	186.3	206.6	210.9	208.8
82.5°	106.1	137.6	154.4	158.7	156.6
85°	47.8	73.4	87.0	89.1	87.0
87.5°	14.2	30.2	36.6	37.0	33.6
90°	1.3	5.0	8.9	11.5	11.5
92.5°	11.5	52.3	90.8	39.0	33.0
95°	28.1	104.4	332.4	144.7	97.2
97.5°	46.5	115.3	509.6	396.5	278.5
100°	58.8	122.6	563.8	571.5	461.5
102.5°	71.1	129.8	578.1	706.9	609.8
105°	92.1	143.3	570.2	868.2	817.0
107.5°	113.8	159.0	537.2	951.5	965.8
110°	129.1	170.4	512.7	967.9	1029.2

TEST NUMBER: P562691

CATALOG NUMBER: SQ4-PC3-050U-125D-935-1D-UNV-STD-W-6

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	142.4	181.7	488.1	954.3	1046.6
115°	163.6	198.7	456.4	908.1	1034.3
117.5°	183.6	217.1	436.2	842.4	984.7
120°	196.9	229.4	427.0	798.4	939.7
122.5°	208.1	240.6	420.9	754.3	890.6
125°	225.0	256.3	413.0	695.8	820.8
127.5°	240.1	271.1	408.6	651.4	758.7
130°	249.3	279.3	406.6	623.5	719.8
132.5°	258.5	288.5	404.5	599.8	685.0
135°	271.0	301.0	401.5	566.7	639.3
137.5°	284.6	311.8	399.9	537.6	598.6
140°	292.8	319.0	398.9	519.0	574.0
142.5°	301.0	325.2	397.9	504.5	550.5
145°	313.2	335.7	396.3	481.5	517.8
147.5°	327.0	346.3	395.1	463.5	492.0
150°	336.2	352.5	395.1	453.1	475.6
152.5°	343.4	357.7	394.0	443.8	462.3
155°	354.1	366.6	393.8	432.4	444.9
157.5°	364.6	374.4	393.8	424.7	434.2
160°	370.8	379.5	393.8	419.5	427.0
162.5°	376.9	383.7	394.8	415.4	420.9
165°	383.6	388.6	395.1	411.7	413.0
167.5°	390.5	393.0	396.3	407.4	408.4
170°	392.5	395.0	396.3	405.3	405.3
172.5°	394.5	396.0	396.3	403.2	403.2
175°	397.6	398.9	396.3	401.4	400.2
177.5°	398.6	398.6	395.6	399.6	397.6
180°	397.6	397.6	397.6	397.6	397.6

(END OF REPORT)