

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: CORELITE

Report Number: P563073

Luminaire Tested: **SQ4-PC3-125U-125D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563073  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-24, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-125U-125D-935-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1250 LUMENS PER FOOT  
UPLIGHT 1250 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 25856.5 lumens  
Efficiency: N/A  
Efficacy: 110.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 233.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563073  
CATALOG NUMBER: SQ4-PC3-125U-125D-935-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563073

CATALOG NUMBER: SQ4-PC3-125U-125D-935-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	93	90	86	90	86	83	80	73	71	68	61	59	57	49	48	47	42
2	89	82	75	70	82	75	70	66	64	60	57	53	50	48	43	42	40	35
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	38	36	34	30
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29	25
5	68	56	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25	22
6	63	51	42	37	58	47	40	35	40	35	30	34	30	26	28	25	22	19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	26	22	20	17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15
9	50	38	30	25	46	35	28	24	30	25	21	26	22	19	22	18	16	14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	14446	14446	14446
5°	14555	14461	14408
10°	14520	14452	14411
15°	14444	14444	14430
20°	14348	14391	14391
25°	14213	14316	14272
30°	14040	14210	14148
35°	13831	14043	13945
40°	13602	13795	13655
45°	13355	13450	13242
50°	13006	13006	12798
55°	12593	12430	12244
60°	11985	11744	11557
65°	11078	10857	10761
70°	9700	9778	9738
75°	7804	8631	8682
80°	5547	7318	7394
85°	3377	6140	6140



TEST NUMBER: P563073

CATALOG NUMBER: SQ4-PC3-125U-125D-935-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	444.6	1.7
10°-20°	1275.8	4.9
20°-30°	1932.0	7.5
30°-40°	2316.2	9.0
40°-50°	2361.7	9.1
50°-60°	2061.6	8.0
60°-70°	1475.9	5.7
70°-80°	760.2	2.9
80°-90°	197.0	0.8
90°-100°	944.3	3.7
100°-110°	2543.8	9.8
110°-120°	2669.6	10.3
120°-130°	2166.3	8.4
130°-140°	1699.0	6.6
140°-150°	1304.4	5.0
150°-160°	937.9	3.6
160°-170°	573.0	2.2
170°-180°	193.2	0.7
0°-30°	3652.3	14.1
0°-40°	5968.5	23.1
0°-60°	10391.8	40.2
0°-90°	12824.9	49.6
90°-120°	6157.8	23.8
90°-150°	11327.5	43.8
90°-180°	13032.0	50.4
0°-180°	25856.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	4697	4697	4697	4697	4697	
5°	4715	4668	4684	4671	4667	448
15°	4536	4498	4536	4536	4532	1279
25°	4188	4159	4219	4206	4206	1928
35°	3684	3676	3740	3714	3714	2304
45°	3071	3062	3092	3053	3045	2364
55°	2349	2319	2318	2284	2284	2094
65°	1522	1488	1492	1479	1479	1506
75°	657	686	726	731	731	710
85°	96	147	174	178	174	130
90°	5	15	31	33	33	14
95°	144	514	1548	792	548	150
105°	471	732	2813	4209	3950	495
115°	831	1017	2343	4526	5120	817
125°	1134	1302	2104	3555	4184	1013
135°	1366	1524	2044	2868	3248	1054
145°	1579	1702	2019	2452	2633	990
155°	1792	1858	2001	2200	2271	825
165°	1944	1967	2008	2088	2098	548
175°	2021	2019	2011	2039	2034	192
180°	2019	2019	2019	2019	2019	

TEST NUMBER: P563073

CATALOG NUMBER: SQ4-PC3-125U-125D-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	4697.4	4697.4	4697.4	4697.4	4697.4
2.5°	4725.2	4684.4	4697.4	4686.6	4669.6
5°	4714.8	4668.0	4684.4	4671.2	4667.0
7.5°	4680.9	4634.1	4655.6	4646.9	4642.6
10°	4649.6	4602.8	4627.8	4619.0	4614.8
12.5°	4607.8	4564.4	4593.0	4584.3	4583.4
15°	4536.5	4498.2	4536.5	4536.4	4532.1
17.5°	4446.9	4412.0	4453.0	4455.5	4453.0
20°	4384.2	4346.0	4397.3	4393.0	4397.3
22.5°	4307.7	4276.2	4331.2	4320.0	4324.2
25°	4188.5	4158.7	4219.0	4205.9	4205.9
27.5°	4047.6	4026.3	4092.0	4078.0	4078.0
30°	3953.6	3932.4	4001.5	3984.1	3984.1
32.5°	3849.3	3834.8	3900.6	3879.7	3879.7
35°	3684.0	3675.5	3740.5	3714.4	3714.4
37.5°	3513.5	3505.8	3564.8	3533.3	3523.1
40°	3388.2	3384.0	3436.1	3401.3	3401.3
42.5°	3263.0	3258.7	3303.8	3262.1	3262.1
45°	3070.7	3062.2	3092.5	3053.1	3044.6
47.5°	2861.1	2852.6	2871.5	2828.8	2824.5
50°	2718.4	2709.9	2718.4	2679.2	2674.9
52.5°	2572.3	2557.0	2558.3	2519.2	2518.3
55°	2348.7	2318.9	2318.3	2283.5	2283.5
57.5°	2112.1	2073.0	2076.4	2046.8	2042.5
60°	1948.6	1906.0	1909.4	1883.2	1879.0
62.5°	1788.5	1739.2	1749.3	1719.8	1718.9
65°	1522.3	1488.3	1491.9	1478.8	1478.8
67.5°	1266.6	1235.1	1257.9	1247.4	1246.6
70°	1078.7	1057.4	1087.4	1087.3	1083.0
72.5°	904.7	903.8	941.2	941.3	943.8
75°	656.8	686.5	726.4	730.7	730.7
77.5°	438.4	491.2	535.0	536.7	535.9
80°	313.2	372.7	413.2	421.8	417.5
82.5°	212.3	275.2	308.8	317.4	313.2
85°	95.7	146.7	174.0	178.2	174.0
87.5°	28.9	61.5	75.8	76.1	69.3
90°	5.1	15.2	30.9	33.4	33.4
92.5°	62.7	221.7	438.2	210.9	146.6
95°	144.0	513.6	1548.1	791.6	547.7
97.5°	229.9	587.9	2428.0	2028.4	1529.6
100°	295.7	617.6	2707.8	2833.2	2350.4
102.5°	359.5	659.2	2800.4	3435.8	3039.6
105°	470.6	732.1	2813.3	4208.9	3949.9
107.5°	575.5	808.8	2693.4	4606.1	4673.0
110°	645.5	866.7	2584.4	4729.5	4973.4

TEST NUMBER: P563073

CATALOG NUMBER: SQ4-PC3-125U-125D-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	719.5	924.7	2479.5	4702.2	5103.0
115°	830.6	1016.7	2342.7	4526.5	5119.9
117.5°	931.9	1106.4	2236.7	4246.2	4907.0
120°	997.8	1166.2	2183.2	4045.0	4723.9
122.5°	1055.4	1221.8	2144.2	3839.3	4516.1
125°	1134.0	1302.5	2103.5	3555.3	4183.9
127.5°	1209.7	1375.6	2077.8	3304.8	3866.1
130°	1254.9	1420.9	2067.5	3161.3	3654.2
132.5°	1300.2	1464.1	2057.2	3034.9	3487.5
135°	1365.5	1523.9	2044.4	2868.2	3247.9
137.5°	1427.7	1579.6	2037.7	2726.7	3038.5
140°	1470.9	1616.8	2031.5	2639.7	2921.3
142.5°	1516.2	1652.0	2027.4	2558.4	2795.8
145°	1578.9	1702.1	2018.7	2452.2	2633.3
147.5°	1646.8	1753.9	2009.9	2362.9	2505.2
150°	1692.1	1785.1	2005.8	2306.8	2425.0
152.5°	1733.2	1814.2	2003.7	2261.0	2357.1
155°	1792.4	1857.7	2000.7	2200.3	2270.7
157.5°	1844.3	1895.1	2001.2	2157.6	2204.8
160°	1877.2	1920.0	2003.2	2132.6	2167.8
162.5°	1906.0	1940.7	2005.3	2111.8	2137.0
165°	1944.1	1966.7	2008.4	2088.3	2098.4
167.5°	1974.9	1988.0	2010.9	2070.2	2074.2
170°	1995.5	2000.5	2010.9	2059.8	2059.8
172.5°	2007.9	2008.9	2013.0	2049.5	2049.5
175°	2021.2	2018.7	2010.9	2039.1	2034.1
177.5°	2026.9	2022.9	2012.5	2028.9	2024.8
180°	2018.7	2018.7	2018.7	2018.7	2018.7

(END OF REPORT)