

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P563145

Luminaire Tested: **SQ4-PC3-150U-100D-935-1D-UNV-STD-W-12**

Issue Date: 7/30/2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P563145  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1910-536-25, G2-2106-289-1)  
Test Lab: INNOVATION CENTER  
Issue Date: 7/30/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH PERCEIVE PYRAMID CONTINUOUS LENS.  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1500 LUMENS PER FOOT  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 25753.7 lumens  
Efficiency: N/A  
Efficacy: 115.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 12' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 223.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P563145

CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P563145

CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	95	91	87	84	87	83	80	77	68	65	63	54	52	51	41	40	39	33
2	87	80	74	69	79	73	67	63	59	56	52	47	45	42	36	34	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	38	36	32	30	28	23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	31	28	26	24	20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21	17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18	15
7	56	44	36	31	51	41	34	29	34	28	25	27	23	20	21	18	16	13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	17	14	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12	10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11321	11321	11321
5°	11406	11332	11290
10°	11378	11325	11293
15°	11318	11318	11307
20°	11244	11277	11277
25°	11138	11219	11184
30°	11002	11135	11087
35°	10838	11004	10928
40°	10659	10810	10700
45°	10466	10540	10376
50°	10192	10192	10029
55°	9868	9740	9594
60°	9392	9203	9056
65°	8681	8507	8433
70°	7601	7662	7631
75°	6116	6763	6804
80°	4346	5735	5795
85°	2646	4810	4810



TEST NUMBER: P563145

CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	348.4	1.4
10°-20°	999.7	3.9
20°-30°	1513.9	5.9
30°-40°	1815.0	7.0
40°-50°	1850.7	7.2
50°-60°	1615.5	6.3
60°-70°	1156.6	4.5
70°-80°	595.7	2.3
80°-90°	155.7	0.6
90°-100°	1131.9	4.4
100°-110°	3060.3	11.9
110°-120°	3217.5	12.5
120°-130°	2613.5	10.1
130°-140°	2050.0	8.0
140°-150°	1573.4	6.1
150°-160°	1131.6	4.4
160°-170°	691.3	2.7
170°-180°	233.1	0.9
0°-30°	2862.0	11.1
0°-40°	4677.0	18.2
0°-60°	8143.2	31.6
0°-90°	10051.1	39.0
90°-120°	7409.7	28.8
90°-150°	13646.6	53.0
90°-180°	15703.0	61.0
0°-180°	25753.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3681	3681	3681	3681	3681	
5°	3695	3658	3671	3660	3657	351
15°	3555	3525	3555	3555	3551	1002
25°	3282	3259	3306	3296	3296	1511
35°	2887	2880	2931	2911	2911	1805
45°	2406	2400	2423	2392	2386	1852
55°	1840	1817	1817	1789	1789	1641
65°	1193	1166	1169	1159	1159	1180
75°	515	538	569	573	573	556
85°	75	115	136	140	136	102
90°	5	16	34	37	34	15
95°	176	616	1882	974	579	184
105°	569	879	3395	5008	4803	599
115°	1002	1224	2816	5451	6153	989
125°	1371	1571	2538	4282	5031	1222
135°	1644	1839	2470	3458	3914	1270
145°	1911	2055	2436	2960	3185	1196
155°	2158	2242	2414	2655	2742	995
165°	2349	2372	2425	2520	2532	662
175°	2438	2436	2428	2459	2454	231
180°	2436	2436	2436	2436	2436	

TEST NUMBER: P563145

CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3681.0	3681.0	3681.0	3681.0	3681.0
2.5°	3702.8	3670.8	3681.0	3672.5	3659.2
5°	3694.6	3657.9	3670.7	3660.4	3657.1
7.5°	3668.0	3631.4	3648.2	3641.4	3638.0
10°	3643.5	3606.8	3626.4	3619.5	3616.2
12.5°	3610.8	3576.8	3599.2	3592.3	3591.7
15°	3554.9	3524.9	3554.9	3554.8	3551.4
17.5°	3484.6	3457.3	3489.4	3491.4	3489.4
20°	3435.6	3405.6	3445.8	3442.5	3445.8
22.5°	3375.6	3350.9	3394.0	3385.2	3388.5
25°	3282.2	3258.9	3306.1	3295.8	3295.8
27.5°	3171.8	3155.1	3206.5	3195.6	3195.6
30°	3098.1	3081.5	3135.6	3122.0	3122.0
32.5°	3016.3	3005.0	3056.6	3040.2	3040.2
35°	2886.8	2880.2	2931.1	2910.7	2910.7
37.5°	2753.2	2747.2	2793.4	2768.7	2760.7
40°	2655.1	2651.7	2692.6	2665.3	2665.3
42.5°	2556.9	2553.6	2588.9	2556.2	2556.2
45°	2406.3	2399.6	2423.3	2392.5	2385.8
47.5°	2242.0	2235.3	2250.2	2216.7	2213.3
50°	2130.2	2123.5	2130.2	2099.4	2096.1
52.5°	2015.7	2003.7	2004.8	1974.1	1973.4
55°	1840.5	1817.2	1816.6	1789.4	1789.4
57.5°	1655.1	1624.4	1627.1	1603.9	1600.5
60°	1526.9	1493.6	1496.2	1475.7	1472.4
62.5°	1401.5	1362.8	1370.8	1347.6	1347.0
65°	1192.9	1166.2	1169.0	1158.8	1158.8
67.5°	992.5	967.8	985.7	977.5	976.8
70°	845.3	828.6	852.1	852.0	848.7
72.5°	708.9	708.3	737.6	737.6	739.6
75°	514.7	538.0	569.2	572.6	572.6
77.5°	343.6	384.9	419.2	420.6	419.9
80°	245.4	292.1	323.8	330.5	327.2
82.5°	166.3	215.6	242.0	248.7	245.4
85°	75.0	115.0	136.3	139.7	136.3
87.5°	22.9	48.9	61.3	61.7	55.9
90°	5.2	15.5	34.1	36.6	34.1
92.5°	74.5	271.3	535.3	232.4	168.3
95°	175.6	616.5	1882.3	974.1	579.4
97.5°	282.1	707.1	2934.1	2428.2	1783.2
100°	361.8	743.7	3261.3	3401.2	2750.1
102.5°	435.2	794.6	3376.7	4139.0	3651.9
105°	568.9	879.1	3395.0	5007.9	4802.8
107.5°	692.6	975.6	3246.6	5550.0	5618.1
110°	789.1	1045.4	3114.5	5695.5	5985.2



TEST NUMBER: P563145

CATALOG NUMBER: SQ4-PC3-150U-100D-935-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	875.1	1115.0	2992.8	5666.4	6153.0
115°	1001.5	1224.5	2815.6	5450.6	6153.0
117.5°	1125.2	1334.4	2698.7	5120.8	5917.0
120°	1200.7	1405.8	2629.5	4884.2	5696.8
122.5°	1272.0	1473.0	2587.5	4630.6	5449.3
125°	1371.1	1571.1	2537.7	4282.4	5030.9
127.5°	1462.3	1658.7	2508.4	3998.3	4656.5
130°	1512.7	1715.2	2495.8	3822.7	4417.4
132.5°	1565.1	1765.6	2483.2	3664.4	4211.9
135°	1643.8	1838.6	2469.6	3457.8	3914.1
137.5°	1722.9	1907.0	2458.0	3290.2	3661.9
140°	1777.5	1949.2	2453.8	3182.3	3513.0
142.5°	1829.9	1991.4	2445.5	3084.9	3374.6
145°	1911.2	2054.7	2435.5	2959.7	3185.3
147.5°	1985.1	2112.2	2424.0	2846.3	3019.6
150°	2039.6	2152.4	2419.8	2784.7	2923.1
152.5°	2090.0	2188.4	2417.7	2727.5	2841.3
155°	2157.6	2242.2	2414.5	2655.1	2742.2
157.5°	2227.9	2286.8	2415.0	2604.6	2662.0
160°	2267.7	2316.4	2417.1	2572.7	2613.8
162.5°	2299.2	2339.7	2419.2	2547.3	2578.1
165°	2349.0	2372.0	2425.0	2519.7	2532.5
167.5°	2383.1	2399.0	2425.5	2495.9	2502.1
170°	2404.0	2411.7	2427.6	2485.3	2485.3
172.5°	2420.8	2422.3	2427.6	2472.7	2470.6
175°	2438.1	2435.5	2427.6	2459.0	2453.8
177.5°	2443.9	2437.7	2427.1	2447.9	2441.8
180°	2435.5	2435.5	2435.5	2435.5	2435.5

(END OF REPORT)