

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521408

Luminaire Tested: SQ4-F-050U-075D-92765-1D-UNV-STD-W-4_4000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521408
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-37)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-F-050U-075D-92765-1D-UNV-STD-W-4_4000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE
DOWNLIGHT 750 LUMENS PER FOOT
UPLIGHT 500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5402.8 lumens
Efficiency: N/A
Efficacy: 113.3 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.25 / 1.38
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 47.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521408

CATALOG NUMBER: SQ4-F-050U-075D-92765-1D-UNV-STD-W-4_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P521408

CATALOG NUMBER: SQ4-F-050U-075D-92765-1D-UNV-STD-W-4_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59																			
1	100	95	91	88	93	89	85	82	77	75	72	66	65	63	57	55	54	49																			
2	91	83	77	71	84	78	72	67	67	63	60	58	55	52	50	47	45	41																			
3	83	73	65	59	77	68	61	56	59	54	50	51	47	44	44	41	38	34																			
4	75	64	56	50	70	60	53	47	53	47	42	46	41	37	39	36	33	29																			
5	69	57	49	43	64	54	46	41	47	41	36	41	36	32	35	31	28	25																			
6	64	51	43	37	59	48	41	35	42	36	32	37	32	28	32	28	25	22																			
7	59	46	38	32	55	44	36	31	38	32	28	33	29	25	29	25	22	20																			
8	55	42	34	29	51	40	32	27	35	29	25	31	26	22	26	23	20	17																			
9	51	38	31	25	47	36	29	24	32	26	22	28	23	20	24	21	18	16																			
10	48	35	28	23	44	33	26	22	29	24	20	26	21	18	23	19	16	14																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10316	10316	10316
5°	10393	10355	10299
10°	10418	10341	10293
15°	10310	10271	10222
20°	10288	10218	10208
25°	10200	10180	10066
30°	10133	10068	9992
35°	9989	9978	9852
40°	9898	9848	9787
45°	9779	9726	9619
50°	9647	9574	9442
55°	9468	9352	9222
60°	9245	9095	8925
65°	8938	8737	8582
70°	8379	8187	7993
75°	7550	7333	7222
80°	6169	6222	6115
85°	4425	5071	5071

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 9779 cd/sqm

TEST NUMBER: P521408

CATALOG NUMBER: SQ4-F-050U-075D-92765-1D-UNV-STD-W-4_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.9	2.0
10°-20°	303.0	5.6
20°-30°	458.4	8.5
30°-40°	551.4	10.2
40°-50°	572.5	10.6
50°-60°	518.6	9.6
60°-70°	394.5	7.3
70°-80°	219.2	4.1
80°-90°	56.5	1.0
90°-100°	163.0	3.0
100°-110°	463.9	8.6
110°-120°	444.5	8.2
120°-130°	351.8	6.5
130°-140°	282.4	5.2
140°-150°	221.1	4.1
150°-160°	161.8	3.0
160°-170°	100.2	1.9
170°-180°	34.0	0.6
0°-30°	867.4	16.1
0°-40°	1418.7	26.3
0°-60°	2509.8	46.5
0°-90°	3180.1	58.9
90°-120°	1071.5	19.8
90°-150°	1926.7	35.7
90°-180°	2223.0	41.1
0°-180°	5402.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1118	1118	1118	1118	1118	
5°	1122	1112	1118	1113	1112	107
15°	1079	1070	1075	1074	1070	305
25°	1002	993	1000	990	989	462
35°	887	883	886	876	875	556
45°	750	744	745	737	737	578
55°	589	588	581	576	573	525
65°	409	403	400	394	393	403
75°	212	209	206	204	203	224
85°	42	45	48	48	48	52
90°	0	0	0	0	0	2
95°	18	70	316	109	67	20
105°	72	109	473	835	794	76
115°	134	162	358	760	892	132
125°	189	210	342	568	679	169
135°	231	251	338	480	542	178
145°	273	287	341	415	452	170
155°	312	319	349	375	390	144
165°	344	346	353	361	366	97
175°	360	358	357	355	352	34
180°	358	358	358	358	358	

TEST NUMBER: P521408

CATALOG NUMBER: SQ4-F-050U-075D-92765-1D-UNV-STD-W-4_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1118.1	1118.1	1118.1	1118.1	1118.1
2.5°	1125.4	1115.9	1118.9	1116.4	1114.0
5°	1122.2	1112.2	1118.1	1113.0	1112.0
7.5°	1116.9	1105.1	1107.9	1106.9	1106.9
10°	1112.0	1097.0	1103.8	1098.7	1098.7
12.5°	1098.9	1086.4	1091.6	1089.0	1090.6
15°	1079.4	1070.4	1075.3	1074.2	1070.2
17.5°	1062.5	1051.7	1055.4	1053.5	1051.9
20°	1047.8	1037.9	1040.7	1035.7	1039.7
22.5°	1031.5	1021.6	1026.8	1018.5	1018.5
25°	1002.0	993.0	1000.0	989.8	988.8
27.5°	970.6	964.9	969.4	961.8	959.0
30°	951.1	942.1	945.0	939.8	937.9
32.5°	928.3	919.3	922.2	913.0	914.2
35°	886.9	883.0	885.9	875.7	874.7
37.5°	849.5	841.5	846.2	837.8	837.0
40°	821.8	813.8	817.7	812.6	812.6
42.5°	796.5	787.7	790.0	783.2	780.8
45°	749.5	744.5	745.4	737.2	737.2
47.5°	703.0	699.4	697.9	689.6	691.2
50°	672.1	666.1	667.0	657.8	657.8
52.5°	636.2	636.6	632.8	626.8	622.0
55°	588.6	587.6	581.4	576.3	573.3
57.5°	537.7	533.1	528.7	521.8	521.2
60°	501.0	498.0	492.9	486.7	483.7
62.5°	463.5	460.5	455.4	450.1	449.5
65°	409.4	403.4	400.2	394.1	393.1
67.5°	350.5	345.7	341.7	336.8	336.2
70°	310.6	306.6	303.5	299.3	296.3
72.5°	273.9	267.5	264.3	261.0	258.9
75°	211.8	208.8	205.7	203.6	202.6
77.5°	151.9	152.1	152.1	149.5	148.5
80°	116.1	117.1	117.1	116.1	115.1
82.5°	84.3	86.1	87.0	85.9	85.7
85°	41.8	44.7	47.9	47.9	47.9
87.5°	11.4	15.4	18.7	19.5	18.7
90°	0.0	0.0	0.0	0.0	0.0
92.5°	5.4	28.9	66.9	19.5	14.7
95°	17.7	70.2	315.6	109.3	67.3
97.5°	32.5	82.3	486.1	347.8	238.4
100°	42.9	89.4	523.1	529.9	408.2
102.5°	54.3	97.1	515.0	678.3	572.0
105°	72.1	109.4	472.8	835.1	793.9
107.5°	90.2	123.6	423.5	879.3	916.0
110°	102.7	134.0	395.2	862.4	944.9

TEST NUMBER: P521408

CATALOG NUMBER: SQ4-F-050U-075D-92765-1D-UNV-STD-W-4_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	114.7	144.4	376.2	822.4	940.0
115°	134.0	161.9	358.5	759.5	891.8
117.5°	151.0	177.2	348.0	690.7	830.9
120°	164.6	186.6	346.9	651.3	785.7
122.5°	175.5	197.5	344.2	616.8	741.6
125°	189.1	209.7	342.2	567.8	678.9
127.5°	203.9	223.2	341.1	538.5	630.1
130°	211.6	230.9	339.5	518.1	598.0
132.5°	219.7	238.5	339.5	502.2	575.6
135°	231.3	250.6	338.1	479.6	542.2
137.5°	242.2	260.9	338.0	460.5	514.6
140°	250.3	269.6	337.4	444.7	496.6
142.5°	259.6	275.7	339.0	432.1	478.6
145°	272.8	286.8	340.8	415.1	452.4
147.5°	284.1	297.6	343.8	398.0	430.2
150°	293.9	303.2	344.9	392.3	415.0
152.5°	301.5	311.3	346.0	384.7	405.7
155°	311.6	318.9	349.0	375.2	390.5
157.5°	324.1	328.5	349.7	370.9	381.8
160°	330.6	333.9	352.4	367.6	376.9
162.5°	334.4	338.3	352.9	364.8	372.0
165°	344.2	345.5	353.1	360.7	366.0
167.5°	350.9	349.7	356.2	359.6	361.8
170°	353.1	352.4	355.1	355.8	358.5
172.5°	358.0	355.7	356.7	354.7	356.9
175°	360.5	358.5	357.1	355.0	352.4
177.5°	361.6	358.4	356.7	354.6	355.1
180°	357.8	357.8	357.8	357.8	357.8

(END OF REPORT)