

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521578

Luminaire Tested: SQ4-F-100U-100D-92765-1D-UNV-STD-W-4\_4500K

Issue Date: 5-5-2021

**Test Information**

Test Method: LM-79-2019  
Report Number: P521578  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2101-105-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 5-5-2021  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-F-100U-100D-92765-1D-UNV-STD-W-4\_4500K  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE  
DOWNLIGHT 1000 LUMENS PER FOOT  
UPLIGHT 1000 LUMENS PER FOOT  
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 4500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8772.1 lumens  
Efficiency: N/A  
Efficacy: 117.4 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.25 / 1.38  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 74.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P521578

CATALOG NUMBER: SQ4-F-100U-100D-92765-1D-UNV-STD-W-4\_4500K

### Luminous Intensity Polar Plot



TEST NUMBER: P521578

CATALOG NUMBER: SQ4-F-100U-100D-92765-1D-UNV-STD-W-4\_4500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				48
1	97	93	89	85	89	86	82	79	72	70	67	60	58	56	48	47	46	41				41
2	88	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38	34				34
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	35	32	28				28
4	74	63	55	49	67	58	51	46	49	44	39	41	37	34	33	30	28	24				24
5	67	56	48	42	62	52	44	39	44	38	34	37	32	29	30	27	24	21				21
6	62	50	42	36	57	46	39	34	39	34	29	33	29	25	27	24	21	18				18
7	57	45	37	31	53	42	35	30	36	30	26	30	26	22	25	21	19	16				16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14				14
9	49	37	30	25	45	35	28	23	30	24	20	25	21	18	21	17	15	13				13
10	46	34	27	22	43	32	25	21	27	22	18	23	19	16	19	16	14	12				12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13747	13747	13747
5°	13857	13771	13733
10°	13843	13746	13707
15°	13777	13698	13668
20°	13715	13654	13573
25°	13610	13557	13409
30°	13493	13460	13295
35°	13356	13308	13169
40°	13222	13172	13010
45°	13069	12960	12812
50°	12846	12757	12609
55°	12666	12482	12333
60°	12372	12123	11952
65°	11972	11634	11453
70°	11276	10914	10717
75°	10181	9921	9774
80°	8411	8411	8299
85°	5918	6796	7008

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 13069 cd/sqm

TEST NUMBER: P521578

CATALOG NUMBER: SQ4-F-100U-100D-92765-1D-UNV-STD-W-4\_4500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.1	1.6
10°-20°	404.1	4.6
20°-30°	611.1	7.0
30°-40°	735.8	8.4
40°-50°	764.2	8.7
50°-60°	692.7	7.9
60°-70°	527.6	6.0
70°-80°	294.8	3.4
80°-90°	76.5	0.9
90°-100°	331.9	3.8
100°-110°	944.4	10.8
110°-120°	904.8	10.3
120°-130°	716.1	8.2
130°-140°	574.8	6.6
140°-150°	450.0	5.1
150°-160°	329.3	3.8
160°-170°	203.9	2.3
170°-180°	69.2	0.8
0°-30°	1156.2	13.2
0°-40°	1892.1	21.6
0°-60°	3349.0	38.2
0°-90°	4247.8	48.4
90°-120°	2181.1	24.9
90°-150°	3921.9	44.7
90°-180°	4524.0	51.6
0°-180°	8772.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1490	1490	1490	1490	1490	
5°	1496	1482	1487	1483	1483	142
15°	1442	1429	1434	1431	1431	407
25°	1337	1326	1332	1321	1317	616
35°	1186	1179	1182	1170	1169	742
45°	1002	996	993	983	982	772
55°	787	784	776	767	767	702
65°	548	542	533	526	525	541
75°	286	282	278	274	274	302
85°	56	60	64	65	66	70
90°	0	0	0	0	0	4
95°	36	143	642	222	137	41
105°	147	223	962	1700	1616	155
115°	273	330	730	1546	1815	269
125°	385	427	696	1156	1382	345
135°	471	510	688	976	1104	363
145°	555	584	694	845	921	347
155°	634	649	710	764	795	293
165°	701	703	719	734	745	197
175°	734	730	727	723	717	70
180°	728	728	728	728	728	

TEST NUMBER: P521578

CATALOG NUMBER: SQ4-F-100U-100D-92765-1D-UNV-STD-W-4\_4500K

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1490.0	1490.0	1490.0	1490.0	1490.0
2.5°	1499.1	1487.0	1490.8	1488.2	1483.4
5°	1496.2	1482.0	1486.9	1482.8	1482.8
7.5°	1485.9	1472.3	1475.5	1473.0	1473.0
10°	1477.6	1462.4	1467.2	1463.1	1463.1
12.5°	1464.3	1450.8	1455.6	1451.5	1450.7
15°	1442.4	1429.2	1434.1	1431.0	1431.0
17.5°	1415.9	1403.4	1409.7	1404.7	1403.1
20°	1396.9	1382.7	1390.7	1382.4	1382.4
22.5°	1373.7	1361.1	1368.3	1358.3	1356.7
25°	1336.9	1325.7	1331.7	1321.2	1317.2
27.5°	1295.5	1283.5	1292.4	1280.7	1278.5
30°	1266.5	1255.4	1263.4	1250.9	1247.9
32.5°	1235.0	1225.5	1231.1	1219.5	1217.2
35°	1185.8	1178.7	1181.6	1170.2	1169.2
37.5°	1133.4	1126.6	1129.3	1116.7	1115.8
40°	1097.8	1091.8	1093.7	1080.2	1080.2
42.5°	1061.4	1054.5	1054.8	1042.2	1041.3
45°	1001.6	995.5	993.3	983.0	981.9
47.5°	938.1	935.2	931.9	921.5	921.5
50°	895.0	893.0	888.8	878.5	878.5
52.5°	851.2	849.9	844.1	835.4	833.8
55°	787.4	784.4	776.0	766.7	766.7
57.5°	717.7	715.3	705.9	698.4	696.6
60°	670.5	666.5	657.0	648.7	647.7
62.5°	621.7	618.4	608.2	600.7	598.9
65°	548.4	542.3	532.9	525.6	524.6
67.5°	471.0	464.1	455.9	449.9	447.8
70°	418.0	412.0	404.6	399.4	397.3
72.5°	365.9	359.8	353.3	349.7	349.3
75°	285.6	281.5	278.3	274.2	274.2
77.5°	207.2	204.7	203.0	200.9	200.9
80°	158.3	158.3	158.3	156.2	156.2
82.5°	113.6	116.0	117.8	116.5	116.5
85°	55.9	59.9	64.2	65.2	66.2
87.5°	15.7	20.6	25.7	26.5	27.3
90°	0.0	0.0	0.0	0.0	0.0
92.5°	11.1	58.7	136.3	39.7	29.9
95°	36.0	143.0	642.5	222.4	137.1
97.5°	66.2	167.5	989.5	708.1	485.2
100°	87.2	182.0	1064.8	1078.6	830.8
102.5°	110.5	197.7	1048.2	1380.6	1164.3
105°	146.8	222.6	962.4	1699.9	1616.0
107.5°	183.6	251.6	862.1	1789.9	1864.7
110°	209.1	272.7	804.5	1755.5	1923.4

TEST NUMBER: P521578

CATALOG NUMBER: SQ4-F-100U-100D-92765-1D-UNV-STD-W-4\_4500K

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	233.5	293.8	765.7	1674.0	1913.4
115°	272.8	329.7	729.7	1545.9	1815.4
117.5°	307.4	360.8	708.4	1405.9	1691.3
120°	335.1	379.8	706.2	1325.8	1599.3
122.5°	357.3	401.9	700.7	1255.6	1509.6
125°	385.0	426.9	696.5	1155.8	1381.9
127.5°	415.1	454.4	694.3	1096.2	1282.5
130°	430.6	469.9	691.0	1054.7	1217.2
132.5°	447.3	485.4	691.0	1022.3	1171.7
135°	470.8	510.1	688.2	976.3	1103.6
137.5°	493.0	531.1	687.9	937.5	1047.4
140°	509.6	548.8	686.8	905.2	1010.8
142.5°	528.4	561.2	690.1	879.5	974.3
145°	555.3	583.7	693.7	845.0	920.8
147.5°	578.3	605.9	699.8	810.2	875.7
150°	598.2	617.2	702.0	798.6	844.7
152.5°	613.7	633.7	704.3	783.1	825.8
155°	634.2	649.1	710.4	763.7	794.8
157.5°	659.7	668.6	711.7	754.9	777.1
160°	673.0	679.7	717.3	748.2	767.1
162.5°	680.7	688.6	718.4	742.5	757.2
165°	700.7	703.4	718.7	734.1	745.0
167.5°	714.2	711.8	725.0	732.1	736.4
170°	718.7	717.3	722.8	724.3	729.7
172.5°	728.6	724.0	726.1	722.1	726.4
175°	733.9	729.8	727.0	722.7	717.3
177.5°	736.1	729.6	726.1	721.7	722.8
180°	728.4	728.4	728.4	728.4	728.4

(END OF REPORT)