

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P521848

Luminaire Tested: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4_3000K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P521848
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4_3000K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7433.7 lumens
Efficiency: N/A
Efficacy: 93.6 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 79.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P521848

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P521848

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63	57																				
1	101	97	93	90	94	90	87	85	78	76	74	67	66	65	57	56	55	51																				
2	93	86	81	76	86	81	76	72	70	67	64	61	58	56	52	50	49	45																				
3	86	77	70	65	80	72	66	62	63	59	55	55	52	49	47	45	43	39																				
4	79	69	62	56	74	65	59	54	57	52	48	50	46	43	43	41	38	35																				
5	73	62	55	49	68	59	52	47	52	47	43	46	42	39	40	37	34	32																				
6	68	57	49	44	63	54	47	42	48	42	38	42	38	35	37	34	31	28																				
7	63	52	44	39	59	49	42	37	44	38	34	39	34	31	34	31	28	26																				
8	59	47	40	35	55	45	38	34	40	35	31	36	32	28	32	28	26	24																				
9	55	44	37	32	52	41	35	31	37	32	28	33	29	26	29	26	24	22																				
10	52	40	34	29	49	38	32	28	35	29	26	31	27	24	28	24	22	20																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26864	26864	26864
5°	26528	26434	26588
10°	25065	25291	25878
15°	23138	23675	24737
20°	21011	21802	23244
25°	18846	19873	21656
30°	16851	17953	20008
35°	14736	15800	18059
40°	12403	13387	15634
45°	10236	11119	13053
50°	8546	9315	10874
55°	7255	7994	8980
60°	6200	6931	7167
65°	4936	5829	4630
70°	4378	4548	2827
75°	4053	3689	1729
80°	3735	3395	1493
85°	3377	3112	1217

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13053 cd/sqm

TEST NUMBER: P521848

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.1	3.6
10°-20°	694.7	9.3
20°-30°	899.8	12.1
30°-40°	881.1	11.9
40°-50°	674.5	9.1
50°-60°	449.4	6.0
60°-70°	245.2	3.3
70°-80°	102.2	1.4
80°-90°	28.9	0.4
90°-100°	234.1	3.1
100°-110°	666.0	9.0
110°-120°	638.1	8.6
120°-130°	505.0	6.8
130°-140°	405.4	5.5
140°-150°	317.4	4.3
150°-160°	232.2	3.1
160°-170°	143.8	1.9
170°-180°	48.8	0.7
0°-30°	1861.5	25.0
0°-40°	2742.7	36.9
0°-60°	3866.5	52.0
0°-90°	4242.9	57.1
90°-120°	1538.2	20.7
90°-150°	2766.0	37.2
90°-180°	3191.0	42.9
0°-180°	7433.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2912	2912	2912	2912	2912	
5°	2864	2836	2854	2861	2871	266
15°	2422	2414	2479	2546	2590	676
25°	1851	1856	1952	2037	2127	851
35°	1308	1314	1403	1497	1603	813
45°	784	800	852	917	1000	612
55°	451	470	497	516	558	409
65°	226	245	267	233	212	235
75°	114	114	104	71	48	121
85°	32	32	29	19	12	35
90°	0	0	0	0	0	3
95°	25	101	453	157	97	29
105°	104	157	679	1199	1140	110
115°	192	232	515	1090	1280	189
125°	272	301	491	815	975	243
135°	332	360	485	689	778	256
145°	392	412	489	596	649	245
155°	447	458	501	539	560	207
165°	494	496	507	518	525	139
175°	518	515	513	510	506	49
180°	514	514	514	514	514	

TEST NUMBER: P521848

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2911.7	2911.7	2911.7	2911.7	2911.7
2.5°	2918.9	2892.9	2899.4	2899.3	2891.3
5°	2864.4	2835.7	2854.2	2860.8	2870.8
7.5°	2758.1	2736.4	2770.2	2795.1	2815.4
10°	2675.4	2656.6	2699.6	2736.0	2762.2
12.5°	2579.3	2563.5	2616.8	2665.7	2699.9
15°	2422.4	2413.6	2478.6	2546.0	2589.8
17.5°	2254.5	2250.3	2324.8	2403.5	2459.4
20°	2140.0	2138.8	2220.5	2302.5	2367.4
22.5°	2024.5	2027.3	2113.2	2198.4	2272.4
25°	1851.3	1856.3	1952.2	2037.3	2127.3
27.5°	1691.1	1693.3	1792.5	1882.3	1978.3
30°	1581.7	1587.9	1685.2	1778.2	1878.1
32.5°	1472.3	1479.6	1574.8	1670.9	1772.8
35°	1308.3	1314.5	1402.8	1497.2	1603.4
37.5°	1139.1	1147.6	1226.0	1315.3	1419.7
40°	1029.8	1042.3	1111.5	1195.6	1298.1
42.5°	924.5	940.0	1004.2	1084.0	1176.4
45°	784.5	799.5	852.2	916.7	1000.4
47.5°	663.9	681.1	721.6	777.1	848.6
50°	595.4	611.6	649.0	690.2	757.6
52.5°	535.1	551.3	584.6	616.4	673.8
55°	451.0	469.7	497.0	515.8	558.3
57.5°	382.0	400.0	421.6	430.1	455.9
60°	336.0	356.0	375.6	374.7	388.4
62.5°	294.1	311.1	330.7	317.1	317.9
65°	226.1	244.9	267.0	233.3	212.1
67.5°	182.7	186.7	209.5	162.7	137.5
70°	162.3	162.3	168.6	126.0	104.8
72.5°	142.8	142.8	137.0	102.5	80.2
75°	113.7	113.7	103.5	71.0	48.5
77.5°	87.6	86.6	79.2	53.0	35.3
80°	70.3	70.3	63.9	41.8	28.1
82.5°	54.9	54.9	49.6	32.7	21.0
85°	31.9	31.9	29.4	19.0	11.5
87.5°	11.2	11.2	10.2	6.1	5.1
90°	0.0	0.0	0.0	0.0	0.0
92.5°	7.8	41.4	96.1	28.0	21.1
95°	25.4	100.8	453.1	156.8	96.7
97.5°	46.7	118.1	697.9	499.4	342.2
100°	61.5	128.4	751.0	760.7	585.9
102.5°	77.9	139.4	739.3	973.7	821.1
105°	103.5	157.0	678.7	1198.9	1139.7
107.5°	129.5	177.4	608.0	1262.3	1315.0
110°	147.5	192.3	567.4	1238.0	1356.5

TEST NUMBER: P521848

CATALOG NUMBER: SQ4-WB-075U-125D-92765-1D-UNV-STD-W-4_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	164.6	207.2	540.0	1180.6	1349.4
115°	192.4	232.5	514.7	1090.3	1280.3
117.5°	216.8	254.4	499.6	991.5	1192.8
120°	236.3	267.8	498.0	935.1	1127.9
122.5°	252.0	283.5	494.1	885.5	1064.7
125°	271.5	301.1	491.2	815.2	974.6
127.5°	292.8	320.5	489.7	773.1	904.5
130°	303.7	331.4	487.3	743.8	858.4
132.5°	315.4	342.4	487.3	721.0	826.4
135°	332.0	359.7	485.4	688.6	778.3
137.5°	347.7	374.6	485.2	661.1	738.7
140°	359.4	387.1	484.4	638.4	712.9
142.5°	372.7	395.8	486.7	620.3	687.1
145°	391.6	411.7	489.3	595.9	649.4
147.5°	407.8	427.3	493.6	571.4	617.6
150°	421.9	435.2	495.1	563.2	595.7
152.5°	432.8	446.9	496.7	552.3	582.4
155°	447.3	457.8	501.0	538.6	560.5
157.5°	465.2	471.5	502.0	532.4	548.0
160°	474.6	479.4	505.9	527.6	541.0
162.5°	480.1	485.6	506.6	523.7	534.0
165°	494.1	496.1	506.8	517.8	525.4
167.5°	503.7	502.0	511.3	516.3	519.3
170°	506.8	505.9	509.8	510.8	514.7
172.5°	513.9	510.6	512.1	509.3	512.3
175°	517.6	514.7	512.7	509.7	505.9
177.5°	519.1	514.6	512.1	509.0	509.8
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)