

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P522061

Luminaire Tested: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5700K

Issue Date: 5-5-2021

Test Information

Test Method: LM-79-2019
Report Number: P522061
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2101-105-51, G2-2009-966-13)
Test Lab: INNOVATION CENTER
Issue Date: 5-5-2021
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5700K
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH WHITE BAFFLE
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 1500 LUMENS PER FOOT
Light Source: 2700K-6500K CCT, 90 CRI LEDS, TUNED TO 5700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11632.7 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 106.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P522061

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5700K

Luminous Intensity Polar Plot



TEST NUMBER: P522061

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	40																				
1	96	92	89	86	88	84	81	79	69	67	65	55	54	53	43	42	41	35																				
2	88	82	76	72	80	75	70	66	62	58	56	50	48	46	39	37	36	31																				
3	81	73	66	61	74	67	61	56	55	51	48	45	42	40	35	33	32	27																				
4	75	65	58	52	68	60	53	49	50	45	42	41	37	35	32	30	28	24																				
5	69	58	51	45	63	54	47	42	45	40	37	37	34	31	29	27	25	22																				
6	64	53	45	40	58	49	42	37	41	36	32	34	30	28	27	25	23	20																				
7	59	48	40	35	54	44	38	33	37	32	29	31	27	25	25	23	21	18																				
8	55	44	36	32	50	40	34	30	34	29	26	29	25	22	23	21	19	16																				
9	52	40	33	28	47	37	31	27	32	27	24	26	23	20	22	19	17	15																				
10	48	37	30	26	44	34	28	24	29	25	21	25	21	19	20	18	16	14																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	29189	29189	29189
5°	28824	28722	28888
10°	27233	27480	28118
15°	25140	25724	26876
20°	22830	23689	25256
25°	20477	21593	23529
30°	18309	19507	21740
35°	16011	17167	19623
40°	13476	14545	16987
45°	11121	12081	14182
50°	9285	10122	11816
55°	7882	8686	9757
60°	6737	7530	7787
65°	5364	6333	5030
70°	4756	4942	3070
75°	4402	4007	1882
80°	4059	3687	1621
85°	3673	3377	1323

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 14182 cd/sqm

TEST NUMBER: P522061

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.2	2.5
10°-20°	754.8	6.5
20°-30°	977.7	8.4
30°-40°	957.4	8.2
40°-50°	732.8	6.3
50°-60°	488.3	4.2
60°-70°	266.5	2.3
70°-80°	111.0	1.0
80°-90°	31.4	0.3
90°-100°	515.2	4.4
100°-110°	1465.8	12.6
110°-120°	1404.4	12.1
120°-130°	1111.5	9.6
130°-140°	892.2	7.7
140°-150°	698.5	6.0
150°-160°	511.1	4.4
160°-170°	316.6	2.7
170°-180°	107.4	0.9
0°-30°	2022.6	17.4
0°-40°	2980.0	25.6
0°-60°	4201.1	36.1
0°-90°	4610.0	39.6
90°-120°	3385.4	29.1
90°-150°	6087.6	52.3
90°-180°	7023.0	60.4
0°-180°	11632.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3164	3164	3164	3164	3164	
5°	3112	3081	3101	3108	3119	290
15°	2632	2622	2693	2766	2814	735
25°	2012	2017	2121	2214	2311	925
35°	1422	1428	1524	1627	1742	884
45°	852	869	926	996	1087	665
55°	490	510	540	560	607	444
65°	246	266	290	254	230	255
75°	124	124	112	77	53	132
85°	35	35	32	21	12	38
90°	0	0	0	0	0	4
95°	56	222	997	345	213	64
105°	228	346	1494	2639	2508	241
115°	423	512	1133	2400	2818	417
125°	598	663	1081	1794	2145	535
135°	731	792	1068	1516	1713	564
145°	862	906	1077	1312	1429	538
155°	984	1008	1103	1185	1234	455
165°	1088	1092	1116	1140	1156	306
175°	1139	1133	1128	1122	1113	108
180°	1131	1131	1131	1131	1131	

TEST NUMBER: P522061

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3163.7	3163.7	3163.7	3163.7	3163.7
2.5°	3171.4	3143.2	3150.3	3150.1	3141.5
5°	3112.3	3081.1	3101.2	3108.4	3119.2
7.5°	2996.8	2973.2	3009.9	3037.0	3059.0
10°	2906.9	2886.5	2933.2	2972.7	3001.3
12.5°	2802.5	2785.4	2843.3	2896.3	2933.5
15°	2632.0	2622.5	2693.1	2766.3	2813.8
17.5°	2449.6	2445.0	2525.9	2611.4	2672.3
20°	2325.2	2323.9	2412.7	2501.7	2572.3
22.5°	2199.7	2202.7	2296.1	2388.7	2469.0
25°	2011.5	2016.9	2121.1	2213.6	2311.3
27.5°	1837.4	1839.8	1947.6	2045.2	2149.5
30°	1718.6	1725.4	1831.0	1932.0	2040.6
32.5°	1599.7	1607.6	1711.1	1815.5	1926.2
35°	1421.5	1428.3	1524.2	1626.8	1742.2
37.5°	1237.7	1246.9	1332.1	1429.1	1542.6
40°	1118.9	1132.4	1207.7	1299.1	1410.4
42.5°	1004.5	1021.3	1091.1	1177.8	1278.2
45°	852.3	868.6	925.9	996.0	1086.9
47.5°	721.3	740.0	784.0	844.4	922.0
50°	646.9	664.5	705.2	749.9	823.2
52.5°	581.4	599.0	635.2	669.7	732.1
55°	490.0	510.4	540.0	560.5	606.6
57.5°	415.1	434.6	458.1	467.3	495.3
60°	365.1	386.8	408.1	407.1	422.0
62.5°	319.6	338.0	359.3	344.6	345.4
65°	245.7	266.1	290.1	253.5	230.4
67.5°	198.5	202.9	227.7	176.8	149.4
70°	176.3	176.3	183.2	136.9	113.8
72.5°	155.2	155.2	148.8	111.3	87.2
75°	123.5	123.5	112.4	77.2	52.8
77.5°	95.2	94.1	86.1	57.6	38.3
80°	76.4	76.4	69.4	45.5	30.5
82.5°	59.7	59.7	53.9	35.5	22.8
85°	34.7	34.7	31.9	20.6	12.5
87.5°	12.2	12.2	11.1	6.6	5.6
90°	0.0	0.0	0.0	0.0	0.0
92.5°	17.2	91.2	211.5	61.6	46.4
95°	55.9	221.9	997.3	345.2	212.8
97.5°	102.7	259.9	1535.9	1099.1	753.1
100°	135.4	282.5	1652.8	1674.2	1289.6
102.5°	171.5	306.9	1627.1	2143.0	1807.2
105°	227.8	345.5	1493.8	2638.6	2508.3
107.5°	285.0	390.5	1338.2	2778.3	2894.3
110°	324.6	423.3	1248.8	2724.8	2985.4

TEST NUMBER: P522061

CATALOG NUMBER: SQ4-WB-150U-125D-92765-1D-UNV-STD-W-4_5700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	362.4	456.1	1188.6	2598.4	2970.0
115°	423.4	511.7	1132.7	2399.6	2817.8
117.5°	477.2	560.0	1099.6	2182.2	2625.2
120°	520.1	589.5	1096.2	2058.0	2482.5
122.5°	554.5	623.9	1087.6	1949.0	2343.2
125°	597.5	662.7	1081.1	1794.1	2145.0
127.5°	644.4	705.3	1077.7	1701.5	1990.7
130°	668.4	729.4	1072.5	1637.1	1889.3
132.5°	694.2	753.5	1072.5	1586.8	1818.8
135°	730.8	791.7	1068.2	1515.5	1713.0
137.5°	765.2	824.4	1067.8	1455.1	1625.8
140°	791.0	851.9	1066.1	1405.1	1569.0
142.5°	820.2	871.0	1071.2	1365.2	1512.3
145°	861.9	906.0	1076.8	1311.6	1429.3
147.5°	897.6	940.4	1086.3	1257.5	1359.2
150°	928.5	957.9	1089.7	1239.6	1311.1
152.5°	952.6	983.7	1093.2	1215.5	1281.9
155°	984.4	1007.5	1102.6	1185.4	1233.7
157.5°	1023.9	1037.8	1104.8	1171.7	1206.2
160°	1044.6	1055.1	1113.4	1161.3	1190.7
162.5°	1056.6	1068.8	1115.1	1152.6	1175.3
165°	1087.6	1091.8	1115.5	1139.5	1156.3
167.5°	1108.6	1104.8	1125.4	1136.3	1143.0
170°	1115.5	1113.4	1122.0	1124.3	1132.7
172.5°	1131.0	1123.8	1127.1	1120.8	1127.5
175°	1139.2	1132.8	1128.4	1121.8	1113.4
177.5°	1142.6	1132.5	1127.1	1120.3	1122.0
180°	1130.6	1130.6	1130.6	1130.6	1130.6

(END OF REPORT)