

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P934284

Luminaire Tested: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P934284  
REPORT IS A COMBINATION OF REPORTS P933690 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Asymmetric Frosted Continuous I  
Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3711.3 lumens  
Efficiency: N/A  
Efficacy: 130.7 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.26 / 1.36  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 28.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P934284  
CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48
1	97	93	89	86	89	86	83	80	72	70	68	60	58	56	48	47	46	41	41	41	41
2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	40	39	34	34	34	34
3	81	71	64	58	74	66	60	55	56	51	47	46	43	40	38	35	33	29	29	29	29
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	33	31	28	25	25	25	25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	21	21	21	21
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22	19	19	19	19
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19	17	17	17	17
8	54	41	34	28	49	38	31	27	33	27	23	28	23	20	23	20	17	15	15	15	15
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16	13	13	13	13
10	47	34	27	22	43	32	26	21	28	22	19	23	19	16	20	16	14	12	12	12	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	6374	6374	6374	6374
5°	6414	6434	6414	5059
10°	6365	6338	6365	4532
15°	6288	6201	6288	5178
20°	6149	6038	6149	5189
25°	5873	5801	5873	5079
30°	5519	5604	5519	4838
35°	4913	5354	4913	4572
40°	4086	5062	4086	4371
45°	3644	4718	3644	4140
50°	3863	4308	3863	3909
55°	3624	3868	3624	3777
60°	3723	3285	3723	3459
65°	3357	2715	3357	3034
70°	2310	2164	2310	2545
75°	2000	1599	2000	1916
80°	1582	1058	1582	1152
85°	861	560	861	476

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 20°  
 Vertical Angle: 45°  
 Luminance: 5596 cd/sqm



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.0	1.7
10°-20°	176.0	4.7
20°-30°	272.1	7.3
30°-40°	324.9	8.8
40°-50°	326.8	8.8
50°-60°	284.3	7.7
60°-70°	201.6	5.4
70°-80°	106.7	2.9
80°-90°	27.7	0.7
90°-100°	145.0	3.9
100°-110°	381.4	10.3
110°-120°	395.4	10.7
120°-130°	317.2	8.5
130°-140°	248.9	6.7
140°-150°	191.0	5.1
150°-160°	137.6	3.7
160°-170°	84.2	2.3
170°-180°	28.4	0.8
0°-30°	510.2	13.7
0°-40°	835.1	22.5
0°-60°	1446.2	39.0
0°-90°	1782.2	48.0
90°-120°	921.8	24.8
90°-150°	1678.9	45.2
90°-180°	1929.0	52.0
0°-180°	3711.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	687	687	687	687	687	
5°	690	712	690	560	690	65
15°	659	705	659	589	659	185
25°	580	658	580	576	580	266
35°	441	587	441	501	441	273
45°	285	484	285	424	285	228
55°	232	357	232	348	232	213
65°	161	215	161	240	161	154
75°	61	102	61	122	61	64
85°	10	26	10	22	10	14
90°	2	8	2	8	2	2
95°	19	88	19	88	19	21
105°	69	597	69	597	69	73
115°	122	769	122	769	122	120
125°	170	612	170	612	170	151
135°	202	475	202	475	202	157
145°	235	386	235	386	235	147
155°	265	332	265	332	265	122
165°	286	309	286	309	286	81
175°	298	300	298	300	298	28
180°	298	298	298	298	298	



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	692.7	692.7	696.6	698.0	698.0	696.0	694.1	696.0	701.8	703.8	703.1
5°	690.1	695.4	702.5	703.8	705.1	704.5	703.1	704.5	711.0	712.2	712.9
7.5°	685.0	694.7	703.8	705.7	707.7	705.7	705.1	706.4	712.9	714.2	714.2
10°	678.5	692.1	702.5	703.8	705.7	703.8	703.8	706.4	712.9	714.2	714.8
12.5°	669.4	688.2	698.0	699.2	701.8	701.2	700.6	703.1	709.7	711.0	711.0
15°	658.9	681.0	690.1	691.5	696.0	694.7	694.7	697.3	704.5	706.4	705.7
17.5°	644.7	672.0	682.4	684.3	687.6	686.9	687.6	690.1	696.6	698.0	698.6
20°	628.4	659.6	672.0	673.9	677.1	677.1	677.1	680.4	686.9	689.5	689.5
22.5°	606.3	646.6	659.6	661.0	664.8	664.8	666.1	670.6	676.5	677.1	677.1
25°	580.3	632.3	643.3	647.3	651.2	653.1	655.0	657.7	659.6	658.9	659.6
27.5°	553.0	614.2	628.4	631.0	636.2	638.2	640.8	641.4	642.1	644.0	642.7
30°	522.5	588.8	610.2	612.8	621.2	622.6	620.0	621.2	624.5	625.8	627.1
32.5°	488.1	551.1	591.4	597.2	605.0	601.2	600.5	602.4	607.7	607.7	608.9
35°	441.3	521.8	573.8	579.1	584.9	580.3	583.0	583.5	586.8	588.8	588.1
37.5°	389.9	496.5	555.6	559.5	564.1	558.2	562.1	564.1	566.7	565.4	565.4
40°	344.4	456.9	534.2	536.8	540.7	536.1	540.0	541.4	542.6	541.4	540.7
42.5°	310.7	413.3	511.4	514.7	512.1	515.3	516.7	519.3	517.3	514.7	514.7
45°	284.6	401.7	486.7	490.6	486.7	492.0	493.9	493.9	488.1	486.7	486.1
47.5°	276.2	378.2	462.0	462.0	460.1	466.6	469.9	465.3	459.5	457.5	457.5
50°	275.6	352.2	428.3	425.7	434.8	442.5	439.3	434.8	430.2	423.1	423.1
52.5°	250.2	320.4	384.7	394.5	408.7	413.3	408.1	403.6	395.7	392.5	389.9
55°	232.0	287.2	345.1	364.5	379.6	385.4	375.6	371.0	359.4	357.5	356.1
57.5°	228.1	239.1	308.7	333.3	351.6	351.0	345.1	336.6	326.8	324.9	324.3
60°	209.3	172.9	269.7	298.9	317.7	315.8	310.7	302.8	293.7	292.4	291.2
62.5°	189.7	125.4	225.5	258.6	285.3	284.6	280.1	268.4	261.9	258.6	256.0
65°	161.1	105.2	160.6	215.1	253.5	254.8	245.0	236.5	229.4	225.5	224.8
67.5°	122.9	85.8	108.5	179.4	222.9	221.6	209.3	205.3	196.2	194.3	190.4
70°	91.0	57.2	75.4	145.5	193.0	189.7	180.0	175.5	167.1	162.5	159.9
72.5°	75.4	46.1	55.2	113.1	162.5	158.5	150.1	145.0	137.8	133.9	131.3
75°	61.0	48.7	42.2	83.8	131.9	129.4	121.5	116.3	110.5	105.2	105.9
77.5°	44.9	45.4	33.8	61.7	104.7	100.8	96.2	89.7	87.1	81.9	81.9
80°	33.8	35.8	25.4	42.2	75.4	75.4	71.5	67.0	62.4	59.8	59.8
82.5°	22.8	22.8	18.8	26.6	51.4	49.4	46.8	45.4	42.9	41.6	41.6
85°	10.4	13.0	11.7	16.3	27.9	29.3	29.3	27.9	27.3	26.0	26.6
87.5°	3.3	5.8	7.2	9.1	14.3	14.9	15.6	15.6	15.6	16.3	16.3
90°	2.0	3.6	5.2	5.6	8.8	13.1	15.2	13.5	10.1	7.6	7.6
92.5°	7.9	21.5	35.2	38.6	54.2	75.0	85.5	74.9	53.8	38.0	36.4
95°	19.2	44.0	68.9	75.1	133.3	211.0	249.8	222.9	169.1	128.8	124.2
97.5°	33.1	55.0	76.9	82.5	179.6	309.1	373.8	356.9	322.9	297.4	288.7
100°	43.9	63.8	83.7	88.7	196.4	340.1	412.0	413.3	415.8	417.6	407.3
102.5°	53.1	71.7	90.2	94.9	204.2	349.9	422.8	444.5	487.8	520.3	511.3
105°	68.7	84.4	100.1	104.1	209.9	351.1	421.6	470.2	567.3	640.1	635.4
107.5°	84.7	99.3	114.0	117.6	211.0	335.5	397.7	465.4	600.9	702.4	703.6
110°	95.4	108.6	121.9	125.2	209.4	321.6	377.7	453.4	604.8	718.4	723.4



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	106.0	118.6	131.2	134.4	209.4	309.5	359.5	437.0	592.0	708.2	715.9
115°	122.0	133.6	145.3	148.2	211.3	295.5	337.7	412.3	561.6	673.6	684.2
117.5°	137.8	148.4	158.9	161.5	215.3	286.9	322.8	390.1	524.8	625.9	637.6
120°	147.0	157.0	166.9	169.4	218.5	284.0	316.8	378.3	501.5	593.8	605.2
122.5°	156.0	166.1	176.1	178.6	223.1	282.5	312.1	367.5	478.5	561.6	572.9
125°	169.8	178.9	188.0	190.3	229.3	281.2	307.2	354.3	448.5	519.1	529.5
127.5°	180.9	190.2	199.4	201.7	235.5	280.5	303.0	343.4	424.2	484.9	493.6
130°	186.9	196.9	206.8	209.3	240.0	280.9	301.4	337.4	409.4	463.4	471.4
132.5°	193.1	203.1	213.0	215.5	243.7	281.2	300.0	332.2	396.6	445.0	452.2
135°	202.3	211.3	220.4	222.7	247.7	280.9	297.6	324.5	378.5	419.0	425.2
137.5°	211.7	220.6	229.7	231.9	253.7	282.7	297.2	320.0	365.6	399.8	404.9
140°	219.5	227.7	236.0	238.1	257.3	282.9	295.7	315.5	354.9	384.5	389.2
142.5°	225.5	233.1	240.7	242.6	260.4	283.9	295.7	313.1	347.7	373.6	377.7
145°	234.7	241.3	248.0	249.6	264.3	284.0	293.8	307.9	336.2	357.5	360.6
147.5°	243.9	250.4	256.8	258.4	270.3	286.0	293.8	304.9	327.2	343.9	346.5
150°	249.8	255.6	261.5	263.0	273.3	286.9	293.8	303.2	322.0	336.1	338.3
152.5°	256.0	260.5	264.9	266.0	275.3	287.6	293.8	301.8	317.9	329.9	331.5
155°	265.2	268.5	271.8	272.6	279.7	289.1	293.8	300.2	313.0	322.6	323.6
157.5°	272.0	275.2	278.4	279.2	284.0	290.5	293.8	298.7	308.7	316.2	317.0
160°	276.6	279.1	281.6	282.2	286.0	291.2	293.8	298.1	306.6	313.0	313.4
162.5°	281.2	283.0	284.9	285.4	288.2	292.0	293.8	297.4	304.6	310.0	310.4
165°	286.2	287.9	289.6	290.0	291.3	292.9	293.8	296.3	301.5	305.3	305.7
167.5°	290.8	291.6	292.3	292.5	293.6	295.1	295.7	297.5	300.9	303.4	303.6
170°	293.8	294.6	295.4	295.5	295.6	295.7	295.7	297.5	300.9	303.4	303.4
172.5°	295.4	295.5	295.7	295.7	295.7	295.7	295.7	297.1	299.7	301.7	301.6
175°	297.6	297.6	297.6	297.6	297.0	296.1	295.7	296.6	298.4	299.6	299.6
177.5°	297.6	297.6	297.6	297.6	297.1	296.5	296.2	296.9	298.3	299.2	299.0
180°	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	704.5	702.5	704.5	703.1	703.8	701.8	696.0	694.1	696.0	698.0	698.0
5°	712.9	711.6	712.9	712.9	712.2	711.0	704.5	703.1	704.5	705.1	703.8
7.5°	715.5	713.6	715.5	714.2	714.2	712.9	706.4	705.1	705.7	707.7	705.7
10°	715.5	713.6	715.5	714.8	714.2	712.9	706.4	703.8	703.8	705.7	703.8
12.5°	712.2	711.0	712.2	711.0	711.0	709.7	703.1	700.6	701.2	701.8	699.2
15°	707.1	705.1	707.1	705.7	706.4	704.5	697.3	694.7	694.7	696.0	691.5
17.5°	699.2	696.6	699.2	698.6	698.0	696.6	690.1	687.6	686.9	687.6	684.3
20°	690.1	688.2	690.1	689.5	689.5	686.9	680.4	677.1	677.1	677.1	673.9
22.5°	675.9	673.9	675.9	677.1	677.1	676.5	670.6	666.1	664.8	664.8	661.0
25°	659.6	657.7	659.6	659.6	658.9	659.6	657.7	655.0	653.1	651.2	647.3
27.5°	644.0	642.7	644.0	642.7	644.0	642.1	641.4	640.8	638.2	636.2	631.0
30°	628.4	627.1	628.4	627.1	625.8	624.5	621.2	620.0	622.6	621.2	612.8
32.5°	608.9	607.7	608.9	608.9	607.7	607.7	602.4	600.5	601.2	605.0	597.2
35°	588.8	586.8	588.8	588.1	588.8	586.8	583.5	583.0	580.3	584.9	579.1
37.5°	565.4	563.5	565.4	565.4	565.4	566.7	564.1	562.1	558.2	564.1	559.5
40°	541.4	538.8	541.4	540.7	541.4	542.6	541.4	540.0	536.1	540.7	536.8
42.5°	514.1	513.4	514.1	514.7	514.7	517.3	519.3	516.7	515.3	512.1	514.7
45°	484.8	483.5	484.8	486.1	486.7	488.1	493.9	493.9	492.0	486.7	490.6
47.5°	453.6	450.4	453.6	457.5	457.5	459.5	465.3	469.9	466.6	460.1	462.0
50°	420.4	421.1	420.4	423.1	423.1	430.2	434.8	439.3	442.5	434.8	425.7
52.5°	388.0	387.3	388.0	389.9	392.5	395.7	403.6	408.1	413.3	408.7	394.5
55°	355.4	356.8	355.4	356.1	357.5	359.4	371.0	375.6	385.4	379.6	364.5
57.5°	323.0	321.0	323.0	324.3	324.9	326.8	336.6	345.1	351.0	351.6	333.3
60°	285.3	282.7	285.3	291.2	292.4	293.7	302.8	310.7	315.8	317.7	298.9
62.5°	252.1	247.6	252.1	256.0	258.6	261.9	268.4	280.1	284.6	285.3	258.6
65°	217.1	215.1	217.1	224.8	225.5	229.4	236.5	245.0	254.8	253.5	215.1
67.5°	185.2	185.2	185.2	190.4	194.3	196.2	205.3	209.3	221.6	222.9	179.4
70°	156.0	155.3	156.0	159.9	162.5	167.1	175.5	180.0	189.7	193.0	145.5
72.5°	128.0	127.3	128.0	131.3	133.9	137.8	145.0	150.1	158.5	162.5	113.1
75°	103.3	102.0	103.3	105.9	105.2	110.5	116.3	121.5	129.4	131.9	83.8
77.5°	79.3	79.3	79.3	81.9	81.9	87.1	89.7	96.2	100.8	104.7	61.7
80°	59.1	58.5	59.1	59.8	59.8	62.4	67.0	71.5	75.4	75.4	42.2
82.5°	41.6	40.3	41.6	41.6	41.6	42.9	45.4	46.8	49.4	51.4	26.6
85°	26.0	26.0	26.0	26.6	26.0	27.3	27.9	29.3	29.3	27.9	16.3
87.5°	16.9	16.3	16.9	16.3	16.3	15.6	15.6	15.6	14.9	14.3	9.1
90°	7.6	7.6	7.6	7.6	7.6	10.1	13.5	15.2	13.1	8.8	5.6
92.5°	30.4	24.3	30.4	36.4	38.0	53.8	74.9	85.5	75.0	54.2	38.6
95°	105.9	87.7	105.9	124.2	128.8	169.1	222.9	249.8	211.0	133.3	75.1
97.5°	253.9	219.1	253.9	288.7	297.4	322.9	356.9	373.8	309.1	179.6	82.5
100°	365.8	324.3	365.8	407.3	417.6	415.8	413.3	412.0	340.1	196.4	88.7
102.5°	475.9	440.4	475.9	511.3	520.3	487.8	444.5	422.8	349.9	204.2	94.9
105°	616.3	597.2	616.3	635.4	640.1	567.3	470.2	421.6	351.1	209.9	104.1
107.5°	708.1	712.8	708.1	703.6	702.4	600.9	465.4	397.7	335.5	211.0	117.6
110°	743.2	763.1	743.2	723.4	718.4	604.8	453.4	377.7	321.6	209.4	125.2





TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	80°	90°	100°	110°	112.5°	120°	130°	135°	140°	150°	157.5°
112.5°	746.4	776.9	746.4	715.9	708.2	592.0	437.0	359.5	309.5	209.4	134.4
115°	726.6	768.9	726.6	684.2	673.6	561.6	412.3	337.7	295.5	211.3	148.2
117.5°	684.6	731.6	684.6	637.6	625.9	524.8	390.1	322.8	286.9	215.3	161.5
120°	650.8	696.4	650.8	605.2	593.8	501.5	378.3	316.8	284.0	218.5	169.4
122.5°	617.9	662.9	617.9	572.9	561.6	478.5	367.5	312.1	282.5	223.1	178.6
125°	570.8	612.3	570.8	529.5	519.1	448.5	354.3	307.2	281.2	229.3	190.3
127.5°	528.6	563.6	528.6	493.6	484.9	424.2	343.4	303.0	280.5	235.5	201.7
130°	503.8	536.1	503.8	471.4	463.4	409.4	337.4	301.4	280.9	240.0	209.3
132.5°	481.1	510.1	481.1	452.2	445.0	396.6	332.2	300.0	281.2	243.7	215.5
135°	450.2	475.1	450.2	425.2	419.0	378.5	324.5	297.6	280.9	247.7	222.7
137.5°	425.3	445.7	425.3	404.9	399.8	365.6	320.0	297.2	282.7	253.7	231.9
140°	408.3	427.4	408.3	389.2	384.5	354.9	315.5	295.7	282.9	257.3	238.1
142.5°	394.2	410.7	394.2	377.7	373.6	347.7	313.1	295.7	283.9	260.4	242.6
145°	373.1	385.5	373.1	360.6	357.5	336.2	307.9	293.8	284.0	264.3	249.6
147.5°	356.8	367.1	356.8	346.5	343.9	327.2	304.9	293.8	286.0	270.3	258.4
150°	346.6	354.9	346.6	338.3	336.1	322.0	303.2	293.8	286.9	273.3	263.0
152.5°	337.8	344.1	337.8	331.5	329.9	317.9	301.8	293.8	287.6	275.3	266.0
155°	327.8	332.0	327.8	323.6	322.6	313.0	300.2	293.8	289.1	279.7	272.6
157.5°	319.9	322.8	319.9	317.0	316.2	308.7	298.7	293.8	290.5	284.0	279.2
160°	315.1	316.8	315.1	313.4	313.0	306.6	298.1	293.8	291.2	286.0	282.2
162.5°	312.0	313.6	312.0	310.4	310.0	304.6	297.4	293.8	292.0	288.2	285.4
165°	307.5	309.2	307.5	305.7	305.3	301.5	296.3	293.8	292.9	291.3	290.0
167.5°	304.3	304.9	304.3	303.6	303.4	300.9	297.5	295.7	295.1	293.6	292.5
170°	303.4	303.4	303.4	303.4	303.4	300.9	297.5	295.7	295.7	295.6	295.5
172.5°	301.0	300.4	301.0	301.6	301.7	299.7	297.1	295.7	295.7	295.7	295.7
175°	299.6	299.6	299.6	299.6	299.6	298.4	296.6	295.7	296.1	297.0	297.6
177.5°	298.4	297.6	298.4	299.0	299.2	298.3	296.9	296.2	296.5	297.1	297.6
180°	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	696.6	692.7	692.7	686.2	683.6	681.7	678.5	668.7	666.1	663.5	667.4
5°	702.5	695.4	690.1	678.5	668.7	664.8	652.4	629.1	613.5	601.7	595.3
7.5°	703.8	694.7	685.0	666.8	643.3	633.0	595.3	552.4	540.7	530.3	523.7
10°	702.5	692.1	678.5	651.2	595.9	577.7	540.0	512.1	504.9	503.0	504.9
12.5°	698.0	688.2	669.4	623.8	546.5	534.2	512.1	495.8	494.6	497.8	515.3
15°	690.1	681.0	658.9	587.5	519.3	510.2	494.6	488.7	495.8	518.6	571.2
17.5°	682.4	672.0	644.7	551.7	498.5	492.0	480.9	492.6	532.9	563.5	581.0
20°	672.0	659.6	628.4	525.8	483.5	477.6	472.5	525.1	555.6	566.7	576.5
22.5°	659.6	646.6	606.3	507.6	467.9	463.4	466.6	543.3	555.6	563.5	571.9
25°	643.3	632.3	580.3	493.2	455.5	450.4	462.7	541.4	548.5	550.4	567.3
27.5°	628.4	614.2	553.0	480.2	440.6	438.7	466.0	532.9	538.1	540.0	558.2
30°	610.2	588.8	522.5	466.6	425.0	424.3	466.6	522.5	521.2	526.4	544.6
32.5°	591.4	551.1	488.1	449.7	410.1	409.4	462.0	506.9	505.6	512.7	526.4
35°	573.8	521.8	441.3	430.2	391.2	391.9	451.0	488.7	489.3	495.8	504.3
37.5°	555.6	496.5	389.9	408.7	373.1	373.1	436.0	471.8	470.5	472.5	484.1
40°	534.2	456.9	344.4	380.8	356.1	354.2	417.8	453.6	449.0	448.5	464.6
42.5°	511.4	413.3	310.7	343.8	336.6	334.0	395.7	431.5	423.1	425.0	445.8
45°	486.7	401.7	284.6	290.5	316.5	314.5	371.7	406.2	400.3	405.5	426.9
47.5°	462.0	378.2	276.2	241.1	295.1	294.4	345.1	381.5	378.2	383.4	406.2
50°	428.3	352.2	275.6	206.7	271.0	273.5	313.3	357.5	357.5	362.0	386.0
52.5°	384.7	320.4	250.2	187.1	243.0	250.9	285.3	336.6	337.9	342.4	364.0
55°	345.1	287.2	232.0	172.2	209.9	226.8	257.9	315.2	317.7	322.3	341.9
57.5°	308.7	239.1	228.1	154.7	179.4	195.6	233.9	294.4	295.6	299.6	318.4
60°	269.7	172.9	209.3	135.9	152.7	165.0	211.8	269.7	274.2	276.8	293.1
62.5°	225.5	125.4	189.7	122.9	139.7	142.3	193.7	246.3	252.1	254.1	263.9
65°	160.6	105.2	161.1	111.8	126.1	126.7	174.1	222.3	227.4	230.7	237.9
67.5°	108.5	85.8	122.9	101.4	115.7	116.3	155.3	194.3	201.5	204.1	208.6
70°	75.4	57.2	91.0	90.3	104.0	105.2	135.2	169.0	175.5	177.4	180.0
72.5°	55.2	46.1	75.4	81.2	91.7	92.9	114.3	140.4	146.9	148.8	150.1
75°	42.2	48.7	61.0	70.8	78.0	78.6	93.6	114.3	118.9	120.3	120.8
77.5°	33.8	45.4	44.9	57.2	63.7	62.4	73.5	88.4	92.2	92.2	92.2
80°	25.4	35.8	33.8	41.0	46.8	45.4	52.6	63.1	64.3	65.6	65.0
82.5°	18.8	22.8	22.8	26.0	31.2	29.9	35.1	41.0	41.0	41.0	42.2
85°	11.7	13.0	10.4	13.7	17.5	16.9	19.5	22.1	22.8	22.8	21.4
87.5°	7.2	5.8	3.3	5.2	7.8	7.8	9.1	9.8	9.1	9.1	9.1
90°	5.2	3.6	2.0	3.6	5.2	5.6	8.8	13.1	15.2	13.5	10.1
92.5°	35.2	21.5	7.9	21.5	35.2	38.6	54.2	75.0	85.5	74.9	53.8
95°	68.9	44.0	19.2	44.0	68.9	75.1	133.3	211.0	249.8	222.9	169.1
97.5°	76.9	55.0	33.1	55.0	76.9	82.5	179.6	309.1	373.8	356.9	322.9
100°	83.7	63.8	43.9	63.8	83.7	88.7	196.4	340.1	412.0	413.3	415.8
102.5°	90.2	71.7	53.1	71.7	90.2	94.9	204.2	349.9	422.8	444.5	487.8
105°	100.1	84.4	68.7	84.4	100.1	104.1	209.9	351.1	421.6	470.2	567.3
107.5°	114.0	99.3	84.7	99.3	114.0	117.6	211.0	335.5	397.7	465.4	600.9
110°	121.9	108.6	95.4	108.6	121.9	125.2	209.4	321.6	377.7	453.4	604.8



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	160°	170°	180°	190°	200°	202.5°	210°	220°	225°	230°	240°
112.5°	131.2	118.6	106.0	118.6	131.2	134.4	209.4	309.5	359.5	437.0	592.0
115°	145.3	133.6	122.0	133.6	145.3	148.2	211.3	295.5	337.7	412.3	561.6
117.5°	158.9	148.4	137.8	148.4	158.9	161.5	215.3	286.9	322.8	390.1	524.8
120°	166.9	157.0	147.0	157.0	166.9	169.4	218.5	284.0	316.8	378.3	501.5
122.5°	176.1	166.1	156.0	166.1	176.1	178.6	223.1	282.5	312.1	367.5	478.5
125°	188.0	178.9	169.8	178.9	188.0	190.3	229.3	281.2	307.2	354.3	448.5
127.5°	199.4	190.2	180.9	190.2	199.4	201.7	235.5	280.5	303.0	343.4	424.2
130°	206.8	196.9	186.9	196.9	206.8	209.3	240.0	280.9	301.4	337.4	409.4
132.5°	213.0	203.1	193.1	203.1	213.0	215.5	243.7	281.2	300.0	332.2	396.6
135°	220.4	211.3	202.3	211.3	220.4	222.7	247.7	280.9	297.6	324.5	378.5
137.5°	229.7	220.6	211.7	220.6	229.7	231.9	253.7	282.7	297.2	320.0	365.6
140°	236.0	227.7	219.5	227.7	236.0	238.1	257.3	282.9	295.7	315.5	354.9
142.5°	240.7	233.1	225.5	233.1	240.7	242.6	260.4	283.9	295.7	313.1	347.7
145°	248.0	241.3	234.7	241.3	248.0	249.6	264.3	284.0	293.8	307.9	336.2
147.5°	256.8	250.4	243.9	250.4	256.8	258.4	270.3	286.0	293.8	304.9	327.2
150°	261.5	255.6	249.8	255.6	261.5	263.0	273.3	286.9	293.8	303.2	322.0
152.5°	264.9	260.5	256.0	260.5	264.9	266.0	275.3	287.6	293.8	301.8	317.9
155°	271.8	268.5	265.2	268.5	271.8	272.6	279.7	289.1	293.8	300.2	313.0
157.5°	278.4	275.2	272.0	275.2	278.4	279.2	284.0	290.5	293.8	298.7	308.7
160°	281.6	279.1	276.6	279.1	281.6	282.2	286.0	291.2	293.8	298.1	306.6
162.5°	284.9	283.0	281.2	283.0	284.9	285.4	288.2	292.0	293.8	297.4	304.6
165°	289.6	287.9	286.2	287.9	289.6	290.0	291.3	292.9	293.8	296.3	301.5
167.5°	292.3	291.6	290.8	291.6	292.3	292.5	293.6	295.1	295.7	297.5	300.9
170°	295.4	294.6	293.8	294.6	295.4	295.5	295.6	295.7	295.7	297.5	300.9
172.5°	295.7	295.5	295.4	295.5	295.7	295.7	295.7	295.7	295.7	297.1	299.7
175°	297.6	297.6	297.6	297.6	297.6	297.6	297.0	296.1	295.7	296.6	298.4
177.5°	297.6	297.6	297.6	297.6	297.6	297.6	297.1	296.5	296.2	296.9	298.3
180°	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
0°	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9	686.9
2.5°	662.9	661.0	663.5	656.4	663.5	661.0	662.9	667.4	663.5	666.1	668.7
5°	581.6	578.4	568.0	559.5	568.0	578.4	581.6	595.3	601.7	613.5	629.1
7.5°	519.9	517.3	514.7	509.5	514.7	517.3	519.9	523.7	530.3	540.7	552.4
10°	506.2	506.9	510.8	510.2	510.8	506.9	506.2	504.9	503.0	504.9	512.1
12.5°	541.4	547.2	568.6	567.3	568.6	547.2	541.4	515.3	497.8	494.6	495.8
15°	581.6	583.5	588.1	588.8	588.1	583.5	581.6	571.2	518.6	495.8	488.7
17.5°	585.6	586.1	589.4	589.4	589.4	586.1	585.6	581.0	563.5	532.9	492.6
20°	582.3	583.5	590.1	591.4	590.1	583.5	582.3	576.5	566.7	555.6	525.1
22.5°	581.0	583.5	588.8	588.1	588.8	583.5	581.0	571.9	563.5	555.6	543.3
25°	574.5	574.5	575.1	575.8	575.1	574.5	574.5	567.3	550.4	548.5	541.4
27.5°	560.9	562.1	566.0	565.4	566.0	562.1	560.9	558.2	540.0	538.1	532.9
30°	548.5	547.2	543.9	541.4	543.9	547.2	548.5	544.6	526.4	521.2	522.5
32.5°	527.7	524.4	521.2	519.3	521.2	524.4	527.7	526.4	512.7	505.6	506.9
35°	503.0	503.7	503.0	501.1	503.0	503.7	503.0	504.3	495.8	489.3	488.7
37.5°	485.5	486.7	486.1	483.5	486.1	486.7	485.5	484.1	472.5	470.5	471.8
40°	467.3	467.9	467.3	465.3	467.3	467.9	467.3	464.6	448.5	449.0	453.6
42.5°	449.7	449.0	447.1	445.8	447.1	449.0	449.7	445.8	425.0	423.1	431.5
45°	429.6	430.2	426.3	424.3	426.3	430.2	429.6	426.9	405.5	400.3	406.2
47.5°	409.4	409.4	406.2	404.2	406.2	409.4	409.4	406.2	383.4	378.2	381.5
50°	388.0	387.3	382.8	382.1	382.8	387.3	388.0	386.0	362.0	357.5	357.5
52.5°	363.3	363.3	364.0	365.2	364.0	363.3	363.3	364.0	342.4	337.9	336.6
55°	341.9	342.4	347.0	348.4	347.0	342.4	341.9	341.9	322.3	317.7	315.2
57.5°	319.8	319.8	323.0	323.0	323.0	319.8	319.8	318.4	299.6	295.6	294.4
60°	294.4	295.6	298.3	297.7	298.3	295.6	294.4	293.1	276.8	274.2	269.7
62.5°	267.7	269.1	269.7	268.4	269.7	269.1	267.7	263.9	254.1	252.1	246.3
65°	239.8	241.1	241.8	240.4	241.8	241.1	239.8	237.9	230.7	227.4	222.3
67.5°	211.2	210.6	209.9	212.5	209.9	210.6	211.2	208.6	204.1	201.5	194.3
70°	182.0	182.0	181.3	182.7	181.3	182.0	182.0	180.0	177.4	175.5	169.0
72.5°	150.8	150.1	152.7	150.8	152.7	150.1	150.8	150.1	148.8	146.9	140.4
75°	120.3	121.5	120.3	122.2	120.3	121.5	120.3	120.8	120.3	118.9	114.3
77.5°	91.7	92.9	91.7	91.7	91.7	92.9	91.7	92.2	92.2	92.2	88.4
80°	65.0	64.3	64.3	63.7	64.3	64.3	65.0	65.0	65.6	64.3	63.1
82.5°	41.6	41.0	41.0	42.2	41.0	41.0	41.6	42.2	41.0	41.0	41.0
85°	22.8	23.4	22.1	22.1	22.1	23.4	22.8	21.4	22.8	22.8	22.1
87.5°	8.4	7.8	7.8	7.8	7.8	7.8	8.4	9.1	9.1	9.1	9.8
90°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	10.1	13.5	15.2	13.1
92.5°	38.0	36.4	30.4	24.3	30.4	36.4	38.0	53.8	74.9	85.5	75.0
95°	128.8	124.2	105.9	87.7	105.9	124.2	128.8	169.1	222.9	249.8	211.0
97.5°	297.4	288.7	253.9	219.1	253.9	288.7	297.4	322.9	356.9	373.8	309.1
100°	417.6	407.3	365.8	324.3	365.8	407.3	417.6	415.8	413.3	412.0	340.1
102.5°	520.3	511.3	475.9	440.4	475.9	511.3	520.3	487.8	444.5	422.8	349.9
105°	640.1	635.4	616.3	597.2	616.3	635.4	640.1	567.3	470.2	421.6	351.1
107.5°	702.4	703.6	708.1	712.8	708.1	703.6	702.4	600.9	465.4	397.7	335.5
110°	718.4	723.4	743.2	763.1	743.2	723.4	718.4	604.8	453.4	377.7	321.6



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	260°	270°	280°	290°	292.5°	300°	310°	315°	320°
112.5°	708.2	715.9	746.4	776.9	746.4	715.9	708.2	592.0	437.0	359.5	309.5
115°	673.6	684.2	726.6	768.9	726.6	684.2	673.6	561.6	412.3	337.7	295.5
117.5°	625.9	637.6	684.6	731.6	684.6	637.6	625.9	524.8	390.1	322.8	286.9
120°	593.8	605.2	650.8	696.4	650.8	605.2	593.8	501.5	378.3	316.8	284.0
122.5°	561.6	572.9	617.9	662.9	617.9	572.9	561.6	478.5	367.5	312.1	282.5
125°	519.1	529.5	570.8	612.3	570.8	529.5	519.1	448.5	354.3	307.2	281.2
127.5°	484.9	493.6	528.6	563.6	528.6	493.6	484.9	424.2	343.4	303.0	280.5
130°	463.4	471.4	503.8	536.1	503.8	471.4	463.4	409.4	337.4	301.4	280.9
132.5°	445.0	452.2	481.1	510.1	481.1	452.2	445.0	396.6	332.2	300.0	281.2
135°	419.0	425.2	450.2	475.1	450.2	425.2	419.0	378.5	324.5	297.6	280.9
137.5°	399.8	404.9	425.3	445.7	425.3	404.9	399.8	365.6	320.0	297.2	282.7
140°	384.5	389.2	408.3	427.4	408.3	389.2	384.5	354.9	315.5	295.7	282.9
142.5°	373.6	377.7	394.2	410.7	394.2	377.7	373.6	347.7	313.1	295.7	283.9
145°	357.5	360.6	373.1	385.5	373.1	360.6	357.5	336.2	307.9	293.8	284.0
147.5°	343.9	346.5	356.8	367.1	356.8	346.5	343.9	327.2	304.9	293.8	286.0
150°	336.1	338.3	346.6	354.9	346.6	338.3	336.1	322.0	303.2	293.8	286.9
152.5°	329.9	331.5	337.8	344.1	337.8	331.5	329.9	317.9	301.8	293.8	287.6
155°	322.6	323.6	327.8	332.0	327.8	323.6	322.6	313.0	300.2	293.8	289.1
157.5°	316.2	317.0	319.9	322.8	319.9	317.0	316.2	308.7	298.7	293.8	290.5
160°	313.0	313.4	315.1	316.8	315.1	313.4	313.0	306.6	298.1	293.8	291.2
162.5°	310.0	310.4	312.0	313.6	312.0	310.4	310.0	304.6	297.4	293.8	292.0
165°	305.3	305.7	307.5	309.2	307.5	305.7	305.3	301.5	296.3	293.8	292.9
167.5°	303.4	303.6	304.3	304.9	304.3	303.6	303.4	300.9	297.5	295.7	295.1
170°	303.4	303.4	303.4	303.4	303.4	303.4	303.4	300.9	297.5	295.7	295.7
172.5°	301.7	301.6	301.0	300.4	301.0	301.6	301.7	299.7	297.1	295.7	295.7
175°	299.6	299.6	299.6	299.6	299.6	299.6	299.6	298.4	296.6	295.7	296.1
177.5°	299.2	299.0	298.4	297.6	298.4	299.0	299.2	298.3	296.9	296.2	296.5
180°	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6	297.6



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	330°	337.5°	340°	350°	360°
0°	686.9	686.9	686.9	686.9	686.9
2.5°	678.5	681.7	683.6	686.2	692.7
5°	652.4	664.8	668.7	678.5	690.1
7.5°	595.3	633.0	643.3	666.8	685.0
10°	540.0	577.7	595.9	651.2	678.5
12.5°	512.1	534.2	546.5	623.8	669.4
15°	494.6	510.2	519.3	587.5	658.9
17.5°	480.9	492.0	498.5	551.7	644.7
20°	472.5	477.6	483.5	525.8	628.4
22.5°	466.6	463.4	467.9	507.6	606.3
25°	462.7	450.4	455.5	493.2	580.3
27.5°	466.0	438.7	440.6	480.2	553.0
30°	466.6	424.3	425.0	466.6	522.5
32.5°	462.0	409.4	410.1	449.7	488.1
35°	451.0	391.9	391.2	430.2	441.3
37.5°	436.0	373.1	373.1	408.7	389.9
40°	417.8	354.2	356.1	380.8	344.4
42.5°	395.7	334.0	336.6	343.8	310.7
45°	371.7	314.5	316.5	290.5	284.6
47.5°	345.1	294.4	295.1	241.1	276.2
50°	313.3	273.5	271.0	206.7	275.6
52.5°	285.3	250.9	243.0	187.1	250.2
55°	257.9	226.8	209.9	172.2	232.0
57.5°	233.9	195.6	179.4	154.7	228.1
60°	211.8	165.0	152.7	135.9	209.3
62.5°	193.7	142.3	139.7	122.9	189.7
65°	174.1	126.7	126.1	111.8	161.1
67.5°	155.3	116.3	115.7	101.4	122.9
70°	135.2	105.2	104.0	90.3	91.0
72.5°	114.3	92.9	91.7	81.2	75.4
75°	93.6	78.6	78.0	70.8	61.0
77.5°	73.5	62.4	63.7	57.2	44.9
80°	52.6	45.4	46.8	41.0	33.8
82.5°	35.1	29.9	31.2	26.0	22.8
85°	19.5	16.9	17.5	13.7	10.4
87.5°	9.1	7.8	7.8	5.2	3.3
90°	8.8	5.6	5.2	3.6	2.0
92.5°	54.2	38.6	35.2	21.5	7.9
95°	133.3	75.1	68.9	44.0	19.2
97.5°	179.6	82.5	76.9	55.0	33.1
100°	196.4	88.7	83.7	63.8	43.9
102.5°	204.2	94.9	90.2	71.7	53.1
105°	209.9	104.1	100.1	84.4	68.7
107.5°	211.0	117.6	114.0	99.3	84.7
110°	209.4	125.2	121.9	108.6	95.4



TEST NUMBER: P934284

CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CANDELA DISTRIBUTION (continued):**

	330°	337.5°	340°	350°	360°
112.5°	209.4	134.4	131.2	118.6	106.0
115°	211.3	148.2	145.3	133.6	122.0
117.5°	215.3	161.5	158.9	148.4	137.8
120°	218.5	169.4	166.9	157.0	147.0
122.5°	223.1	178.6	176.1	166.1	156.0
125°	229.3	190.3	188.0	178.9	169.8
127.5°	235.5	201.7	199.4	190.2	180.9
130°	240.0	209.3	206.8	196.9	186.9
132.5°	243.7	215.5	213.0	203.1	193.1
135°	247.7	222.7	220.4	211.3	202.3
137.5°	253.7	231.9	229.7	220.6	211.7
140°	257.3	238.1	236.0	227.7	219.5
142.5°	260.4	242.6	240.7	233.1	225.5
145°	264.3	249.6	248.0	241.3	234.7
147.5°	270.3	258.4	256.8	250.4	243.9
150°	273.3	263.0	261.5	255.6	249.8
152.5°	275.3	266.0	264.9	260.5	256.0
155°	279.7	272.6	271.8	268.5	265.2
157.5°	284.0	279.2	278.4	275.2	272.0
160°	286.0	282.2	281.6	279.1	276.6
162.5°	288.2	285.4	284.9	283.0	281.2
165°	291.3	290.0	289.6	287.9	286.2
167.5°	293.6	292.5	292.3	291.6	290.8
170°	295.6	295.5	295.4	294.6	293.8
172.5°	295.7	295.7	295.7	295.5	295.4
175°	297.0	297.6	297.6	297.6	297.6
177.5°	297.1	297.6	297.6	297.6	297.6
180°	297.6	297.6	297.6	297.6	297.6



TEST NUMBER: P934284  
 CATALOG NUMBER: SQ4-FA-050U-050D-B2750-1D-UNV-STD-W-4-3500K

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.04	11.89	12.02	12.87	14.17	13.84	14.68	14.81	15.67	16.97
	3H	11.52	12.27	12.50	13.27	14.59	15.17	15.93	16.16	16.93	18.25
	4H	11.71	12.42	12.71	13.43	14.75	15.61	16.33	16.61	17.33	18.66
	6H	11.83	12.49	12.84	13.49	14.83	15.89	16.55	16.90	17.55	18.89
	8H	11.83	12.46	12.84	13.48	14.82	15.96	16.58	16.97	17.61	18.94
	12H	11.80	12.40	12.82	13.41	14.77	15.99	16.59	17.01	17.60	18.97
4H	2H	12.07	12.78	13.07	13.78	15.11	14.25	14.96	15.25	15.97	17.29
	3H	13.09	13.69	14.10	14.72	16.06	15.74	16.34	16.76	17.37	18.71
	4H	13.37	13.91	14.39	14.93	16.30	16.26	16.81	17.29	17.83	19.20
	6H	13.49	13.96	14.52	15.00	16.37	16.62	17.09	17.65	18.13	19.50
	8H	13.50	13.93	14.53	14.97	16.35	16.72	17.16	17.76	18.20	19.58
	12H	13.46	13.86	14.51	14.91	16.29	16.77	17.17	17.82	18.22	19.60
8H	4H	13.81	14.25	14.85	15.29	16.67	16.39	16.83	17.42	17.86	19.24
	6H	14.07	14.44	15.13	15.52	16.89	16.82	17.18	17.87	18.26	19.63
	8H	14.12	14.44	15.18	15.50	16.89	16.96	17.28	18.03	18.35	19.74
	12H	14.10	14.38	15.17	15.44	16.88	17.05	17.33	18.12	18.39	19.83
12H	4H	13.82	14.21	14.87	15.27	16.65	16.35	16.75	17.40	17.80	19.18
	6H	14.13	14.45	15.20	15.52	16.91	16.81	17.13	17.88	18.20	19.59
	8H	14.20	14.48	15.27	15.54	16.97	16.97	17.25	18.04	18.31	19.74