

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621748

Luminaire Tested: VLT-FB-025U-050D-930-UNV-STD-W-4

Issue Date: 9/2/2020

**Test Information**

Test Method: LM-79-2019  
Report Number: P621748  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 9/2/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: VLT-FB-025U-050D-930-UNV-STD-W-4  
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE  
LIGHT SHAPING LENS - BATWING  
DOWNLIGHT 500 LUMENS PER FOOT  
UPLIGHT 250 LUMENS PER FOOT  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2353.5 lumens  
Efficiency: N/A  
Efficacy: 103.7 lumens/watt  
Spacing Criteria (0/90/45): 1.05 / 1.83 / 1.75  
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 22.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P621748  
CATALOG NUMBER: VLT-FB-025U-050D-930-UNV-STD-W-4

### Luminous Intensity Polar Plot





TEST NUMBER: P621748

CATALOG NUMBER: VLT-FB-025U-050D-930-UNV-STD-W-4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									70									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	63																			
1	101	97	94	90	95	92	88	85	81	78	76	71	69	67	62	60	59	55																			
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	55	53	51	47																			
3	85	76	69	64	80	72	66	61	64	59	55	56	53	50	49	47	44	41																			
4	78	68	60	54	73	64	57	52	57	52	47	51	46	43	45	41	39	36																			
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	40	37	34	31																			
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	30	28																			
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27	25																			
8	57	45	38	32	54	43	36	31	39	33	29	35	30	26	31	27	24	22																			
9	54	41	34	29	50	39	32	28	36	30	26	32	27	24	29	25	22	20																			
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	26	23	20	18																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2977	2977	2977
5°	2952	3164	3389
10°	2894	3742	4620
15°	2806	4560	5625
20°	2672	5254	5911
25°	2531	5682	5968
30°	2368	5813	5939
35°	2208	5813	5702
40°	2078	5632	5521
45°	1977	5460	2644
50°	1920	5168	2279
55°	1867	3461	1804
60°	1816	2105	1307
65°	1776	1603	1360
70°	1752	1397	1397
75°	1708	1450	1403
80°	1500	1463	1393
85°	1112	1531	1317

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 5460 cd/sqm



TEST NUMBER: P621748

CATALOG NUMBER: VLT-FB-025U-050D-930-UNV-STD-W-4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.7	1.9
10°-20°	165.0	7.0
20°-30°	279.4	11.9
30°-40°	338.9	14.4
40°-50°	298.3	12.7
50°-60°	184.6	7.8
60°-70°	100.1	4.3
70°-80°	57.0	2.4
80°-90°	19.0	0.8
90°-100°	19.8	0.8
100°-110°	141.3	6.0
110°-120°	191.9	8.2
120°-130°	156.1	6.6
130°-140°	125.6	5.3
140°-150°	99.0	4.2
150°-160°	72.4	3.1
160°-170°	45.0	1.9
170°-180°	15.3	0.7
0°-30°	489.1	20.8
0°-40°	828.0	35.2
0°-60°	1310.9	55.7
0°-90°	1487.0	63.2
90°-120°	353.0	15.0
90°-150°	733.8	31.2
90°-180°	866.0	36.8
0°-180°	2353.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	415	415	415	415	415	
5°	410	423	439	458	470	39
15°	378	436	614	726	757	106
25°	320	438	718	739	754	147
35°	252	406	664	654	651	158
45°	195	333	538	456	260	151
55°	149	232	277	160	144	134
65°	105	131	94	81	80	104
75°	62	54	52	51	51	64
85°	14	18	19	17	16	16
90°	0	1	2	3	3	1
95°	8	15	8	9	11	9
105°	31	48	184	235	155	33
115°	56	68	158	329	384	55
125°	80	91	149	261	308	71
135°	99	110	150	215	246	76
145°	118	128	151	187	207	74
155°	138	143	154	170	178	63
165°	153	155	158	162	165	43
175°	161	162	161	160	159	15
180°	161	161	161	161	161	

TEST NUMBER: P621748

CATALOG NUMBER: VLT-FB-025U-050D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	414.8	414.8	414.8	414.8	414.8
2.5°	413.5	418.1	420.2	424.3	426.3
5°	409.8	423.0	439.3	458.1	470.5
7.5°	403.2	426.8	478.4	537.9	563.3
10°	397.1	429.3	513.5	599.5	634.1
12.5°	390.4	431.8	554.7	658.8	694.1
15°	377.7	435.5	613.8	725.9	757.2
17.5°	361.4	437.7	665.1	761.4	781.5
20°	349.9	438.1	688.0	765.8	774.0
22.5°	339.1	438.6	704.2	755.0	761.9
25°	319.6	437.5	717.6	739.0	753.8
27.5°	300.0	432.6	711.0	728.3	739.0
30°	285.8	427.6	701.5	715.9	716.7
32.5°	272.4	419.4	687.4	691.6	690.4
35°	252.1	405.5	663.6	654.2	650.9
37.5°	233.2	386.9	628.9	613.8	613.0
40°	221.8	373.5	601.2	586.9	589.4
42.5°	211.0	358.0	576.2	559.5	513.2
45°	194.8	333.3	538.0	455.9	260.5
47.5°	180.8	305.1	494.6	244.2	224.3
50°	172.0	285.8	462.9	214.8	204.1
52.5°	163.2	267.8	421.8	193.1	179.1
55°	149.2	232.5	276.6	159.9	144.2
57.5°	135.9	195.4	169.0	124.2	107.3
60°	126.5	173.5	146.7	100.1	91.1
62.5°	117.7	155.5	125.1	88.8	87.0
65°	104.6	130.9	94.4	80.9	80.1
67.5°	92.2	107.6	72.0	72.8	72.0
70°	83.5	90.9	66.6	67.4	66.6
72.5°	75.4	74.9	61.2	60.7	59.9
75°	61.6	54.1	52.3	51.4	50.6
77.5°	47.0	40.0	42.2	41.3	40.5
80°	36.3	33.8	35.4	34.6	33.7
82.5°	26.8	27.6	28.7	27.1	26.3
85°	13.5	18.4	18.6	16.8	16.0
87.5°	4.0	8.2	7.8	6.7	6.0
90°	0.0	1.0	2.0	3.0	3.0
92.5°	2.4	3.4	4.5	6.3	7.1
95°	8.1	15.1	8.1	9.2	11.2
97.5°	14.4	28.9	59.7	17.6	15.2
100°	19.3	36.1	119.7	35.2	23.3
102.5°	24.1	41.8	161.9	93.0	50.9
105°	31.4	48.3	183.6	234.6	155.2
107.5°	38.8	51.5	175.3	341.4	319.8
110°	43.6	55.5	170.4	358.7	385.5



TEST NUMBER: P621748

CATALOG NUMBER: VLT-FB-025U-050D-930-UNV-STD-W-4

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	48.5	60.4	165.6	348.6	393.6
115°	55.8	67.7	158.3	328.9	384.5
117.5°	63.3	75.0	156.4	307.7	364.8
120°	69.0	79.9	153.2	291.5	351.0
122.5°	73.0	84.7	149.1	277.6	332.3
125°	80.1	91.1	149.1	260.8	308.4
127.5°	86.0	97.1	149.3	241.3	288.3
130°	89.3	101.2	150.1	228.3	272.9
132.5°	93.3	105.2	150.1	222.4	259.1
135°	99.4	110.3	150.1	214.8	246.5
137.5°	104.5	116.2	150.1	206.4	233.5
140°	108.6	119.5	150.1	201.4	226.2
142.5°	112.6	122.7	151.0	195.7	218.9
145°	117.7	127.6	151.2	187.1	207.0
147.5°	123.8	132.5	152.4	180.9	196.2
150°	127.8	135.8	153.2	176.8	189.7
152.5°	131.9	139.0	153.2	173.5	184.0
155°	138.0	142.9	154.2	169.6	177.5
157.5°	142.8	147.6	155.4	167.1	172.9
160°	146.1	150.1	156.2	165.5	170.4
162.5°	148.5	152.5	157.0	164.6	168.0
165°	153.2	155.2	158.3	162.4	165.4
167.5°	155.8	157.6	159.3	161.3	163.1
170°	158.3	159.3	159.3	161.3	162.3
172.5°	159.1	160.9	160.1	160.5	161.5
175°	161.3	162.3	161.3	160.3	159.3
177.5°	161.3	162.1	161.3	161.3	160.5
180°	161.3	161.3	161.3	161.3	161.3

(END OF REPORT)