

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P621815

Luminaire Tested: VLT-FB-075U-125D-935-UNV-STD-W-4

Issue Date: 9/2/2020

Test Information

Test Method: LM-79-2019
Report Number: P621815
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2203-563-26, G2-2203-563-19)
Test Lab: INNOVATION CENTER
Issue Date: 9/2/2020
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: VLT-FB-075U-125D-935-UNV-STD-W-4
Description: CORELITE VAULT SUSPENDED LED LUMINAIRE
LIGHT SHAPING LENS - BATWING
DOWNLIGHT 1250 LUMENS PER FOOT
UPLIGHT 750 LUMENS PER FOOT
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6622.9 lumens
Efficiency: N/A
Efficacy: 111.3 lumens/watt
Spacing Criteria (0/90/45): 1.05 / 1.83 / 1.75
Luminous Opening: Rectangular (W 0.38' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P621815
CATALOG NUMBER: VLT-FB-075U-125D-935-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P621815

CATALOG NUMBER: VLT-FB-075U-125D-935-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	109	109	109	109	102	102	102	102	89	89	89	76	76	76	65	65	65	60																			
1	101	97	93	90	94	90	87	84	79	77	75	68	67	65	59	58	56	52																			
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45																			
3	85	76	68	63	79	71	65	60	62	58	54	55	51	48	47	45	42	39																			
4	78	67	60	54	73	63	57	51	56	51	46	49	45	42	43	39	37	34																			
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	32	30																			
6	66	54	46	41	62	51	44	39	46	40	35	40	36	32	35	32	29	26																			
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	28	26	23																			
8	57	45	37	32	53	42	35	30	38	32	28	34	29	26	30	26	23	21																			
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21	19																			
10	50	37	30	25	46	36	29	25	32	26	23	28	24	21	25	22	19	17																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7934	7934	7934
5°	7868	8434	9033
10°	7713	9973	12314
15°	7480	12155	14993
20°	7123	14004	15755
25°	6744	15143	15908
30°	6313	15493	15829
35°	5887	15494	15199
40°	5537	15011	14715
45°	5268	14551	7047
50°	5119	13774	6072
55°	4977	9222	4808
60°	4838	5612	3483
65°	4732	4274	3625
70°	4668	3724	3724
75°	4550	3862	3737
80°	3992	3901	3715
85°	2964	4067	3516

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 14551 cd/sqm



TEST NUMBER: P621815

CATALOG NUMBER: VLT-FB-075U-125D-935-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.2	1.8
10°-20°	439.6	6.6
20°-30°	744.6	11.2
30°-40°	903.3	13.6
40°-50°	795.1	12.0
50°-60°	492.0	7.4
60°-70°	266.7	4.0
70°-80°	152.0	2.3
80°-90°	50.8	0.8
90°-100°	60.9	0.9
100°-110°	433.8	6.5
110°-120°	588.9	8.9
120°-130°	479.3	7.2
130°-140°	385.5	5.8
140°-150°	303.9	4.6
150°-160°	222.2	3.4
160°-170°	138.0	2.1
170°-180°	47.1	0.7
0°-30°	1303.5	19.7
0°-40°	2206.9	33.3
0°-60°	3494.0	52.8
0°-90°	3963.5	59.8
90°-120°	1083.5	16.4
90°-150°	2252.2	34.0
90°-180°	2659.0	40.1
0°-180°	6622.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1092	1127	1171	1221	1254	103
15°	1007	1161	1636	1935	2018	282
25°	852	1166	1912	1970	2009	391
35°	672	1081	1769	1744	1735	421
45°	519	888	1434	1215	694	403
55°	398	620	737	426	384	356
65°	279	349	252	216	214	277
75°	164	144	139	137	135	171
85°	36	49	49	45	43	44
90°	0	3	6	9	9	3
95°	25	46	25	28	34	28
105°	96	148	564	720	476	102
115°	171	208	486	1010	1180	170
125°	246	280	458	800	947	219
135°	305	339	461	659	757	235
145°	361	392	464	574	635	227
155°	424	439	473	521	545	194
165°	470	476	486	498	508	132
175°	495	498	495	492	489	47
180°	495	495	495	495	495	



TEST NUMBER: P621815

CATALOG NUMBER: VLT-FB-075U-125D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1105.7	1105.7	1105.7	1105.7	1105.7
2.5°	1102.1	1114.4	1120.1	1131.0	1136.3
5°	1092.2	1127.4	1170.9	1221.1	1254.0
7.5°	1074.7	1137.5	1275.1	1433.6	1501.2
10°	1058.5	1144.2	1368.6	1597.7	1690.0
12.5°	1040.5	1150.8	1478.3	1756.0	1850.0
15°	1006.8	1160.6	1636.1	1934.6	2018.1
17.5°	963.2	1166.7	1772.7	2029.2	2082.8
20°	932.7	1167.8	1833.8	2041.1	2063.1
22.5°	903.9	1168.9	1877.0	2012.3	2030.7
25°	851.7	1166.0	1912.5	1969.6	2009.1
27.5°	799.6	1153.0	1895.0	1941.0	1969.6
30°	761.9	1139.8	1869.8	1908.1	1910.3
32.5°	725.9	1117.9	1832.0	1843.2	1840.1
35°	672.0	1080.7	1768.7	1743.7	1735.0
37.5°	621.6	1031.2	1676.1	1636.0	1633.8
40°	591.1	995.4	1602.4	1564.3	1570.9
42.5°	562.3	954.3	1535.8	1491.2	1367.7
45°	519.1	888.3	1433.8	1215.2	694.4
47.5°	481.8	813.2	1318.3	651.0	597.8
50°	458.5	761.7	1233.8	572.4	543.9
52.5°	435.1	713.7	1124.1	514.7	477.3
55°	397.8	619.7	737.1	426.0	384.3
57.5°	362.3	520.9	450.4	331.1	285.9
60°	337.1	462.4	391.0	266.9	242.7
62.5°	313.7	414.4	333.5	236.8	231.9
65°	278.7	349.0	251.7	215.7	213.5
67.5°	245.9	286.7	191.9	194.1	191.9
70°	222.5	242.3	177.5	179.7	177.5
72.5°	200.9	199.6	163.2	161.8	159.6
75°	164.1	144.3	139.3	137.0	134.8
77.5°	125.4	106.5	112.4	110.1	107.9
80°	96.6	90.0	94.4	92.1	89.9
82.5°	71.5	73.7	76.4	72.3	70.1
85°	36.0	49.1	49.4	44.9	42.7
87.5°	10.8	21.9	21.0	18.0	16.3
90°	0.0	3.0	6.2	9.3	9.3
92.5°	7.5	10.5	13.7	19.4	21.8
95°	24.9	46.2	24.9	28.2	34.3
97.5°	44.2	88.7	183.1	54.0	46.7
100°	59.2	110.9	367.4	108.2	71.6
102.5°	74.1	128.3	497.0	285.4	156.3
105°	96.5	148.3	563.6	720.0	476.4
107.5°	118.9	157.9	538.1	1047.8	981.5
110°	133.9	170.4	523.1	1101.0	1183.2



TEST NUMBER: P621815

CATALOG NUMBER: VLT-FB-075U-125D-935-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	148.8	185.4	508.2	1069.9	1208.1
115°	171.3	207.8	485.8	1009.6	1180.1
117.5°	194.3	230.2	480.1	944.3	1119.7
120°	211.7	245.2	470.2	894.7	1077.4
122.5°	224.2	260.1	457.7	852.0	1020.1
125°	246.0	279.5	457.7	800.5	946.6
127.5°	264.0	298.1	458.3	740.6	884.9
130°	274.0	310.5	460.8	700.6	837.6
132.5°	286.5	323.0	460.8	682.6	795.3
135°	305.2	338.6	460.8	659.2	756.7
137.5°	320.7	356.6	460.8	633.4	716.8
140°	333.2	366.7	460.8	618.3	694.4
142.5°	345.6	376.7	463.3	600.7	672.0
145°	361.2	391.6	464.0	574.3	635.2
147.5°	379.9	406.7	467.7	555.3	602.2
150°	392.3	416.7	470.2	542.7	582.3
152.5°	404.8	426.7	470.2	532.6	564.8
155°	423.5	438.7	473.3	520.6	544.9
157.5°	438.4	453.0	477.0	512.9	530.6
160°	448.4	460.6	479.5	507.9	523.1
162.5°	455.9	468.0	482.0	505.3	515.6
165°	470.2	476.3	485.8	498.4	507.5
167.5°	478.3	483.8	488.9	495.2	500.7
170°	485.8	488.8	488.9	495.2	498.2
172.5°	488.2	493.7	491.4	492.7	495.7
175°	495.1	498.1	495.1	491.9	488.9
177.5°	495.1	497.5	495.1	495.0	492.6
180°	495.1	495.1	495.1	495.1	495.1

(END OF REPORT)