

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P727024

Luminaire Tested: **MRI-DRV-FLD4C-20-L940 F4LC-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P727024
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-20-L940 F4LC-W-X-LI
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI
LEDS, 4LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2003.0 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P727024
CATALOG NUMBER: MRI-DRV-FLD4C-20-L940 F4LC-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P727024
 CATALOG NUMBER: MRI-DRV-FLD4C-20-L940 F4LC-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.0	6.0
10°-20°	378.7	18.9
20°-30°	590.8	29.5
30°-40°	574.9	28.7
40°-50°	287.2	14.3
50°-60°	44.5	2.2
60°-70°	5.4	0.3
70°-80°	1.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1089.6	54.4
0°-40°	1664.5	83.1
0°-60°	1996.1	99.7
0°-90°	2003.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2003.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1227	
5°	1243	120
15°	1337	379
25°	1298	591
35°	934	575
45°	360	287
55°	37	44
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P727024
CATALOG NUMBER: MRI-DRV-FLD4C-20-L940 F4LC-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1227.2
2.5°	1231.8
5°	1243.3
7.5°	1261.7
10°	1284.6
12.5°	1314.4
15°	1337.4
17.5°	1355.7
20°	1358.0
22.5°	1342.0
25°	1298.4
27.5°	1234.1
30°	1153.8
32.5°	1053.0
35°	933.7
37.5°	802.8
40°	665.2
42.5°	518.5
45°	360.2
47.5°	231.7
50°	139.9
52.5°	75.7
55°	36.7
57.5°	16.1
60°	9.2
62.5°	6.9
65°	4.6
67.5°	4.6
70°	2.3
72.5°	2.3
75°	2.3
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)