

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P727240

Luminaire Tested: **MRI-DRV-FLD4C-30-L950 F4LC-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P727240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-30-L950 F4LC-W-X-LI
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI
LEDS, 4LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3015.0 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P727240
CATALOG NUMBER: MRI-DRV-FLD4C-30-L950 F4LC-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P727240
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L950 F4LC-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.7	6.0
10°-20°	570.1	18.9
20°-30°	889.4	29.5
30°-40°	865.4	28.7
40°-50°	432.2	14.3
50°-60°	66.9	2.2
60°-70°	8.1	0.3
70°-80°	2.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1640.1	54.4
0°-40°	2505.5	83.1
0°-60°	3004.6	99.7
0°-90°	3015.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3015.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1847	
5°	1872	181
15°	2013	570
25°	1954	889
35°	1405	865
45°	542	432
55°	55	67
65°	7	8
75°	4	2
85°	0	0
90°	0	



TEST NUMBER: P727240
CATALOG NUMBER: MRI-DRV-FLD4C-30-L950 F4LC-W-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1847.3
2.5°	1854.2
5°	1871.5
7.5°	1899.1
10°	1933.7
12.5°	1978.5
15°	2013.1
17.5°	2040.7
20°	2044.2
22.5°	2020.0
25°	1954.4
27.5°	1857.6
30°	1736.8
32.5°	1585.0
35°	1405.4
37.5°	1208.5
40°	1001.3
42.5°	780.4
45°	542.2
47.5°	348.7
50°	210.6
52.5°	113.9
55°	55.3
57.5°	24.2
60°	13.8
62.5°	10.4
65°	6.9
67.5°	6.9
70°	3.5
72.5°	3.5
75°	3.5
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)