

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P205314

Luminaire Tested: **MRI-DRV-FLD6C-40-L950 F6LC-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P205314
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-40-L950 F6LC-M-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI
LEDS, 6LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3814.0 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P205314
CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P205314
 CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.7	11.5
10°-20°	1094.7	28.7
20°-30°	1272.5	33.4
30°-40°	779.3	20.4
40°-50°	193.5	5.1
50°-60°	22.6	0.6
60°-70°	8.4	0.2
70°-80°	3.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2806.9	73.6
0°-40°	3586.2	94.0
0°-60°	3802.3	99.7
0°-90°	3814.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3814.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4773	
5°	4710	440
15°	3929	1095
25°	2816	1273
35°	1220	779
45°	215	194
55°	20	23
65°	10	8
75°	5	3
85°	0	0
90°	0	



TEST NUMBER: P205314
CATALOG NUMBER: MRI-DRV-FLD6C-40-L950 F6LC-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	4773.0
2.5°	4768.1
5°	4709.6
7.5°	4582.7
10°	4411.8
12.5°	4187.4
15°	3928.7
17.5°	3650.5
20°	3377.3
22.5°	3103.9
25°	2816.1
27.5°	2484.2
30°	2103.4
32.5°	1659.3
35°	1220.1
37.5°	858.9
40°	585.7
42.5°	366.0
45°	214.8
47.5°	122.0
50°	63.4
52.5°	29.3
55°	19.5
57.5°	14.6
60°	14.6
62.5°	9.8
65°	9.8
67.5°	4.9
70°	4.9
72.5°	4.9
75°	4.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)