

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579701

Luminaire Tested: **HCC4S10D010BZ-HM40525827-41WWWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579701  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S10D010BZ-HM40525827-41WWWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 988.2 lumens  
Efficiency: N/A  
Efficacy: 99.8 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579701  
CATALOG NUMBER: HCC4S10D010BZ-HM40525827-41WWWB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579701

CATALOG NUMBER: HCC4S10D010BZ-HM40525827-41WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	62857	62857	62857
5°	66081	62775	60423
10°	68398	62010	57677
15°	70489	60886	55203
20°	70579	58385	52032
25°	67926	54561	48791
30°	63067	50220	45562
35°	56527	45203	42147
40°	49609	40335	38982
45°	43348	35707	35951
50°	38282	31240	32391
55°	33741	27698	29117
60°	30170	24546	25483
65°	26734	21598	21598
70°	23369	18393	18393
75°	19968	15584	17442
80°	15769	13922	15769
85°	10190	12029	14860



TEST NUMBER: P579701  
 CATALOG NUMBER: HCC4S10D010BZ-HM40525827-41WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.3	4.9
10°-20°	136.0	13.8
20°-30°	190.5	19.3
30°-40°	196.2	19.9
40°-50°	167.1	16.9
50°-60°	123.8	12.5
60°-70°	77.7	7.9
70°-80°	38.6	3.9
80°-90°	10.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.7	37.9
0°-40°	570.9	57.8
0°-60°	861.8	87.2
0°-90°	988.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	988.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	510	510	510	510	510	
5°	534	525	507	492	488	51
15°	552	527	477	442	432	155
25°	499	464	401	366	358	228
35°	375	347	300	281	280	234
45°	248	232	205	201	206	193
55°	157	144	129	131	135	142
65°	92	82	74	73	74	91
75°	42	37	33	35	37	45
85°	7	7	8	10	10	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579701

CATALOG NUMBER: HCC4S10D010BZ-HM40525827-41WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6	509.6
2.5°	520.6	518.7	516.1	511.5	507.0	503.0	499.1	497.1	496.5
5°	533.7	529.9	524.6	516.1	507.0	499.1	492.5	489.2	488.0
7.5°	542.9	539.0	530.5	517.4	504.4	492.5	482.1	477.5	476.1
10°	546.1	541.6	529.9	512.2	495.1	480.8	469.0	463.2	460.5
12.5°	548.7	542.9	527.9	507.0	486.0	468.3	455.9	448.0	446.1
15°	552.0	545.6	527.2	501.7	476.8	455.9	442.2	434.9	432.3
17.5°	548.7	541.6	520.1	491.3	463.2	440.2	425.2	418.7	416.1
20°	537.7	529.9	505.6	474.9	444.8	421.3	406.2	399.7	396.4
22.5°	520.6	512.2	487.3	454.6	423.9	400.9	386.6	380.1	378.0
25°	499.1	490.6	464.4	431.1	400.9	378.7	366.3	360.4	358.5
27.5°	473.5	465.1	439.6	406.8	378.0	357.1	347.3	341.4	340.1
30°	442.8	434.4	409.5	379.4	352.6	333.0	325.1	320.5	319.9
32.5°	408.8	401.6	378.7	351.3	325.7	309.4	303.5	300.2	299.6
35°	375.4	367.6	347.3	322.5	300.2	285.9	280.6	279.9	279.9
37.5°	341.4	333.5	317.3	294.4	275.4	262.3	260.4	260.9	260.9
40°	308.1	300.9	286.5	267.5	250.5	240.7	240.0	241.4	242.1
42.5°	276.6	270.8	257.8	241.4	227.0	219.2	219.7	222.4	224.4
45°	248.5	243.3	231.6	217.1	204.7	198.8	200.9	204.0	206.1
47.5°	223.0	218.5	207.3	194.3	183.8	179.9	182.5	186.4	189.0
50°	199.5	195.6	185.2	171.4	162.8	160.2	163.5	167.4	168.8
52.5°	178.6	174.7	163.5	151.8	145.2	144.0	147.1	150.4	152.4
55°	156.9	153.7	144.5	134.1	128.8	128.3	131.4	134.1	135.4
57.5°	139.3	136.1	127.6	118.4	113.8	113.1	116.4	118.4	119.0
60°	122.3	119.0	111.2	102.6	99.5	99.5	101.4	102.6	103.3
62.5°	106.6	103.3	96.2	89.0	86.4	86.4	86.4	86.9	89.0
65°	91.6	89.0	82.4	75.9	74.0	72.6	72.6	72.6	74.0
67.5°	77.8	75.2	70.0	64.1	62.1	60.2	59.5	60.9	60.9
70°	64.8	62.8	57.6	53.0	51.0	49.0	48.4	51.0	51.0
72.5°	53.0	51.0	47.8	43.1	41.2	40.5	41.9	43.1	43.8
75°	41.9	39.9	37.3	34.7	32.7	33.3	35.3	36.0	36.6
77.5°	31.4	30.7	28.1	26.2	26.2	26.9	28.1	29.5	30.0
80°	22.2	21.6	20.3	19.0	19.6	20.9	21.6	22.9	22.2
82.5°	13.8	13.8	13.1	13.1	13.8	15.0	15.7	16.4	17.0
85°	7.2	7.2	7.2	7.9	8.5	9.1	9.8	10.5	10.5
87.5°	1.9	2.6	2.6	3.3	3.9	3.9	4.6	4.6	4.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)