

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579733

Luminaire Tested: **HCC4S10D010SL-HM40525835-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S10D010SL-HM40525835-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1132.2 lumens
Efficiency: N/A
Efficacy: 114.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579733
CATALOG NUMBER: HCC4S10D010SL-HM40525835-41RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579733

CATALOG NUMBER: HCC4S10D010SL-HM40525835-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76					76			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67					67			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41					41			
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37					37			
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34					34			
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	67014	67014	67014
5°	69734	67629	66911
10°	72005	68235	66757
15°	74537	68445	66760
20°	74793	66786	65920
25°	72145	63448	63952
30°	67140	59079	60759
35°	60472	54057	56045
40°	53329	49174	51429
45°	46610	44307	46487
50°	41276	39875	41986
55°	36321	35225	36644
60°	32415	30072	30960
65°	28486	24458	24020
70°	24884	18032	16409
75°	20683	10866	8721
80°	15698	4191	2557
85°	7218	991	991



TEST NUMBER: P579733
 CATALOG NUMBER: HCC4S10D010SL-HM40525835-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.4	4.6
10°-20°	152.9	13.5
20°-30°	221.5	19.6
30°-40°	233.7	20.6
40°-50°	202.2	17.9
50°-60°	149.8	13.2
60°-70°	86.4	7.6
70°-80°	30.2	2.7
80°-90°	3.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	426.8	37.7
0°-40°	660.5	58.3
0°-60°	1012.5	89.4
0°-90°	1132.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1132.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	543	543	543	543	543	
5°	563	556	546	542	540	54
15°	584	565	536	524	523	164
25°	530	504	466	463	470	243
35°	402	383	359	367	372	251
45°	267	260	254	264	266	207
55°	169	165	164	170	170	152
65°	98	92	84	79	82	98
75°	43	37	23	18	18	47
85°	5	3	1	1	1	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579733

CATALOG NUMBER: HCC4S10D010SL-HM40525835-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	543.3	543.3	543.3	543.3	543.3	543.3	543.3	543.3	543.3
2.5°	551.4	549.9	547.7	544.8	541.8	539.6	539.0	538.2	538.2
5°	563.2	560.2	555.8	549.9	546.2	544.1	541.8	540.4	540.4
7.5°	571.3	568.3	561.7	553.6	548.5	544.1	541.1	539.0	539.0
10°	574.9	571.3	563.2	552.8	544.8	539.0	534.5	533.0	533.0
12.5°	579.2	574.9	563.9	550.7	540.4	533.0	528.6	527.1	527.1
15°	583.7	578.6	564.6	549.2	536.0	527.1	523.5	522.8	522.8
17.5°	581.5	574.9	558.8	540.4	525.6	516.9	513.2	513.2	513.9
20°	569.8	563.2	544.8	524.3	508.8	502.2	499.2	500.7	502.2
22.5°	552.2	544.1	524.3	504.4	488.2	482.4	482.4	484.6	486.8
25°	530.1	522.8	503.7	481.6	466.2	461.8	463.3	466.9	469.9
27.5°	505.2	497.1	477.3	456.7	441.3	439.0	442.7	447.9	449.4
30°	471.4	464.8	447.9	428.0	414.8	414.1	419.2	422.9	426.6
32.5°	439.0	431.8	415.6	396.5	386.9	387.7	393.5	398.0	400.1
35°	401.6	395.0	383.3	367.8	359.0	360.5	367.1	371.6	372.2
37.5°	366.3	362.0	350.3	338.4	331.8	334.8	340.7	345.8	345.8
40°	331.2	327.5	318.6	309.1	305.4	309.1	315.0	319.4	319.4
42.5°	297.4	295.2	287.8	281.2	279.0	284.2	289.3	292.9	292.2
45°	267.2	265.0	259.9	254.8	254.0	259.1	263.6	265.8	266.5
47.5°	240.1	238.6	234.2	230.6	230.6	235.7	239.3	241.6	242.3
50°	215.1	213.6	210.0	207.0	207.8	212.9	215.9	218.0	218.8
52.5°	190.2	189.5	186.5	182.9	185.0	188.7	192.3	193.8	194.6
55°	168.9	168.9	165.2	162.3	163.8	167.4	169.6	170.4	170.4
57.5°	149.8	149.1	144.6	141.7	142.5	146.1	147.6	148.3	148.3
60°	131.4	130.6	126.3	121.9	121.9	124.0	124.8	125.5	125.5
62.5°	113.8	113.1	107.9	104.2	102.8	102.1	102.1	103.6	106.5
65°	97.6	97.0	91.7	85.9	83.8	81.5	79.3	80.8	82.3
67.5°	83.0	81.5	76.4	71.2	66.1	62.4	58.7	61.0	63.8
70°	69.0	67.6	61.7	55.8	50.0	44.0	41.1	44.0	45.5
72.5°	55.8	54.3	48.5	42.6	35.3	29.4	28.7	29.4	30.2
75°	43.4	42.6	36.8	30.2	22.8	18.3	18.3	18.3	18.3
77.5°	32.3	30.8	24.9	19.1	13.2	10.2	9.6	9.6	9.6
80°	22.1	20.6	15.4	11.0	5.9	4.4	4.4	3.6	3.6
82.5°	12.5	11.7	8.1	4.4	2.2	1.5	1.5	1.5	1.5
85°	5.1	4.4	3.0	1.5	0.7	0.7	0.7	0.7	0.7
87.5°	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)