

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579773

Luminaire Tested: **HCC4W10D010MB-HM40525927-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579773
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010MB-HM40525927-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 845.4 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579773
CATALOG NUMBER: HCC4W10D010MB-HM40525927-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579773

CATALOG NUMBER: HCC4W10D010MB-HM40525927-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	53779	53779	53779
5°	56547	53699	51681
10°	58529	53068	49348
15°	60311	52100	47248
20°	60380	49945	44511
25°	58113	46681	41741
30°	53951	42970	38982
35°	48380	38668	36063
40°	42444	34506	33330
45°	37103	30544	30753
50°	32756	26731	27709
55°	28881	23720	24902
60°	25829	20969	21808
65°	22853	18475	18475
70°	19979	15760	15760
75°	17061	13344	14917
80°	13496	11933	13496
85°	8633	10331	12737



TEST NUMBER: P579773
 CATALOG NUMBER: HCC4W10D010MB-HM40525927-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.3	4.9
10°-20°	116.3	13.8
20°-30°	163.0	19.3
30°-40°	167.9	19.9
40°-50°	142.9	16.9
50°-60°	105.9	12.5
60°-70°	66.5	7.9
70°-80°	33.0	3.9
80°-90°	8.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	320.6	37.9
0°-40°	488.5	57.8
0°-60°	737.3	87.2
0°-90°	845.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	845.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	436	436	436	436	436	
5°	457	449	434	421	417	44
15°	472	451	408	378	370	133
25°	427	397	343	313	307	195
35°	321	297	257	240	240	200
45°	213	198	175	172	176	165
55°	134	124	110	112	116	121
65°	78	71	63	62	63	78
75°	36	32	28	30	31	38
85°	6	6	7	8	9	8
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579773

CATALOG NUMBER: HCC4W10D010MB-HM40525927-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	436.0	436.0	436.0	436.0	436.0	436.0	436.0	436.0	436.0
2.5°	445.4	443.8	441.5	437.7	433.7	430.4	427.0	425.3	424.7
5°	456.7	453.3	448.8	441.5	433.7	427.0	421.4	418.6	417.4
7.5°	464.5	461.1	453.8	442.7	431.4	421.4	412.4	408.5	407.4
10°	467.3	463.4	453.3	438.1	423.7	411.3	401.3	396.3	394.0
12.5°	469.5	464.5	451.6	433.7	415.8	400.7	390.1	383.4	381.7
15°	472.3	466.7	451.1	429.3	408.0	390.1	378.3	372.1	370.0
17.5°	469.5	463.4	444.8	420.3	396.3	376.7	363.7	358.1	356.0
20°	460.0	453.3	432.6	406.3	380.5	360.4	347.5	342.0	339.1
22.5°	445.4	438.1	417.0	389.0	362.7	343.0	330.7	325.1	323.4
25°	427.0	419.7	397.3	368.8	343.0	324.0	313.4	308.4	306.7
27.5°	405.1	397.8	376.1	348.1	323.4	305.6	297.1	292.1	291.0
30°	378.8	371.6	350.3	324.6	301.7	284.8	278.1	274.3	273.7
32.5°	349.7	343.6	324.0	300.5	278.7	264.7	259.7	256.8	256.3
35°	321.3	314.5	297.1	275.9	256.8	244.6	240.1	239.5	239.5
37.5°	292.1	285.4	271.4	251.8	235.6	224.4	222.7	223.3	223.3
40°	263.6	257.4	245.1	228.9	214.3	206.0	205.4	206.5	207.0
42.5°	236.7	231.7	220.5	206.5	194.1	187.4	188.0	190.3	192.0
45°	212.7	208.1	198.1	185.8	175.1	170.1	171.8	174.6	176.3
47.5°	190.8	186.9	177.4	166.3	157.3	153.9	156.1	159.5	161.7
50°	170.7	167.3	158.4	146.6	139.3	137.1	139.9	143.3	144.4
52.5°	152.7	149.4	139.9	129.8	124.3	123.1	125.9	128.7	130.4
55°	134.3	131.6	123.7	114.7	110.3	109.7	112.4	114.7	115.8
57.5°	119.1	116.4	109.1	101.3	97.4	96.8	99.6	101.3	101.9
60°	104.7	101.9	95.1	87.9	85.0	85.0	86.7	87.9	88.4
62.5°	91.3	88.4	82.3	76.1	73.9	73.9	73.9	74.4	76.1
65°	78.3	76.1	70.6	64.9	63.3	62.1	62.1	62.1	63.3
67.5°	66.6	64.4	59.9	54.9	53.1	51.4	50.9	52.0	52.0
70°	55.4	53.7	49.3	45.3	43.7	42.0	41.4	43.7	43.7
72.5°	45.3	43.7	40.9	37.0	35.3	34.7	35.8	37.0	37.4
75°	35.8	34.1	31.9	29.7	28.0	28.6	30.3	30.7	31.3
77.5°	26.9	26.3	24.0	22.4	22.4	23.0	24.0	25.1	25.7
80°	19.0	18.4	17.3	16.3	16.8	17.9	18.4	19.6	19.0
82.5°	11.7	11.7	11.2	11.2	11.7	12.9	13.4	14.0	14.6
85°	6.1	6.1	6.1	6.7	7.3	7.9	8.4	9.0	9.0
87.5°	1.7	2.3	2.3	2.8	3.4	3.4	3.9	3.9	3.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)