

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579789

Luminaire Tested: **HCC4S10D010SL-HM40525930-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579789
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S10D010SL-HM40525930-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 755.8 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579789
CATALOG NUMBER: HCC4S10D010SL-HM40525930-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579789

CATALOG NUMBER: HCC4S10D010SL-HM40525930-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	53976	53976	53976
5°	57179	53786	51087
10°	59556	52917	48095
15°	61831	51666	45217
20°	62415	49171	41820
25°	60386	45484	38284
30°	56472	41218	34838
35°	50323	36635	31305
40°	43990	31865	27856
45°	38324	27038	24107
50°	33428	22931	20667
55°	29311	19010	16731
60°	25631	15344	12285
65°	22357	11470	6917
70°	19547	7393	2272
75°	16013	3860	620
80°	11933	1776	426
85°	7076	849	849



TEST NUMBER: P579789
 CATALOG NUMBER: HCC4S10D010SL-HM40525930-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.3	5.5
10°-20°	115.6	15.3
20°-30°	159.8	21.1
30°-40°	160.7	21.3
40°-50°	129.7	17.2
50°-60°	87.7	11.6
60°-70°	44.6	5.9
70°-80°	14.3	1.9
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.6	41.9
0°-40°	477.3	63.2
0°-60°	694.6	91.9
0°-90°	755.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	755.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	438	438	438	438	438	
5°	462	453	434	419	413	45
15°	484	458	405	366	354	136
25°	444	405	334	293	281	203
35°	334	302	243	213	208	209
45°	220	197	155	138	138	170
55°	136	118	88	77	78	122
65°	77	62	39	26	24	77
75°	34	24	8	2	1	36
85°	5	2	1	1	1	7
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579789

CATALOG NUMBER: HCC4S10D010SL-HM40525930-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	437.6	437.6	437.6	437.6	437.6	437.6	437.6	437.6	437.6
2.5°	449.4	446.9	444.4	440.0	435.1	430.1	427.0	424.5	423.2
5°	461.8	458.7	453.0	443.7	434.4	425.7	418.9	414.5	412.6
7.5°	471.7	467.4	458.0	445.0	430.6	417.0	408.3	402.1	399.6
10°	475.5	470.4	458.0	440.6	422.5	405.8	393.3	387.1	384.0
12.5°	479.8	474.2	458.7	436.9	414.5	394.5	380.2	372.1	369.1
15°	484.2	476.7	458.0	431.3	404.6	381.5	366.0	357.9	354.1
17.5°	484.2	475.5	453.0	422.0	391.5	367.2	349.7	340.4	337.3
20°	475.5	465.6	441.2	407.1	374.6	348.6	331.7	322.4	318.6
22.5°	461.8	450.5	424.5	389.0	354.7	329.2	312.4	303.7	300.0
25°	443.7	432.6	405.1	368.5	334.2	308.7	293.1	285.1	281.3
27.5°	422.5	410.1	382.7	346.1	312.4	288.1	273.8	266.4	263.2
30°	396.5	384.6	357.9	321.7	289.4	267.0	253.9	247.1	244.6
32.5°	366.0	356.0	329.8	296.2	265.7	245.2	233.4	227.8	225.3
35°	334.2	324.9	301.8	270.7	243.3	224.1	212.8	209.2	207.9
37.5°	304.3	296.2	273.8	245.2	220.3	203.5	193.6	191.1	189.8
40°	273.2	267.7	247.1	220.9	197.9	183.0	174.9	173.0	173.0
42.5°	245.2	239.0	220.9	197.3	176.7	161.8	156.2	154.3	155.0
45°	219.7	213.5	196.6	174.9	155.0	142.5	138.2	138.2	138.2
47.5°	196.1	190.4	174.9	152.5	136.3	126.3	122.0	122.0	122.6
50°	174.2	170.5	153.1	133.8	119.5	110.2	107.1	106.4	107.7
52.5°	153.7	149.4	133.8	116.4	102.6	95.3	92.1	91.5	92.1
55°	136.3	131.3	117.7	100.8	88.4	80.9	77.2	76.6	77.8
57.5°	119.5	115.7	101.4	86.5	74.7	67.3	64.1	62.8	63.5
60°	103.9	100.1	87.2	72.8	62.2	54.7	50.4	49.2	49.8
62.5°	89.7	86.5	74.1	60.3	49.8	42.9	38.6	35.5	36.8
65°	76.6	73.4	62.2	48.6	39.3	31.8	25.5	23.0	23.7
67.5°	65.3	61.6	51.0	38.6	29.2	21.2	14.3	13.1	13.1
70°	54.2	50.4	41.1	29.9	20.5	11.2	6.3	6.3	6.3
72.5°	43.6	40.4	31.8	22.4	13.1	5.0	2.5	2.5	2.5
75°	33.6	31.1	23.7	15.6	8.1	2.5	1.8	1.3	1.3
77.5°	24.9	22.4	16.8	10.6	5.0	1.3	1.3	1.3	1.3
80°	16.8	14.9	11.2	6.3	2.5	0.6	0.6	0.6	0.6
82.5°	10.0	8.8	6.3	3.1	1.3	0.6	0.6	0.6	0.6
85°	5.0	3.8	2.5	1.3	0.6	0.6	0.6	0.6	0.6
87.5°	1.3	0.6	0.6	0.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)