

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579825

Luminaire Tested: **HCC4S10D010MW-HM40525940-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579825  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S10D010MW-HM40525940-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 824.9 lumens  
Efficiency: N/A  
Efficacy: 83.3 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579825  
CATALOG NUMBER: HCC4S10D010MW-HM40525940-41WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579825

CATALOG NUMBER: HCC4S10D010MW-HM40525940-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	58898	58898	58898
5°	62404	58702	55767
10°	64991	57765	52492
15°	67488	56378	49355
20°	68112	53673	45653
25°	65912	49635	41782
30°	61628	44993	38028
35°	54916	39993	34166
40°	48015	34780	30400
45°	41830	29497	26305
50°	36498	25023	22566
55°	31977	20752	18257
60°	27999	16750	13420
65°	24370	12492	7530
70°	21314	8078	2452
75°	17442	4241	667
80°	12999	1918	497
85°	7784	991	991



TEST NUMBER: P579825  
 CATALOG NUMBER: HCC4S10D010MW-HM40525940-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.1	5.5
10°-20°	126.1	15.3
20°-30°	174.4	21.1
30°-40°	175.4	21.3
40°-50°	141.5	17.2
50°-60°	95.7	11.6
60°-70°	48.7	5.9
70°-80°	15.6	1.9
80°-90°	2.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	345.6	41.9
0°-40°	521.0	63.2
0°-60°	758.2	91.9
0°-90°	824.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	824.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	478	478	478	478	478	
5°	504	495	474	457	450	49
15°	528	500	442	399	386	149
25°	484	442	365	320	307	222
35°	365	330	266	232	227	228
45°	240	215	169	151	151	186
55°	149	128	96	84	85	134
65°	84	68	43	28	26	84
75°	37	26	9	2	1	40
85°	6	3	1	1	1	7
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579825

CATALOG NUMBER: HCC4S10D010MW-HM40525940-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	477.5	477.5	477.5	477.5	477.5	477.5	477.5	477.5	477.5
2.5°	490.5	487.7	485.0	480.2	474.8	469.4	466.0	463.3	461.9
5°	504.0	500.6	494.6	484.3	474.1	464.6	457.1	452.4	450.4
7.5°	514.9	510.2	499.9	485.7	470.1	455.1	445.6	438.8	436.1
10°	518.9	513.6	499.9	480.9	461.2	442.9	429.3	422.5	419.1
12.5°	523.7	517.6	500.6	476.8	452.4	430.6	415.0	406.3	402.9
15°	528.5	520.3	499.9	470.8	441.5	416.4	399.4	390.6	386.5
17.5°	528.5	518.9	494.6	460.5	427.3	400.8	381.8	371.6	368.1
20°	518.9	508.1	481.6	444.3	408.9	380.4	362.1	351.9	347.8
22.5°	504.0	491.8	463.3	424.6	387.1	359.4	340.9	331.5	327.4
25°	484.3	472.2	442.2	402.2	364.7	337.0	319.9	311.1	307.0
27.5°	461.2	447.7	417.8	377.7	340.9	314.5	298.8	290.8	287.3
30°	432.7	419.8	390.6	351.2	315.9	291.4	277.1	269.7	267.0
32.5°	399.4	388.5	360.1	323.3	290.1	267.7	254.7	248.7	245.9
35°	364.7	354.6	329.5	295.5	265.6	244.6	232.3	228.3	226.9
37.5°	332.2	323.3	298.8	267.7	240.5	222.1	211.2	208.6	207.2
40°	298.2	292.1	269.7	241.1	216.0	199.7	190.8	188.8	188.8
42.5°	267.7	260.8	241.1	215.3	192.9	176.6	170.5	168.4	169.1
45°	239.8	232.9	214.6	190.8	169.1	155.6	150.8	150.8	150.8
47.5°	213.9	207.9	190.8	166.4	148.7	137.9	133.1	133.1	133.8
50°	190.2	186.2	167.1	146.0	130.4	120.3	116.9	116.2	117.6
52.5°	167.7	163.1	146.0	127.0	112.1	103.9	100.5	99.8	100.5
55°	148.7	143.3	128.4	110.0	96.5	88.3	84.2	83.5	84.9
57.5°	130.4	126.3	110.7	94.5	81.5	73.4	70.0	68.6	69.3
60°	113.5	109.4	95.1	79.4	67.9	59.7	55.0	53.7	54.4
62.5°	97.9	94.5	80.8	65.9	54.4	46.9	42.1	38.7	40.1
65°	83.5	80.1	67.9	53.0	42.8	34.6	27.9	25.1	25.8
67.5°	71.4	67.3	55.6	42.1	32.0	23.1	15.6	14.2	14.2
70°	59.1	55.0	44.8	32.7	22.4	12.2	6.8	6.8	6.8
72.5°	47.6	44.2	34.6	24.5	14.2	5.5	2.7	2.7	2.7
75°	36.6	33.9	25.8	17.0	8.9	2.7	2.0	1.4	1.4
77.5°	27.2	24.5	18.3	11.5	5.5	1.4	1.4	1.4	1.4
80°	18.3	16.3	12.2	6.8	2.7	0.7	0.7	0.7	0.7
82.5°	10.9	9.6	6.8	3.4	1.4	0.7	0.7	0.7	0.7
85°	5.5	4.1	2.7	1.4	0.7	0.7	0.7	0.7	0.7
87.5°	1.4	0.7	0.7	0.7	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)