

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579827

Luminaire Tested: **HCC4W10D010MW-HM40525940-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579827
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W10D010MW-HM40525940-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1026.6 lumens
Efficiency: N/A
Efficacy: 103.7 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579827

CATALOG NUMBER: HCC4W10D010MW-HM40525940-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579827

CATALOG NUMBER: HCC4W10D010MW-HM40525940-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	65299	65299	65299
5°	68656	65214	62775
10°	71066	64428	59919
15°	73247	63261	57361
20°	73323	60656	54054
25°	70566	56698	50682
30°	65531	52171	47329
35°	58740	46965	43803
40°	51541	41913	40479
45°	45040	37103	37347
50°	39760	32468	33658
55°	35074	28773	30257
60°	31354	25483	26495
65°	27756	22415	22415
70°	24271	19114	19114
75°	20731	16203	18110
80°	16408	14491	16408
85°	10614	12596	15426



TEST NUMBER: P579827

CATALOG NUMBER: HCC4W10D010MW-HM40525940-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.2	4.9
10°-20°	141.2	13.8
20°-30°	197.9	19.3
30°-40°	203.9	19.9
40°-50°	173.6	16.9
50°-60°	128.6	12.5
60°-70°	80.7	7.9
70°-80°	40.1	3.9
80°-90°	10.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	389.3	37.9
0°-40°	593.2	57.8
0°-60°	895.3	87.2
0°-90°	1026.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1026.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	529	529	529	529	529	
5°	554	545	527	512	507	53
15°	574	548	495	459	449	161
25°	518	482	417	380	372	237
35°	390	361	312	292	291	243
45°	258	241	213	209	214	200
55°	163	150	134	137	141	147
65°	95	86	77	75	77	95
75°	44	39	34	37	38	47
85°	8	8	9	10	11	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579827

CATALOG NUMBER: HCC4W10D010MW-HM40525940-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	529.4	529.4	529.4	529.4	529.4	529.4	529.4	529.4	529.4
2.5°	540.9	538.8	536.2	531.4	526.7	522.6	518.5	516.4	515.7
5°	554.5	550.5	545.0	536.2	526.7	518.5	511.8	508.3	507.0
7.5°	564.0	560.0	551.1	537.6	523.9	511.8	500.8	496.1	494.7
10°	567.4	562.6	550.5	532.1	514.4	499.5	487.3	481.1	478.4
12.5°	570.1	564.0	548.4	526.7	504.9	486.6	473.6	465.6	463.5
15°	573.6	566.7	547.7	521.2	495.4	473.6	459.4	451.9	449.2
17.5°	570.1	562.6	540.2	510.4	481.1	457.4	441.8	434.9	432.2
20°	558.6	550.5	525.3	493.3	462.1	437.7	422.0	415.3	411.8
22.5°	540.9	532.1	506.3	472.3	440.4	416.6	401.6	394.8	392.8
25°	518.5	509.7	482.5	447.8	416.6	393.5	380.5	374.4	372.4
27.5°	492.0	483.2	456.7	422.7	392.8	371.0	360.9	354.7	353.3
30°	460.1	451.2	425.4	394.2	366.3	346.0	337.8	333.0	332.3
32.5°	424.7	417.3	393.5	365.0	338.4	321.5	315.3	311.9	311.2
35°	390.1	381.9	360.9	335.0	311.9	297.0	291.6	290.9	290.9
37.5°	354.7	346.6	329.6	305.8	286.1	272.6	270.5	271.2	271.2
40°	320.1	312.6	297.7	277.9	260.3	250.1	249.4	250.8	251.4
42.5°	287.5	281.3	267.8	250.8	235.8	227.6	228.3	231.0	233.1
45°	258.2	252.7	240.6	225.7	212.7	206.5	208.6	212.0	214.1
47.5°	231.7	227.0	215.4	201.9	191.0	186.9	189.6	193.7	196.4
50°	207.2	203.2	192.3	178.1	169.2	166.5	169.9	174.0	175.4
52.5°	185.5	181.4	169.9	157.6	150.9	149.5	152.9	156.2	158.3
55°	163.1	159.7	150.2	139.3	133.8	133.1	136.6	139.3	140.7
57.5°	144.8	141.3	132.5	123.0	118.2	117.6	121.0	123.0	123.7
60°	127.1	123.7	115.5	106.7	103.3	103.3	105.4	106.7	107.4
62.5°	110.7	107.4	99.9	92.4	89.7	89.7	89.7	90.4	92.4
65°	95.1	92.4	85.6	78.9	76.8	75.4	75.4	75.4	76.8
67.5°	80.9	78.2	72.7	66.6	64.5	62.5	61.8	63.2	63.2
70°	67.3	65.2	59.7	55.1	53.0	51.0	50.3	53.0	53.0
72.5°	55.1	53.0	49.6	44.8	42.8	42.1	43.5	44.8	45.5
75°	43.5	41.4	38.7	36.0	34.0	34.7	36.6	37.3	38.0
77.5°	32.7	32.0	29.2	27.2	27.2	27.9	29.2	30.6	31.3
80°	23.1	22.4	21.1	19.7	20.4	21.7	22.4	23.8	23.1
82.5°	14.2	14.2	13.5	13.5	14.2	15.6	16.3	17.0	17.6
85°	7.5	7.5	7.5	8.2	8.9	9.6	10.2	10.9	10.9
87.5°	2.0	2.7	2.7	3.4	4.1	4.1	4.8	4.8	4.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)