

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579841

Luminaire Tested: **HCC4W15D010MW-HM40525827-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579841
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010MW-HM40525827-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1371.1 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579841
CATALOG NUMBER: HCC4W15D010MW-HM40525827-41RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579841

CATALOG NUMBER: HCC4W15D010MW-HM40525827-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76					76			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67					67			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58					58			
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52					52			
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46					46			
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41					41			
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37					37			
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34					34			
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31					31			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	81161	81161	81161
5°	84443	81905	81038
10°	87198	82639	80860
15°	90269	82888	80845
20°	90571	80870	79833
25°	87374	76840	77453
30°	81312	71541	73592
35°	73241	65471	67880
40°	64568	59560	62281
45°	56465	53674	56308
50°	49988	48280	50832
55°	43977	42644	44364
60°	39273	36412	37497
65°	34498	29595	29069
70°	30149	21819	19871
75°	24972	13106	10628
80°	18966	5114	3125
85°	8916	1274	1274



TEST NUMBER: P579841
 CATALOG NUMBER: HCC4W15D010MW-HM40525827-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.5	4.6
10°-20°	185.2	13.5
20°-30°	268.2	19.6
30°-40°	283.0	20.6
40°-50°	244.9	17.9
50°-60°	181.4	13.2
60°-70°	104.6	7.6
70°-80°	36.5	2.7
80°-90°	3.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	516.9	37.7
0°-40°	799.9	58.3
0°-60°	1226.2	89.4
0°-90°	1371.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1371.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	658	658	658	658	658	
5°	682	673	662	656	654	66
15°	707	684	649	634	633	199
25°	642	610	565	561	569	294
35°	486	464	435	445	451	304
45°	324	315	308	319	323	251
55°	204	200	198	205	206	184
65°	118	111	101	96	100	118
75°	52	44	28	22	22	56
85°	6	4	1	1	1	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579841

CATALOG NUMBER: HCC4W15D010MW-HM40525827-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	658.0	658.0	658.0	658.0	658.0	658.0	658.0	658.0	658.0
2.5°	667.8	665.9	663.3	659.8	656.2	653.5	652.6	651.7	651.7
5°	682.0	678.4	673.1	665.9	661.5	658.9	656.2	654.5	654.5
7.5°	691.8	688.2	680.3	670.5	664.2	658.9	655.4	652.6	652.6
10°	696.2	691.8	682.0	669.6	659.8	652.6	647.3	645.6	645.6
12.5°	701.5	696.2	682.9	666.9	654.5	645.6	640.2	638.4	638.4
15°	706.9	700.6	683.8	665.1	649.1	638.4	634.0	633.1	633.1
17.5°	704.3	696.2	676.6	654.5	636.6	626.0	621.5	621.5	622.4
20°	690.0	682.0	659.8	634.9	616.1	608.2	604.7	606.4	608.2
22.5°	668.7	658.9	634.9	610.9	591.4	584.2	584.2	586.8	589.5
25°	642.0	633.1	610.0	583.3	564.6	559.3	561.1	565.5	569.1
27.5°	611.7	601.9	577.9	553.0	534.4	531.8	536.2	542.3	544.2
30°	570.9	562.8	542.3	518.4	502.3	501.5	507.7	512.2	516.7
32.5°	531.8	522.8	503.2	480.2	468.6	469.5	476.6	482.0	484.6
35°	486.4	478.3	464.1	445.5	434.8	436.6	444.6	449.9	450.8
37.5°	443.7	438.3	424.1	409.9	401.9	405.5	412.6	418.8	418.8
40°	401.0	396.6	385.9	374.3	369.9	374.3	381.5	386.8	386.8
42.5°	360.1	357.5	348.6	340.5	337.9	344.1	350.3	354.7	353.8
45°	323.7	321.0	314.7	308.6	307.7	313.9	319.2	321.9	322.8
47.5°	290.7	289.0	283.7	279.2	279.2	285.4	289.8	292.6	293.5
50°	260.5	258.8	254.3	250.7	251.6	257.9	261.4	264.1	264.9
52.5°	230.2	229.4	225.8	221.4	224.1	228.5	233.0	234.8	235.6
55°	204.5	204.5	200.1	196.5	198.3	202.7	205.3	206.3	206.3
57.5°	181.4	180.6	175.2	171.6	172.5	176.9	178.7	179.6	179.6
60°	159.2	158.3	152.9	147.6	147.6	150.3	151.1	152.0	152.0
62.5°	137.8	136.9	130.8	126.2	124.5	123.6	123.6	125.4	128.9
65°	118.2	117.3	111.2	104.0	101.4	98.7	96.1	97.8	99.6
67.5°	100.5	98.7	92.4	86.3	80.0	75.6	71.2	73.8	77.3
70°	83.6	81.8	74.7	67.5	60.5	53.3	49.8	53.3	55.1
72.5°	67.5	65.8	58.7	51.6	42.6	35.6	34.7	35.6	36.5
75°	52.4	51.6	44.5	36.5	27.5	22.3	22.3	22.3	22.3
77.5°	39.1	37.3	30.2	23.1	16.0	12.4	11.6	11.6	11.6
80°	26.7	24.9	18.6	13.3	7.2	5.3	5.3	4.4	4.4
82.5°	15.1	14.2	9.8	5.3	2.6	1.8	1.8	1.8	1.8
85°	6.3	5.3	3.5	1.8	0.9	0.9	0.9	0.9	0.9
87.5°	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)