

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579861

Luminaire Tested: **HCC4S15D010MW-HM40525830-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579861  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S15D010MW-HM40525830-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1169.2 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579861  
CATALOG NUMBER: HCC4S15D010MW-HM40525830-41WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P579861

CATALOG NUMBER: HCC4S15D010MW-HM40525830-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20				
RC	80					70					50					30				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89		
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78		
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69		
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61		
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55		
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49		
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44		
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40		
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37		
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	83493	83493	83493
5°	88467	83217	79045
10°	92133	81887	74410
15°	95658	79925	69965
20°	96556	76079	64712
25°	93430	70376	59229
30°	87351	63779	53894
35°	77863	56692	48411
40°	68062	49303	43088
45°	59274	41830	37295
50°	51734	35481	31969
55°	45353	29418	25892
60°	39668	23756	18995
65°	34585	17716	10682
70°	30222	11432	3498
75°	24782	5957	905
80°	18468	2770	639
85°	10897	1274	1274



TEST NUMBER: P579861  
 CATALOG NUMBER: HCC4S15D010MW-HM40525830-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.9	5.5
10°-20°	178.8	15.3
20°-30°	247.2	21.1
30°-40°	248.6	21.3
40°-50°	200.6	17.2
50°-60°	135.6	11.6
60°-70°	69.0	5.9
70°-80°	22.1	1.9
80°-90°	3.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.9	41.9
0°-40°	738.5	63.2
0°-60°	1074.7	91.9
0°-90°	1169.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1169.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	677	677	677	677	677	
5°	714	701	672	648	638	69
15°	749	709	626	566	548	211
25°	686	627	517	454	435	314
35°	517	467	376	329	322	323
45°	340	304	240	214	214	263
55°	211	182	137	119	120	189
65°	118	96	61	40	37	119
75°	52	37	12	3	2	56
85°	8	4	1	1	1	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579861

CATALOG NUMBER: HCC4S15D010MW-HM40525830-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	676.9	676.9	676.9	676.9	676.9	676.9	676.9	676.9	676.9
2.5°	695.2	691.3	687.5	680.7	673.0	665.4	660.5	656.7	654.8
5°	714.5	709.6	701.0	686.5	672.1	658.6	648.0	641.3	638.4
7.5°	729.8	723.1	708.7	688.5	666.3	645.1	631.6	622.1	618.2
10°	735.6	727.9	708.7	681.7	653.8	627.7	608.5	598.9	594.1
12.5°	742.3	733.7	709.6	675.9	641.3	610.5	588.3	575.8	571.0
15°	749.1	737.6	708.7	667.3	625.9	590.2	566.1	553.6	547.9
17.5°	749.1	735.6	701.0	652.9	605.7	568.0	541.1	526.7	521.9
20°	735.6	720.2	682.7	629.7	579.6	539.2	513.2	498.8	493.0
22.5°	714.5	697.1	656.7	601.8	548.8	509.4	483.3	469.9	464.1
25°	686.5	669.2	626.8	570.0	517.1	477.5	453.5	441.0	435.2
27.5°	653.8	634.6	592.1	535.3	483.3	445.8	423.6	412.2	407.3
30°	613.3	595.1	553.6	497.8	447.8	413.1	392.8	382.3	378.4
32.5°	566.1	550.8	510.3	458.3	411.1	379.4	361.1	352.4	348.6
35°	517.1	502.7	467.0	418.9	376.5	346.7	329.3	323.5	321.5
37.5°	470.8	458.3	423.6	379.4	340.9	314.8	299.5	295.6	293.7
40°	422.7	414.0	382.3	341.8	306.2	283.1	270.6	267.6	267.6
42.5°	379.4	369.8	341.8	305.3	273.4	250.4	241.7	238.8	239.8
45°	339.8	330.3	304.3	270.6	239.8	220.5	213.8	213.8	213.8
47.5°	303.4	294.6	270.6	235.9	210.9	195.5	188.7	188.7	189.7
50°	269.6	263.8	236.8	207.0	184.9	170.4	165.7	164.6	166.6
52.5°	237.9	231.0	207.0	180.1	158.8	147.4	142.5	141.6	142.5
55°	210.9	203.2	182.0	156.0	136.8	125.2	119.4	118.5	120.4
57.5°	184.9	179.1	156.9	133.8	115.5	104.0	99.1	97.2	98.2
60°	160.8	155.0	134.8	112.7	96.3	84.7	78.0	76.1	77.0
62.5°	138.6	133.8	114.6	93.3	77.0	66.4	59.7	54.9	56.8
65°	118.5	113.6	96.3	75.2	60.7	49.1	39.5	35.6	36.6
67.5°	101.1	95.3	78.9	59.7	45.3	32.7	22.2	20.2	20.2
70°	83.8	78.0	63.6	46.2	31.7	17.3	9.7	9.7	9.7
72.5°	67.4	62.5	49.1	34.7	20.2	7.7	3.9	3.9	3.9
75°	52.0	48.1	36.6	24.1	12.5	3.9	2.8	1.9	1.9
77.5°	38.5	34.7	26.0	16.4	7.7	1.9	1.9	1.9	1.9
80°	26.0	23.1	17.3	9.7	3.9	0.9	0.9	0.9	0.9
82.5°	15.3	13.5	9.7	4.8	1.9	0.9	0.9	0.9	0.9
85°	7.7	5.8	3.9	1.9	0.9	0.9	0.9	0.9	0.9
87.5°	1.9	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)