

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579916

Luminaire Tested: **HCC4W15D010MW-HM40525927-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579916
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010MW-HM40525927-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1154.8 lumens
Efficiency: N/A
Efficacy: 82.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579916
CATALOG NUMBER: HCC4W15D010MW-HM40525927-41WWW

Luminous Intensity Polar Plot





TEST NUMBER: P579916

CATALOG NUMBER: HCC4W15D010MW-HM40525927-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87																			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76																			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66																			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58																			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47																			
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35																			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	79755	79755	79755
5°	83267	79416	75739
10°	85369	77754	70991
15°	87140	75673	65879
20°	86685	71997	60315
25°	83033	66565	54874
30°	76711	60788	49736
35°	67248	54072	45023
40°	58546	47790	40544
45°	50953	41673	36231
50°	45402	35922	31969
55°	40558	31569	27655
60°	36214	27605	23830
65°	32192	24195	22619
70°	28238	20881	21133
75°	23972	17776	19539
80°	18326	15130	17829
85°	10756	11888	15143



TEST NUMBER: P579916
 CATALOG NUMBER: HCC4W15D010MW-HM40525927-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	5.2
10°-20°	167.2	14.5
20°-30°	228.4	19.8
30°-40°	229.4	19.9
40°-50°	189.8	16.4
50°-60°	137.5	11.9
60°-70°	87.1	7.5
70°-80°	44.0	3.8
80°-90°	10.8	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.2	39.5
0°-40°	685.6	59.4
0°-60°	1012.9	87.7
0°-90°	1154.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1154.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	647	647	647	647	647	
5°	672	663	641	620	612	64
15°	682	656	593	538	516	192
25°	610	570	489	428	403	279
35°	447	420	359	315	299	280
45°	292	275	239	215	208	227
55°	189	172	147	134	129	170
65°	110	98	83	75	78	110
75°	50	43	37	39	41	54
85°	8	8	8	10	11	11
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579916

CATALOG NUMBER: HCC4W15D010MW-HM40525927-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	646.6	646.6	646.6	646.6	646.6	646.6	646.6	646.6	646.6
2.5°	658.9	656.5	652.8	648.2	642.9	636.7	631.5	628.4	626.9
5°	672.5	669.5	662.6	652.8	641.4	629.9	620.0	614.0	611.7
7.5°	680.9	676.3	666.4	651.3	633.8	617.0	602.5	594.2	591.9
10°	681.6	676.3	663.4	642.9	620.8	598.7	581.2	569.1	566.8
12.5°	682.4	675.6	659.6	635.2	607.8	580.4	559.2	544.7	540.9
15°	682.4	675.6	655.8	626.9	592.6	561.5	537.9	521.1	515.9
17.5°	676.3	668.8	645.1	611.7	574.4	539.4	512.0	494.5	489.1
20°	660.4	652.0	625.4	588.9	548.5	512.0	484.6	466.4	459.5
22.5°	637.5	627.6	599.5	560.0	519.6	482.3	455.7	436.7	430.6
25°	610.1	600.2	569.9	531.0	489.1	454.2	427.5	410.1	403.2
27.5°	576.7	566.0	536.3	497.6	458.8	423.8	399.4	383.4	376.6
30°	538.6	527.2	499.0	461.8	426.8	393.3	369.8	356.8	349.2
32.5°	494.5	484.6	459.5	426.0	393.3	361.3	341.6	330.2	324.0
35°	446.6	441.3	420.0	391.0	359.1	332.5	314.9	304.3	299.0
37.5°	404.0	398.6	380.4	356.0	327.9	303.6	289.1	279.9	275.4
40°	363.6	359.1	341.6	321.1	296.8	275.4	263.2	256.4	251.8
42.5°	324.0	321.8	307.3	288.3	267.1	248.8	238.9	233.5	229.8
45°	292.1	289.1	275.4	257.2	238.9	223.6	215.3	211.5	207.7
47.5°	264.0	260.1	245.7	229.8	213.1	199.3	191.7	187.9	186.4
50°	236.6	232.7	219.9	203.9	187.2	177.3	171.2	167.4	166.6
52.5°	212.3	208.4	194.0	178.7	165.9	157.5	152.1	148.4	146.8
55°	188.6	184.1	171.9	157.5	146.8	139.2	133.9	130.1	128.6
57.5°	167.4	162.8	152.1	138.5	128.6	121.8	117.1	113.4	111.9
60°	146.8	143.0	133.1	120.2	111.9	105.7	101.2	98.1	96.6
62.5°	127.8	124.7	114.8	103.5	96.6	91.3	87.4	84.5	86.0
65°	110.3	107.2	98.1	88.2	82.9	77.5	74.6	74.6	77.5
67.5°	93.6	90.5	82.9	74.6	70.0	66.2	63.9	66.2	68.4
70°	78.3	75.3	68.4	61.6	57.9	54.8	54.8	57.1	58.6
72.5°	63.9	60.8	55.5	50.3	47.2	44.9	47.2	48.7	50.3
75°	50.3	48.0	43.3	39.6	37.3	36.5	38.8	40.4	41.0
77.5°	37.3	35.7	32.7	29.7	28.2	28.9	31.2	31.9	32.7
80°	25.8	25.1	22.9	21.3	21.3	22.1	23.5	24.3	25.1
82.5°	16.0	16.0	14.4	13.6	14.4	16.0	16.7	17.5	17.5
85°	7.6	8.4	7.6	7.6	8.4	9.9	9.9	10.7	10.7
87.5°	2.3	2.3	3.1	3.1	3.8	3.8	3.8	3.8	4.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)