

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579932

Luminaire Tested: **HCC4W15D010SL-HM40525930-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010SL-HM40525930-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1298.4 lumens
Efficiency: N/A
Efficacy: 92.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579932
CATALOG NUMBER: HCC4W15D010SL-HM40525930-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579932

CATALOG NUMBER: HCC4W15D010SL-HM40525930-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	84023	84023	84023
5°	86226	84034	82450
10°	88175	83303	80021
15°	90652	82122	77908
20°	90413	78967	74754
25°	86612	73941	71165
30°	79660	68094	67368
35°	70079	61812	62309
40°	60639	55325	57628
45°	52697	49139	52104
50°	46764	43348	46284
55°	41482	38020	39655
60°	36930	32983	32983
65°	32864	27406	25684
70°	28382	20737	18320
75°	23781	13725	11247
80°	18042	6606	5967
85°	9624	2406	2406



TEST NUMBER: P579932

CATALOG NUMBER: HCC4W15D010SL-HM40525930-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.5	5.0
10°-20°	182.9	14.1
20°-30°	257.9	19.9
30°-40°	266.4	20.5
40°-50°	225.9	17.4
50°-60°	164.3	12.7
60°-70°	96.0	7.4
70°-80°	35.7	2.7
80°-90°	4.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	505.3	38.9
0°-40°	771.8	59.4
0°-60°	1162.0	89.5
0°-90°	1298.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1298.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	681	681	681	681	681	
5°	696	690	679	668	666	67
15°	710	688	643	616	610	200
25°	636	601	543	524	523	291
35°	465	445	410	411	414	291
45°	302	294	282	292	299	235
55°	193	184	177	183	184	173
65°	113	103	94	88	88	112
75°	50	42	29	23	24	54
85°	7	4	2	2	2	9
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579932

CATALOG NUMBER: HCC4W15D010SL-HM40525930-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	681.2	681.2	681.2	681.2	681.2	681.2	681.2	681.2	681.2
2.5°	687.1	685.4	683.7	681.2	677.8	675.3	672.8	671.1	671.1
5°	696.4	693.9	690.5	684.6	678.7	673.6	668.4	665.9	665.9
7.5°	703.2	699.8	693.0	684.6	674.5	666.9	659.2	655.8	654.1
10°	704.0	700.6	691.3	678.7	665.1	653.2	644.8	639.7	638.9
12.5°	705.7	701.5	689.6	671.9	654.1	639.7	630.5	625.4	623.6
15°	709.9	704.0	688.0	665.1	643.1	626.1	616.0	611.8	610.1
17.5°	705.7	697.2	677.8	650.7	626.1	607.6	597.4	593.2	593.2
20°	688.8	680.4	657.5	627.9	601.6	583.8	573.7	571.2	569.5
22.5°	665.1	655.8	631.3	600.0	573.7	557.6	550.9	547.5	546.7
25°	636.4	627.1	600.8	568.6	543.3	529.7	523.8	523.8	522.9
27.5°	604.2	592.4	565.2	537.3	512.8	502.7	500.1	500.1	501.0
30°	559.3	550.9	528.0	501.0	478.1	471.3	471.3	473.0	473.0
32.5°	511.1	505.2	484.8	461.2	443.4	439.2	440.8	444.2	445.1
35°	465.4	458.7	445.1	424.0	410.5	408.8	411.3	413.8	413.8
37.5°	420.6	413.8	404.4	387.6	377.4	378.3	381.6	385.0	387.6
40°	376.6	371.5	364.7	351.2	343.6	346.9	351.2	354.5	357.9
42.5°	337.6	332.6	327.5	317.3	312.2	316.4	321.5	325.0	328.4
45°	302.1	298.7	293.6	285.2	281.7	286.1	292.0	295.3	298.7
47.5°	271.6	269.9	263.2	255.6	253.9	258.1	263.2	267.4	269.9
50°	243.7	241.2	235.2	227.6	225.9	232.7	236.0	238.7	241.2
52.5°	216.6	214.1	207.3	200.6	200.6	205.6	208.2	209.0	211.6
55°	192.9	190.4	183.6	178.5	176.8	181.1	182.8	182.8	184.4
57.5°	170.9	168.4	161.6	155.7	154.9	157.4	157.4	157.4	158.3
60°	149.7	147.2	140.4	135.4	133.7	134.5	133.7	132.8	133.7
62.5°	130.3	127.8	121.0	115.1	113.4	113.4	110.9	110.1	110.9
65°	112.6	108.4	103.2	97.3	93.9	91.4	88.0	88.0	88.0
67.5°	94.8	91.4	85.5	79.6	75.3	71.1	66.1	67.7	68.6
70°	78.7	76.2	69.4	63.4	57.5	52.4	48.2	49.9	50.8
72.5°	64.4	60.9	55.0	48.2	43.2	36.4	33.9	35.6	35.6
75°	49.9	46.5	41.5	34.7	28.8	22.9	22.9	23.6	23.6
77.5°	37.2	33.9	28.8	22.9	17.7	13.5	14.4	14.4	14.4
80°	25.4	22.9	18.6	13.5	9.3	7.6	7.6	7.6	8.4
82.5°	14.4	12.7	10.1	6.8	4.2	4.2	4.2	4.2	4.2
85°	6.8	5.1	4.2	2.5	1.7	1.7	1.7	1.7	1.7
87.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)