

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579934

Luminaire Tested: **HCC4W15D010SL-HM40525930-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010SL-HM40525930-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1284.8 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579934
CATALOG NUMBER: HCC4W15D010SL-HM40525930-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579934

CATALOG NUMBER: HCC4W15D010SL-HM40525930-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	88747	88747	88747
5°	92652	88356	84257
10°	94988	86509	78982
15°	96960	84190	73272
20°	96438	80096	67101
25°	92383	74078	61067
30°	85357	67624	55333
35°	74822	60156	50097
40°	65131	53151	45117
45°	56709	46365	40295
50°	50506	39952	35558
55°	45138	35139	30752
60°	40309	30688	26495
65°	35811	26910	25188
70°	31448	23225	23514
75°	26593	19778	21779
80°	20457	16764	19889
85°	11888	13162	16700



TEST NUMBER: P579934

CATALOG NUMBER: HCC4W15D010SL-HM40525930-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	5.2
10°-20°	186.0	14.5
20°-30°	254.2	19.8
30°-40°	255.2	19.9
40°-50°	211.1	16.4
50°-60°	153.0	11.9
60°-70°	96.9	7.5
70°-80°	49.0	3.8
80°-90°	12.0	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	507.6	39.5
0°-40°	762.8	59.4
0°-60°	1126.9	87.7
0°-90°	1284.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1284.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	720	720	720	720	720	
5°	748	737	714	690	680	72
15°	759	730	659	598	574	214
25°	679	634	544	476	449	310
35°	497	467	400	350	333	311
45°	325	306	266	240	231	253
55°	210	191	163	149	143	189
65°	123	109	92	83	86	122
75°	56	48	42	43	46	60
85°	8	8	9	11	12	12
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579934

CATALOG NUMBER: HCC4W15D010SL-HM40525930-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	719.5	719.5	719.5	719.5	719.5	719.5	719.5	719.5	719.5
2.5°	733.0	730.4	726.2	721.2	715.2	708.5	702.6	699.1	697.4
5°	748.3	744.8	737.2	726.2	713.6	700.8	689.8	683.1	680.5
7.5°	757.6	752.5	741.4	724.5	705.1	686.4	670.4	661.1	658.6
10°	758.4	752.5	738.0	715.2	690.7	666.2	646.6	633.1	630.6
12.5°	759.3	751.7	733.8	706.8	676.3	645.8	622.2	606.0	601.8
15°	759.3	751.7	729.6	697.4	659.3	624.7	598.4	579.8	573.8
17.5°	752.5	744.1	717.8	680.5	639.0	600.1	569.6	550.2	544.3
20°	734.7	725.4	695.7	655.1	610.2	569.6	539.2	518.8	511.2
22.5°	709.3	698.3	667.0	623.0	578.1	536.7	507.0	485.8	479.1
25°	678.8	667.9	634.0	590.8	544.3	505.3	475.7	456.3	448.7
27.5°	641.6	629.8	596.7	553.6	510.4	471.5	444.3	426.6	419.0
30°	599.3	586.6	555.2	513.8	474.8	437.6	411.4	396.9	388.5
32.5°	550.2	539.2	511.2	474.0	437.6	402.0	380.1	367.4	360.5
35°	496.9	491.0	467.2	435.0	399.5	369.9	350.4	338.6	332.7
37.5°	449.5	443.5	423.2	396.1	364.9	337.7	321.7	311.5	306.4
40°	404.5	399.5	380.1	357.2	330.1	306.4	292.9	285.3	280.2
42.5°	360.5	358.0	342.0	320.7	297.1	276.7	265.8	259.8	255.6
45°	325.1	321.7	306.4	286.1	265.8	248.9	239.6	235.4	231.0
47.5°	293.7	289.5	273.4	255.6	237.0	221.7	213.3	209.1	207.4
50°	263.2	259.0	244.6	226.8	208.2	197.3	190.4	186.2	185.3
52.5°	236.2	231.9	215.8	198.9	184.5	175.2	169.3	165.1	163.4
55°	209.9	204.9	191.2	175.2	163.4	154.9	148.9	144.7	143.0
57.5°	186.2	181.1	169.3	154.1	143.0	135.4	130.3	126.1	124.4
60°	163.4	159.2	148.2	133.7	124.4	117.7	112.6	109.2	107.4
62.5°	142.2	138.8	127.8	115.1	107.4	101.5	97.3	93.9	95.6
65°	122.7	119.4	109.2	98.2	92.2	86.3	83.0	83.0	86.3
67.5°	104.1	100.7	92.2	83.0	77.9	73.7	71.1	73.7	76.2
70°	87.2	83.8	76.2	68.6	64.4	60.9	60.9	63.4	65.2
72.5°	71.1	67.8	61.7	55.8	52.5	49.9	52.5	54.1	55.8
75°	55.8	53.3	48.2	44.0	41.5	40.6	43.2	44.9	45.7
77.5°	41.5	39.8	36.4	33.0	31.3	32.2	34.7	35.6	36.4
80°	28.8	28.0	25.4	23.6	23.6	24.6	26.3	27.1	28.0
82.5°	17.7	17.7	16.0	15.2	16.0	17.7	18.6	19.4	19.4
85°	8.4	9.3	8.4	8.4	9.3	11.0	11.0	11.8	11.8
87.5°	2.5	2.5	3.4	3.4	4.2	4.2	4.2	4.2	5.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)