

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579950

Luminaire Tested: **HCC4S15D010MB-HM40525935-41RWWH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579950  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S15D010MB-HM40525935-41RWWH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1367.7 lumens  
Efficiency: N/A  
Efficacy: 97.7 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579950  
CATALOG NUMBER: HCC4S15D010MB-HM40525935-41RWWH

### Luminous Intensity Polar Plot





TEST NUMBER: P579950

CATALOG NUMBER: HCC4S15D010MB-HM40525935-41RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77					77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	88513	88513	88513
5°	90832	88504	86857
10°	92884	87749	84292
15°	95492	86502	82058
20°	95230	83194	78744
25°	91226	77888	74976
30°	83918	71726	70957
35°	73828	65095	65622
40°	63875	58272	60703
45°	55506	51790	54878
50°	49259	45670	48740
55°	43697	40042	41784
60°	38928	34759	34759
65°	34615	28865	27055
70°	29897	21855	19258
75°	25068	14488	11914
80°	18966	6961	6322
85°	10190	2547	2547



TEST NUMBER: P579950  
 CATALOG NUMBER: HCC4S15D010MB-HM40525935-41RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.0	5.0
10°-20°	192.6	14.1
20°-30°	271.7	19.9
30°-40°	280.7	20.5
40°-50°	237.9	17.4
50°-60°	173.1	12.7
60°-70°	101.2	7.4
70°-80°	37.6	2.7
80°-90°	4.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.3	38.9
0°-40°	812.9	59.4
0°-60°	1224.0	89.5
0°-90°	1367.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1367.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	718	718	718	718	718	
5°	734	727	715	704	702	70
15°	748	725	677	649	643	210
25°	670	633	572	552	551	307
35°	490	469	432	433	436	306
45°	318	309	297	308	315	248
55°	203	193	186	192	194	183
65°	119	109	99	93	93	118
75°	53	44	30	24	25	56
85°	7	4	2	2	2	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579950

CATALOG NUMBER: HCC4S15D010MB-HM40525935-41RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6	717.6
2.5°	723.8	722.0	720.2	717.6	713.9	711.3	708.6	706.9	706.9
5°	733.6	730.9	727.3	721.1	714.8	709.5	704.1	701.5	701.5
7.5°	740.8	737.1	730.1	721.1	710.4	702.3	694.4	690.8	689.0
10°	741.6	738.0	728.2	714.8	700.6	688.1	679.2	673.9	673.0
12.5°	743.4	738.9	726.4	707.8	689.0	673.9	664.0	658.7	657.0
15°	747.8	741.6	724.6	700.6	677.4	659.6	648.9	644.5	642.6
17.5°	743.4	734.5	713.9	685.5	659.6	640.0	629.3	624.8	624.8
20°	725.5	716.7	692.5	661.4	633.8	615.0	604.3	601.7	599.9
22.5°	700.6	690.8	664.9	631.9	604.3	587.4	580.2	576.7	575.8
25°	670.3	660.5	632.9	599.0	572.3	557.9	551.8	551.8	550.9
27.5°	636.4	624.0	595.4	566.0	540.2	529.5	526.8	526.8	527.7
30°	589.2	580.2	556.2	527.7	503.6	496.5	496.5	498.2	498.2
32.5°	538.4	532.1	510.7	485.8	467.1	462.6	464.4	468.0	468.9
35°	490.3	483.1	468.9	446.6	432.3	430.5	433.2	435.8	435.8
37.5°	443.0	435.8	426.0	408.2	397.5	398.4	402.0	405.6	408.2
40°	396.7	391.4	384.2	369.9	361.9	365.4	369.9	373.5	377.0
42.5°	355.7	350.3	345.0	334.3	328.9	333.4	338.7	342.2	345.9
45°	318.2	314.6	309.3	300.4	296.9	301.3	307.6	311.1	314.6
47.5°	286.1	284.4	277.2	269.2	267.4	271.9	277.2	281.6	284.4
50°	256.7	254.0	247.8	239.8	238.0	245.1	248.7	251.4	254.0
52.5°	228.2	225.5	218.4	211.3	211.3	216.6	219.3	220.1	222.9
55°	203.2	200.6	193.4	188.1	186.2	190.8	192.5	192.5	194.3
57.5°	180.1	177.4	170.2	164.0	163.2	165.8	165.8	165.8	166.7
60°	157.8	155.1	147.9	142.6	140.9	141.7	140.9	140.0	140.9
62.5°	137.2	134.6	127.5	121.2	119.4	119.4	116.8	115.9	116.8
65°	118.6	114.0	108.7	102.6	98.9	96.3	92.7	92.7	92.7
67.5°	99.8	96.3	90.1	83.8	79.4	74.9	69.5	71.3	72.2
70°	82.9	80.3	73.1	66.9	60.6	55.3	50.8	52.6	53.4
72.5°	67.8	64.1	58.0	50.8	45.5	38.3	35.7	37.4	37.4
75°	52.6	49.0	43.7	36.5	30.4	24.1	24.1	25.0	25.0
77.5°	39.2	35.7	30.4	24.1	18.8	14.2	15.1	15.1	15.1
80°	26.7	24.1	19.6	14.2	9.8	8.1	8.1	8.1	8.9
82.5°	15.1	13.4	10.7	7.2	4.4	4.4	4.4	4.4	4.4
85°	7.2	5.3	4.4	2.7	1.8	1.8	1.8	1.8	1.8
87.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)