

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579967

Luminaire Tested: **HCC4W15D010SL-HM40525940-41RWWC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579967  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W15D010SL-HM40525940-41RWWC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1424.5 lumens  
Efficiency: N/A  
Efficacy: 101.7 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 14  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579967  
CATALOG NUMBER: HCC4W15D010SL-HM40525940-41RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P579967

CATALOG NUMBER: HCC4W15D010SL-HM40525940-41RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	84319	84319	84319
5°	87737	85099	84183
10°	90605	85858	84004
15°	93781	86119	83999
20°	94101	84021	82931
25°	90777	79834	80460
30°	84474	74333	76441
35°	76087	68016	70515
40°	67079	61879	64696
45°	58646	55750	58489
50°	51945	50160	52828
55°	45697	44300	46084
60°	40778	37842	38953
65°	35870	30733	30208
70°	31339	22648	20665
75°	25973	13678	11009
80°	19676	5256	3339
85°	9199	1274	1274



TEST NUMBER: P579967  
 CATALOG NUMBER: HCC4W15D010SL-HM40525940-41RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.9	4.6
10°-20°	192.4	13.5
20°-30°	278.7	19.6
30°-40°	294.0	20.6
40°-50°	254.4	17.9
50°-60°	188.5	13.2
60°-70°	108.6	7.6
70°-80°	38.0	2.7
80°-90°	4.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	537.0	37.7
0°-40°	831.0	58.3
0°-60°	1273.9	89.4
0°-90°	1424.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1424.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	684	684	684	684	684	
5°	709	699	687	682	680	68
15°	734	710	674	659	658	207
25°	667	634	587	583	591	305
35°	505	482	452	462	468	316
45°	336	327	320	332	335	261
55°	212	208	206	213	214	192
65°	123	116	105	100	104	123
75°	54	46	29	23	23	59
85°	6	4	1	1	1	10
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579967

CATALOG NUMBER: HCC4W15D010SL-HM40525940-41RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	683.6	683.6	683.6	683.6	683.6	683.6	683.6	683.6	683.6
2.5°	693.8	691.9	689.1	685.5	681.7	679.0	678.1	677.1	677.1
5°	708.6	704.8	699.3	691.9	687.3	684.5	681.7	679.9	679.9
7.5°	718.7	714.9	706.6	696.5	690.0	684.5	680.8	678.1	678.1
10°	723.4	718.7	708.6	695.6	685.5	678.1	672.5	670.7	670.7
12.5°	728.8	723.4	709.5	692.9	679.9	670.7	665.1	663.3	663.3
15°	734.4	727.9	710.4	691.0	674.4	663.3	658.7	657.8	657.8
17.5°	731.7	723.4	703.0	679.9	661.4	650.4	645.7	645.7	646.6
20°	716.9	708.6	685.5	659.6	640.1	631.8	628.2	630.0	631.8
22.5°	694.7	684.5	659.6	634.7	614.3	606.9	606.9	609.7	612.5
25°	667.0	657.8	633.8	606.0	586.6	581.0	582.9	587.5	591.2
27.5°	635.6	625.4	600.4	574.6	555.2	552.5	557.0	563.5	565.3
30°	593.1	584.8	563.5	538.6	521.9	521.0	527.5	532.1	536.7
32.5°	552.5	543.1	522.9	498.8	486.9	487.8	495.2	500.7	503.5
35°	505.3	497.0	482.2	462.8	451.7	453.5	461.8	467.4	468.3
37.5°	460.9	455.4	440.6	425.8	417.5	421.3	428.6	435.1	435.1
40°	416.6	412.0	400.9	388.9	384.3	388.9	396.2	401.8	401.8
42.5°	374.1	371.3	362.1	353.8	351.0	357.5	364.0	368.6	367.7
45°	336.2	333.5	327.0	320.5	319.6	326.1	331.7	334.4	335.3
47.5°	302.1	300.3	294.7	290.0	290.0	296.5	301.2	303.9	304.8
50°	270.7	268.8	264.2	260.5	261.4	267.9	271.6	274.4	275.3
52.5°	239.2	238.3	234.7	230.0	232.7	237.4	242.1	243.9	244.8
55°	212.5	212.5	207.8	204.2	206.0	210.6	213.4	214.3	214.3
57.5°	188.4	187.5	182.0	178.3	179.2	183.9	185.7	186.6	186.6
60°	165.3	164.4	158.8	153.4	153.4	156.1	157.0	157.9	157.9
62.5°	143.1	142.2	135.8	131.2	129.3	128.4	128.4	130.3	133.9
65°	122.9	121.9	115.5	108.1	105.3	102.6	99.7	101.6	103.5
67.5°	104.4	102.6	96.1	89.6	83.1	78.6	73.9	76.6	80.4
70°	86.9	84.9	77.5	70.2	62.8	55.4	51.7	55.4	57.3
72.5°	70.2	68.3	60.9	53.6	44.3	37.0	36.0	37.0	37.9
75°	54.5	53.6	46.2	37.9	28.7	23.1	23.1	23.1	23.1
77.5°	40.6	38.8	31.4	24.0	16.6	13.0	12.1	12.1	12.1
80°	27.7	25.8	19.4	13.9	7.4	5.6	5.6	4.7	4.7
82.5°	15.7	14.8	10.1	5.6	2.7	1.8	1.8	1.8	1.8
85°	6.5	5.6	3.6	1.8	0.9	0.9	0.9	0.9	0.9
87.5°	0.9	0.9	0.9	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)