

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579971

Luminaire Tested: **HCC4W15D010SL-HM40525940-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579971
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W15D010SL-HM40525940-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1395.9 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579971
CATALOG NUMBER: HCC4W15D010SL-HM40525940-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579971

CATALOG NUMBER: HCC4W15D010SL-HM40525940-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	88772	88772	88772
5°	93345	88665	85335
10°	96629	87611	81474
15°	99591	86017	77984
20°	99693	82472	73507
25°	95935	77072	68906
30°	89102	70929	64349
35°	79851	63860	59538
40°	70058	56968	55051
45°	61245	50465	50779
50°	54094	44135	45747
55°	47676	39138	41117
60°	42628	34635	36017
65°	37767	30470	30470
70°	32998	26002	26002
75°	28165	22018	24639
80°	22304	19676	22304
85°	14294	17124	20945



TEST NUMBER: P579971
 CATALOG NUMBER: HCC4W15D010SL-HM40525940-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.2	4.9
10°-20°	192.0	13.8
20°-30°	269.0	19.3
30°-40°	277.2	19.9
40°-50°	236.0	16.9
50°-60°	174.9	12.5
60°-70°	109.7	7.9
70°-80°	54.5	3.9
80°-90°	14.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.3	37.9
0°-40°	806.5	57.8
0°-60°	1217.3	87.2
0°-90°	1395.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1395.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	720	720	720	720	720	
5°	754	741	716	696	689	72
15°	780	745	674	625	611	219
25°	705	656	566	517	506	322
35°	530	491	424	396	395	331
45°	351	327	289	284	291	272
55°	222	204	182	186	191	200
65°	129	116	104	103	104	129
75°	59	53	46	50	52	63
85°	10	10	12	14	15	13
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579971

CATALOG NUMBER: HCC4W15D010SL-HM40525940-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7	719.7
2.5°	735.5	732.7	729.0	722.6	716.1	710.5	704.9	702.2	701.3
5°	753.9	748.4	741.0	729.0	716.1	704.9	695.7	691.1	689.2
7.5°	766.9	761.3	749.3	730.9	712.3	695.7	680.9	674.5	672.6
10°	771.5	765.1	748.4	723.5	699.5	679.1	662.5	654.1	650.5
12.5°	775.2	766.9	745.6	716.1	686.5	661.5	644.0	633.0	630.1
15°	779.9	770.5	744.7	708.7	673.6	644.0	624.6	614.4	610.7
17.5°	775.2	765.1	734.5	693.9	654.1	621.8	600.6	591.4	587.6
20°	759.5	748.4	714.3	670.8	628.3	595.0	573.7	564.5	560.0
22.5°	735.5	723.5	688.3	642.2	598.7	566.3	546.1	536.8	534.0
25°	704.9	693.0	656.0	608.9	566.3	535.0	517.4	509.1	506.3
27.5°	668.9	657.0	620.9	574.8	534.0	504.5	490.6	482.3	480.5
30°	625.6	613.5	578.4	535.9	498.0	470.3	459.2	452.8	451.8
32.5°	577.5	567.4	535.0	496.2	460.1	437.1	428.8	424.1	423.2
35°	530.3	519.3	490.6	455.5	424.1	403.7	396.4	395.4	395.4
37.5°	482.3	471.2	448.1	415.8	389.0	370.5	367.7	368.6	368.6
40°	435.1	425.0	404.7	377.9	353.8	340.0	339.1	341.0	341.9
42.5°	390.8	382.5	364.1	341.0	320.6	309.5	310.4	314.2	316.9
45°	351.1	343.7	327.1	306.8	289.3	280.8	283.7	288.2	291.1
47.5°	315.1	308.6	292.9	274.5	259.6	254.1	257.8	263.3	267.1
50°	281.9	276.3	261.5	242.1	230.0	226.4	231.0	236.5	238.4
52.5°	252.2	246.7	231.0	214.3	205.1	203.3	207.8	212.5	215.2
55°	221.7	217.2	204.2	189.4	182.0	181.1	185.7	189.4	191.2
57.5°	196.8	192.2	180.2	167.3	160.8	159.9	164.4	167.3	168.2
60°	172.8	168.2	157.0	145.1	140.4	140.4	143.3	145.1	146.0
62.5°	150.7	146.0	135.9	125.6	122.0	122.0	122.0	122.9	125.6
65°	129.4	125.6	116.4	107.2	104.4	102.6	102.6	102.6	104.4
67.5°	109.9	106.3	98.9	90.5	87.8	85.0	84.0	86.0	86.0
70°	91.5	88.7	81.3	74.8	72.1	69.2	68.3	72.1	72.1
72.5°	74.8	72.1	67.4	60.9	58.2	57.3	59.1	60.9	61.9
75°	59.1	56.4	52.6	49.0	46.2	47.1	49.9	50.8	51.7
77.5°	44.3	43.4	39.7	37.0	37.0	37.9	39.7	41.6	42.5
80°	31.4	30.5	28.7	26.8	27.7	29.6	30.5	32.3	31.4
82.5°	19.4	19.4	18.5	18.5	19.4	21.3	22.2	23.1	24.0
85°	10.1	10.1	10.1	11.1	12.1	13.0	13.9	14.8	14.8
87.5°	2.7	3.8	3.8	4.7	5.6	5.6	6.5	6.5	6.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)