

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579988

Luminaire Tested: **HCC4W20D010MW-HM40525827-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P579988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W20D010MW-HM40525827-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1835.8 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P579988
CATALOG NUMBER: HCC4W20D010MW-HM40525827-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579988

CATALOG NUMBER: HCC4W20D010MW-HM40525827-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87					87			
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76					76			
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66					66			
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58					58			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47					47			
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35					35			
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	126812	126812	126812
5°	132373	126244	120399
10°	135732	123608	112861
15°	138525	120303	104711
20°	137799	114473	95887
25°	132014	105843	87252
30°	121975	96637	79061
35°	106910	85965	71569
40°	93084	75935	64455
45°	81009	66251	57599
50°	72170	57088	50813
55°	64492	50192	43956
60°	57578	43862	37892
65°	51192	38467	36016
70°	44936	33143	33575
75°	38030	28261	31120
80°	29265	24009	28342
85°	16983	18823	24059



TEST NUMBER: P579988
 CATALOG NUMBER: HCC4W20D010MW-HM40525827-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.4	5.2
10°-20°	265.8	14.5
20°-30°	363.2	19.8
30°-40°	364.7	19.9
40°-50°	301.7	16.4
50°-60°	218.6	11.9
60°-70°	138.5	7.5
70°-80°	70.0	3.8
80°-90°	17.1	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	725.3	39.5
0°-40°	1090.0	59.4
0°-60°	1610.2	87.7
0°-90°	1835.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1835.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1028	1028	1028	1028	1028	
5°	1069	1053	1020	986	972	102
15°	1085	1042	942	855	820	305
25°	970	906	778	680	641	443
35°	710	668	571	501	475	445
45°	464	438	380	342	330	361
55°	300	273	233	213	204	270
65°	175	156	132	118	123	175
75°	80	69	59	62	65	85
85°	12	12	13	16	17	17
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P579988

CATALOG NUMBER: HCC4W20D010MW-HM40525827-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1028.1	1028.1	1028.1	1028.1	1028.1	1028.1	1028.1	1028.1	1028.1
2.5°	1047.4	1043.8	1037.7	1030.5	1022.0	1012.3	1003.9	999.0	996.6
5°	1069.1	1064.3	1053.4	1037.7	1019.6	1001.4	985.7	976.0	972.4
7.5°	1082.4	1075.2	1059.5	1035.3	1007.5	980.9	957.9	944.6	941.0
10°	1083.7	1075.2	1054.7	1022.0	986.9	951.9	924.0	904.6	901.1
12.5°	1084.8	1074.1	1048.6	1009.9	966.3	922.8	888.9	866.0	859.9
15°	1084.8	1074.1	1042.5	996.6	942.1	892.6	855.1	828.5	820.0
17.5°	1075.2	1063.2	1025.6	972.4	913.1	857.5	813.9	786.2	777.7
20°	1049.8	1036.5	994.2	936.1	872.1	813.9	770.4	741.4	730.5
22.5°	1013.5	997.8	953.0	890.2	826.1	766.8	724.4	694.3	684.5
25°	970.0	954.3	905.9	844.2	777.7	722.0	679.7	651.8	641.1
27.5°	916.8	899.8	852.7	791.0	729.3	673.6	635.0	609.5	598.7
30°	856.4	838.1	793.4	734.2	678.5	625.3	587.8	567.2	555.1
32.5°	786.2	770.4	730.5	677.3	625.3	574.5	543.0	524.9	515.2
35°	710.0	701.5	667.7	621.7	570.9	528.5	500.7	483.8	475.3
37.5°	642.2	633.7	604.7	566.0	521.3	482.5	459.6	445.0	437.8
40°	578.1	570.9	543.0	510.4	471.6	437.8	418.4	407.6	400.3
42.5°	515.2	511.6	488.6	458.3	424.5	395.5	379.8	371.3	365.2
45°	464.4	459.6	437.8	408.8	379.8	355.6	342.3	336.2	330.2
47.5°	419.7	413.6	390.7	365.2	338.6	316.9	304.8	298.7	296.3
50°	376.1	370.1	349.5	324.1	297.5	281.8	272.2	266.1	264.8
52.5°	337.4	331.4	308.4	284.2	263.7	250.4	241.9	235.8	233.4
55°	299.9	292.7	273.3	250.4	233.4	221.4	212.9	206.8	204.4
57.5°	266.1	258.9	241.9	220.1	204.4	193.5	186.3	180.2	177.8
60°	233.4	227.3	211.6	191.1	177.8	168.2	160.8	156.0	153.6
62.5°	203.1	198.3	182.6	164.5	153.6	145.1	139.1	134.2	136.7
65°	175.4	170.6	156.0	140.3	131.8	123.4	118.5	118.5	123.4
67.5°	148.8	143.9	131.8	118.5	111.3	105.2	101.6	105.2	108.9
70°	124.6	119.7	108.9	98.0	91.9	87.1	87.1	90.7	93.1
72.5°	101.6	96.8	88.3	79.8	75.0	71.3	75.0	77.4	79.8
75°	79.8	76.2	68.9	62.9	59.3	58.0	61.7	64.1	65.3
77.5°	59.3	56.9	52.0	47.1	44.7	46.0	49.6	50.8	52.0
80°	41.2	39.9	36.2	33.8	33.8	35.1	37.5	38.7	39.9
82.5°	25.3	25.3	22.9	21.8	22.9	25.3	26.6	27.9	27.9
85°	12.0	13.3	12.0	12.0	13.3	15.7	15.7	17.0	17.0
87.5°	3.7	3.7	4.8	4.8	6.1	6.1	6.1	6.1	7.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)