

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P579987

Luminaire Tested: **HCC4W20D010SL-HM40525827-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P579987  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W20D010SL-HM40525827-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1468.2 lumens  
Efficiency: N/A  
Efficacy: 73.4 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P579987  
CATALOG NUMBER: HCC4W20D010SL-HM40525827-41WWBB

### Luminous Intensity Polar Plot





TEST NUMBER: P579987

CATALOG NUMBER: HCC4W20D010SL-HM40525827-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	104844	104844	104844
5°	111088	104501	99252
10°	115705	102829	93435
15°	120124	100357	87855
20°	121260	95545	81251
25°	117329	88368	74377
30°	109697	80087	67681
35°	97770	71193	60818
40°	85467	61911	54134
45°	74450	52523	46819
50°	64975	44557	40144
55°	56944	36923	32515
60°	49807	29825	23855
65°	43429	22240	13426
70°	37939	14389	4328
75°	31120	7482	1144
80°	23227	3410	923
85°	13586	1840	1840



TEST NUMBER: P579987  
 CATALOG NUMBER: HCC4W20D010SL-HM40525827-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.2	5.5
10°-20°	224.5	15.3
20°-30°	310.4	21.1
30°-40°	312.2	21.3
40°-50°	251.9	17.2
50°-60°	170.3	11.6
60°-70°	86.7	5.9
70°-80°	27.7	1.9
80°-90°	4.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	615.2	41.9
0°-40°	927.3	63.2
0°-60°	1349.5	91.9
0°-90°	1468.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1468.2	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	850	850	850	850	850	
5°	897	880	844	814	802	86
15°	941	890	786	711	688	265
25°	862	787	649	570	546	395
35°	649	586	473	414	404	406
45°	427	382	301	268	268	331
55°	265	228	172	150	151	238
65°	149	121	76	50	46	149
75°	65	46	16	4	2	70
85°	10	5	1	1	1	13
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P579987

CATALOG NUMBER: HCC4W20D010SL-HM40525827-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	850.0	850.0	850.0	850.0	850.0	850.0	850.0	850.0	850.0
2.5°	873.0	868.2	863.3	854.9	845.1	835.5	829.4	824.6	822.2
5°	897.2	891.1	880.2	862.1	844.0	827.0	813.7	805.3	801.6
7.5°	916.5	908.1	889.8	864.5	836.7	810.1	793.2	781.1	776.3
10°	923.8	914.0	889.8	856.0	821.0	788.3	764.1	752.1	746.0
12.5°	932.2	921.4	891.1	848.8	805.3	766.5	738.8	723.1	717.0
15°	940.7	926.2	889.8	837.9	785.9	741.2	710.9	695.2	688.0
17.5°	940.7	923.8	880.2	819.8	760.6	713.3	679.5	661.4	655.3
20°	923.8	904.4	857.3	790.7	727.9	677.1	644.5	626.3	619.0
22.5°	897.2	875.4	824.6	755.6	689.2	639.6	607.0	590.0	582.8
25°	862.1	840.3	787.1	715.8	649.3	599.8	569.5	553.8	546.5
27.5°	821.0	796.8	743.6	672.3	607.0	559.9	532.0	517.5	511.4
30°	770.2	747.3	695.2	625.1	562.3	518.7	493.3	480.0	475.2
32.5°	710.9	691.6	640.8	575.6	516.3	476.3	453.4	442.5	437.7
35°	649.3	631.2	586.5	526.0	472.8	435.3	413.5	406.3	403.9
37.5°	591.3	575.6	532.0	476.3	428.1	395.4	376.0	371.2	368.8
40°	530.8	519.9	480.0	429.2	384.5	355.5	339.7	336.2	336.2
42.5°	476.3	464.3	429.2	383.3	343.4	314.4	303.5	299.8	301.1
45°	426.8	414.8	382.1	339.7	301.1	276.9	268.4	268.4	268.4
47.5°	380.9	370.0	339.7	296.3	264.8	245.5	237.0	237.0	238.2
50°	338.6	331.3	297.4	259.9	232.2	214.0	208.0	206.8	209.2
52.5°	298.7	290.2	259.9	226.1	199.5	185.0	178.9	177.8	178.9
55°	264.8	255.1	228.5	195.9	171.7	157.1	149.9	148.8	151.2
57.5°	232.2	224.9	197.1	168.0	145.1	130.5	124.6	122.2	123.3
60°	201.9	194.6	169.3	141.4	120.9	106.4	98.0	95.5	96.7
62.5°	174.1	168.0	143.8	117.3	96.7	83.4	75.0	68.9	71.3
65°	148.8	142.7	120.9	94.3	76.2	61.7	49.6	44.7	46.0
67.5°	127.0	119.7	99.1	75.0	56.8	41.1	27.8	25.3	25.3
70°	105.2	98.0	79.8	58.0	39.9	21.8	12.0	12.0	12.0
72.5°	84.6	78.6	61.7	43.5	25.3	9.6	4.8	4.8	4.8
75°	65.3	60.4	46.0	30.3	15.7	4.8	3.7	2.4	2.4
77.5°	48.4	43.5	32.7	20.5	9.6	2.4	2.4	2.4	2.4
80°	32.7	29.0	21.8	12.0	4.8	1.3	1.3	1.3	1.3
82.5°	19.4	17.0	12.0	6.1	2.4	1.3	1.3	1.3	1.3
85°	9.6	7.2	4.8	2.4	1.3	1.3	1.3	1.3	1.3
87.5°	2.4	1.3	1.3	1.3	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)