

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580019

Luminaire Tested: **HCC4S20D010MB-HM40525835-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580019
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S20D010MB-HM40525835-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2061.1 lumens
Efficiency: N/A
Efficacy: 103.1 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580019
CATALOG NUMBER: HCC4S20D010MB-HM40525835-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580019

CATALOG NUMBER: HCC4S20D010MB-HM40525835-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	142353	142353	142353
5°	148617	141733	135171
10°	152377	138775	126689
15°	155535	135078	117558
20°	154718	128505	107648
25°	148209	118826	97935
30°	136915	108487	88775
35°	120025	96505	80348
40°	104516	85274	72361
45°	90951	74363	64664
50°	81036	64092	57069
55°	72428	56364	49353
60°	64658	49240	42530
65°	57467	43195	40394
70°	50417	37218	37723
75°	42701	31692	34933
80°	32746	26992	31822
85°	19106	21087	26889



TEST NUMBER: P580019
 CATALOG NUMBER: HCC4S20D010MB-HM40525835-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.2	5.2
10°-20°	298.4	14.5
20°-30°	407.7	19.8
30°-40°	409.4	19.9
40°-50°	338.7	16.4
50°-60°	245.4	11.9
60°-70°	155.4	7.5
70°-80°	78.6	3.8
80°-90°	19.2	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	814.3	39.5
0°-40°	1223.7	59.4
0°-60°	1807.8	87.7
0°-90°	2061.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2061.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1154	1154	1154	1154	1154	
5°	1200	1183	1145	1107	1092	115
15°	1218	1170	1058	960	921	343
25°	1089	1017	873	763	720	498
35°	797	750	641	562	534	500
45°	521	492	426	384	371	406
55°	337	307	262	239	230	303
65°	197	175	148	133	138	196
75°	90	77	66	69	73	96
85°	14	14	15	18	19	19
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580019

CATALOG NUMBER: HCC4S20D010MB-HM40525835-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1	1154.1
2.5°	1175.9	1171.8	1165.0	1156.9	1147.3	1136.6	1127.0	1121.5	1118.9
5°	1200.3	1194.9	1182.7	1165.0	1144.7	1124.3	1106.6	1095.7	1091.7
7.5°	1215.2	1207.1	1189.4	1162.4	1131.1	1101.2	1075.4	1060.5	1056.4
10°	1216.6	1207.1	1184.0	1147.3	1108.0	1068.7	1037.3	1015.7	1011.5
12.5°	1218.0	1205.7	1177.3	1133.8	1084.9	1036.1	998.0	972.2	965.4
15°	1218.0	1205.7	1170.5	1118.9	1057.8	1002.1	960.0	930.1	920.6
17.5°	1207.1	1193.6	1151.5	1091.7	1025.2	962.7	913.8	882.6	873.1
20°	1178.7	1163.6	1116.1	1051.0	979.0	913.8	865.0	832.4	820.1
22.5°	1137.8	1120.3	1070.0	999.4	927.5	860.8	813.3	779.4	768.5
25°	1089.0	1071.3	1017.0	947.8	873.1	810.6	763.1	731.9	719.6
27.5°	1029.2	1010.3	957.3	888.0	818.7	756.3	712.9	684.3	672.1
30°	961.3	941.0	890.8	824.2	761.7	702.0	659.9	636.8	623.3
32.5°	882.6	865.0	820.1	760.3	702.0	645.0	609.6	589.3	578.4
35°	797.1	787.5	749.6	697.9	640.9	593.3	562.1	543.1	533.6
37.5°	721.0	711.5	678.9	635.4	585.2	541.7	516.0	499.6	491.5
40°	649.1	640.9	609.6	573.0	529.6	491.5	469.8	457.5	449.4
42.5°	578.4	574.4	548.6	514.7	476.6	444.0	426.3	416.8	410.1
45°	521.4	516.0	491.5	458.9	426.3	399.2	384.2	377.5	370.7
47.5°	471.2	464.4	438.6	410.1	380.2	355.8	342.2	335.4	332.6
50°	422.3	415.4	392.4	363.9	334.0	316.3	305.6	298.7	297.4
52.5°	378.9	372.1	346.3	319.1	296.0	281.1	271.6	264.7	262.1
55°	336.8	328.6	306.8	281.1	262.1	248.4	239.0	232.2	229.5
57.5°	298.7	290.5	271.6	247.2	229.5	217.2	209.1	202.3	199.6
60°	262.1	255.3	237.7	214.5	199.6	188.8	180.5	175.1	172.4
62.5°	228.1	222.6	205.1	184.7	172.4	163.0	156.1	150.7	153.5
65°	196.9	191.4	175.1	157.5	148.0	138.4	133.1	133.1	138.4
67.5°	167.0	161.6	148.0	133.1	124.9	118.1	114.0	118.1	122.2
70°	139.8	134.4	122.2	110.0	103.2	97.7	97.7	101.9	104.6
72.5°	114.0	108.6	99.1	89.6	84.2	80.1	84.2	86.9	89.6
75°	89.6	85.6	77.4	70.7	66.5	65.1	69.3	71.9	73.3
77.5°	66.5	63.8	58.4	53.0	50.2	51.6	55.6	57.0	58.4
80°	46.1	44.8	40.7	38.0	38.0	39.3	42.1	43.5	44.8
82.5°	28.6	28.6	25.8	24.4	25.8	28.6	29.8	31.2	31.2
85°	13.5	14.9	13.5	13.5	14.9	17.7	17.7	19.0	19.0
87.5°	4.1	4.1	5.4	5.4	6.8	6.8	6.8	6.8	8.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)