

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580018

Luminaire Tested: **HCC4W20D010MB-HM40525835-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580018  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W20D010MB-HM40525835-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1648.4 lumens  
Efficiency: N/A  
Efficacy: 82.4 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580018  
CATALOG NUMBER: HCC4W20D010MB-HM40525835-41WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580018

CATALOG NUMBER: HCC4W20D010MB-HM40525835-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	117709	117709	117709
5°	124708	117316	111423
10°	129895	115441	104896
15°	134848	112680	98633
20°	136131	107267	91227
25°	131715	99201	83495
30°	123157	89900	75985
35°	109756	79911	68272
40°	95950	69495	60768
45°	83590	58960	52558
50°	72938	50007	45056
55°	63933	41461	36472
60°	55900	33476	26791
65°	48741	24983	15060
70°	42591	16157	4869
75°	34933	8435	1334
80°	26069	3836	994
85°	15426	1981	1981



TEST NUMBER: P580018

CATALOG NUMBER: HCC4W20D010MB-HM40525835-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.1	5.5
10°-20°	252.1	15.3
20°-30°	348.5	21.1
30°-40°	350.4	21.3
40°-50°	282.8	17.2
50°-60°	191.2	11.6
60°-70°	97.3	5.9
70°-80°	31.2	1.9
80°-90°	4.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.6	41.9
0°-40°	1041.1	63.2
0°-60°	1515.1	91.9
0°-90°	1648.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1648.4	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	954	954	954	954	954	
5°	1007	988	948	914	900	97
15°	1056	999	882	798	772	297
25°	968	884	729	639	614	443
35°	729	658	531	464	453	455
45°	479	429	338	301	301	371
55°	297	257	193	168	170	267
65°	167	136	86	56	52	167
75°	73	52	18	4	3	79
85°	11	5	1	1	1	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580018

CATALOG NUMBER: HCC4W20D010MB-HM40525835-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3	954.3
2.5°	980.1	974.6	969.2	959.7	948.8	938.0	931.2	925.7	923.1
5°	1007.2	1000.4	988.3	967.8	947.5	928.5	913.6	904.1	899.9
7.5°	1029.0	1019.5	999.0	970.6	939.4	909.5	890.5	876.9	871.5
10°	1037.1	1026.2	999.0	961.1	921.7	885.0	858.0	844.3	837.5
12.5°	1046.6	1034.4	1000.4	952.9	904.1	860.6	829.4	811.7	805.0
15°	1056.0	1039.8	999.0	940.7	882.4	832.1	798.2	780.5	772.4
17.5°	1056.0	1037.1	988.3	920.4	853.8	800.8	762.9	742.6	735.7
20°	1037.1	1015.3	962.4	887.8	817.2	760.1	723.5	703.1	695.0
22.5°	1007.2	982.7	925.7	848.4	773.8	718.1	681.4	662.4	654.2
25°	967.8	943.4	883.6	803.6	728.9	673.3	639.3	621.7	613.5
27.5°	921.7	894.5	834.8	754.7	681.4	628.4	597.2	581.0	574.2
30°	864.7	838.9	780.5	701.8	631.2	582.3	553.9	538.9	533.5
32.5°	798.2	776.4	719.4	646.1	579.6	534.8	509.0	496.9	491.4
35°	728.9	708.6	658.4	590.5	530.7	488.7	464.2	456.0	453.4
37.5°	663.8	646.1	597.2	534.8	480.5	443.9	422.2	416.7	414.1
40°	595.9	583.7	538.9	481.9	431.6	399.0	381.5	377.4	377.4
42.5°	534.8	521.3	481.9	430.4	385.5	352.9	340.8	336.6	338.0
45°	479.2	465.6	429.0	381.5	338.0	310.8	301.3	301.3	301.3
47.5°	427.6	415.3	381.5	332.6	297.3	275.5	266.1	266.1	267.4
50°	380.1	372.0	333.9	291.8	260.6	240.3	233.5	232.2	234.8
52.5°	335.3	325.7	291.8	253.8	224.0	207.7	201.0	199.6	201.0
55°	297.3	286.4	256.6	219.9	192.8	176.5	168.4	167.0	169.6
57.5°	260.6	252.5	221.3	188.7	162.9	146.6	139.8	137.1	138.4
60°	226.6	218.5	190.1	158.9	135.7	119.4	110.0	107.2	108.6
62.5°	195.4	188.7	161.5	131.7	108.6	93.7	84.2	77.4	80.1
65°	167.0	160.1	135.7	105.9	85.6	69.3	55.6	50.2	51.6
67.5°	142.6	134.4	111.3	84.2	63.8	46.1	31.2	28.6	28.6
70°	118.1	110.0	89.6	65.1	44.8	24.4	13.5	13.5	13.5
72.5°	95.0	88.2	69.3	48.9	28.6	10.9	5.4	5.4	5.4
75°	73.3	67.9	51.6	34.0	17.7	5.4	4.1	2.8	2.8
77.5°	54.3	48.9	36.7	23.1	10.9	2.8	2.8	2.8	2.8
80°	36.7	32.6	24.4	13.5	5.4	1.4	1.4	1.4	1.4
82.5°	21.7	19.0	13.5	6.8	2.8	1.4	1.4	1.4	1.4
85°	10.9	8.1	5.4	2.8	1.4	1.4	1.4	1.4	1.4
87.5°	2.8	1.4	1.4	1.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)