

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580035

Luminaire Tested: **HCC4S20D010MB-HM40525840-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580035
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S20D010MB-HM40525840-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2140.4 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580035
CATALOG NUMBER: HCC4S20D010MB-HM40525840-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580035

CATALOG NUMBER: HCC4S20D010MB-HM40525840-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77								
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67								
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47								
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35								
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	138505	138505	138505
5°	142142	138526	135926
10°	145363	137322	131912
15°	149456	135384	128437
20°	149048	130185	123228
25°	142766	121888	117329
30°	131332	112247	111051
35°	115523	101865	102709
40°	99959	91200	95000
45°	86870	81026	85893
50°	77102	71460	76296
55°	68406	62708	65396
60°	60908	54395	54395
65°	54169	45180	42349
70°	46775	34225	30185
75°	39269	22637	18634
80°	29762	10939	9944
85°	15709	3963	3963



TEST NUMBER: P580035
 CATALOG NUMBER: HCC4S20D010MB-HM40525840-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	5.0
10°-20°	301.5	14.1
20°-30°	425.2	19.9
30°-40°	439.2	20.5
40°-50°	372.3	17.4
50°-60°	270.9	12.7
60°-70°	158.3	7.4
70°-80°	58.8	2.7
80°-90°	7.7	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	833.0	38.9
0°-40°	1272.3	59.4
0°-60°	1915.5	89.5
0°-90°	2140.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2140.4	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1123	1123	1123	1123	1123	
5°	1148	1138	1119	1102	1098	110
15°	1170	1134	1060	1016	1006	329
25°	1049	990	896	864	862	480
35°	767	734	676	678	682	479
45°	498	484	464	481	492	388
55°	318	303	292	301	304	286
65°	186	170	155	145	145	184
75°	82	68	48	38	39	88
85°	11	7	3	3	3	16
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580035

CATALOG NUMBER: HCC4S20D010MB-HM40525840-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9	1122.9
2.5°	1132.7	1129.9	1127.2	1122.9	1117.4	1113.2	1109.0	1106.2	1106.2
5°	1148.0	1143.9	1138.3	1128.5	1118.8	1110.4	1102.0	1097.8	1097.8
7.5°	1159.2	1153.7	1142.5	1128.5	1111.8	1099.3	1086.7	1081.0	1078.3
10°	1160.6	1155.0	1139.7	1118.8	1096.4	1076.9	1062.9	1054.6	1053.2
12.5°	1163.4	1156.4	1136.9	1107.5	1078.3	1054.6	1039.3	1030.9	1028.1
15°	1170.4	1160.6	1134.2	1096.4	1060.2	1032.3	1015.6	1008.6	1005.8
17.5°	1163.4	1149.4	1117.4	1072.7	1032.3	1001.6	984.8	977.8	977.8
20°	1135.5	1121.5	1083.9	1035.1	991.8	962.6	945.8	941.6	938.8
22.5°	1096.4	1081.0	1040.7	989.1	945.8	919.3	908.1	902.6	901.2
25°	1049.0	1033.7	990.4	937.4	895.6	873.2	863.5	863.5	862.1
27.5°	996.1	976.4	931.8	885.8	845.3	828.6	824.5	824.5	825.8
30°	922.1	908.1	870.5	825.8	788.1	777.0	777.0	779.7	779.7
32.5°	842.6	832.8	799.3	760.2	731.0	724.0	726.7	732.4	733.7
35°	767.2	756.1	733.7	698.9	676.5	673.7	678.0	682.1	682.1
37.5°	693.2	682.1	666.8	638.9	622.1	623.5	629.1	634.7	638.9
40°	620.8	612.4	601.3	578.9	566.4	571.9	578.9	584.5	590.0
42.5°	556.6	548.3	539.9	523.1	514.8	521.8	530.0	535.6	541.3
45°	498.0	492.4	484.0	470.2	464.5	471.5	481.3	486.8	492.4
47.5°	447.8	445.0	433.8	421.3	418.5	425.4	433.8	440.8	445.0
50°	401.8	397.6	387.8	375.3	372.4	383.6	389.2	393.4	397.6
52.5°	357.1	352.9	341.8	330.6	330.6	338.9	343.2	344.6	348.7
55°	318.1	313.8	302.7	294.3	291.6	298.6	301.3	301.3	304.1
57.5°	281.8	277.6	266.4	256.7	255.3	259.5	259.5	259.5	260.8
60°	246.9	242.7	231.6	223.2	220.5	221.8	220.5	219.0	220.5
62.5°	214.8	210.6	199.5	189.7	187.0	187.0	182.7	181.3	182.7
65°	185.6	178.6	170.2	160.5	154.8	150.6	145.1	145.1	145.1
67.5°	156.2	150.6	140.9	131.1	124.1	117.2	108.9	111.6	113.0
70°	129.7	125.6	114.4	104.6	94.9	86.5	79.5	82.4	83.7
72.5°	106.0	100.5	90.7	79.5	71.1	60.0	55.7	58.6	58.6
75°	82.4	76.7	68.4	57.2	47.5	37.6	37.6	39.1	39.1
77.5°	61.4	55.7	47.5	37.6	29.2	22.4	23.7	23.7	23.7
80°	41.9	37.6	30.7	22.4	15.4	12.5	12.5	12.5	14.0
82.5°	23.7	20.9	16.7	11.1	7.0	7.0	7.0	7.0	7.0
85°	11.1	8.4	7.0	4.1	2.8	2.8	2.8	2.8	2.8
87.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)