

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580069

Luminaire Tested: **HCC4S20D010MW-HM40525930-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S20D010MW-HM40525930-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1765.8 lumens
Efficiency: N/A
Efficacy: 88.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 20
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580069
CATALOG NUMBER: HCC4S20D010MW-HM40525930-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580069

CATALOG NUMBER: HCC4S20D010MW-HM40525930-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77					77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	114267	114267	114267
5°	117279	114283	112153
10°	119925	113300	108841
15°	123317	111696	105976
20°	122979	107411	101675
25°	117792	100562	96806
30°	108344	92606	91638
35°	95315	84037	84745
40°	82456	75243	78383
45°	71676	66844	70874
50°	63612	58968	62940
55°	56428	51719	53934
60°	50251	44848	44848
65°	44684	37300	34936
70°	38588	28202	24884
75°	32359	18634	15346
80°	24506	8950	8169
85°	13020	3255	3255



TEST NUMBER: P580069
 CATALOG NUMBER: HCC4S20D010MW-HM40525930-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	5.0
10°-20°	248.7	14.1
20°-30°	350.8	19.9
30°-40°	362.4	20.5
40°-50°	307.2	17.4
50°-60°	223.5	12.7
60°-70°	130.6	7.4
70°-80°	48.5	2.7
80°-90°	6.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	687.3	38.9
0°-40°	1049.7	59.4
0°-60°	1580.4	89.5
0°-90°	1765.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1765.8	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	926	926	926	926	926	
5°	947	939	923	909	906	91
15°	966	936	875	838	830	271
25°	866	817	739	712	711	396
35°	633	605	558	559	563	395
45°	411	399	383	397	406	320
55°	262	250	240	249	251	236
65°	153	140	128	120	120	152
75°	68	56	39	31	32	73
85°	9	6	2	2	2	13
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580069

CATALOG NUMBER: HCC4S20D010MW-HM40525930-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	926.4	926.4	926.4	926.4	926.4	926.4	926.4	926.4	926.4
2.5°	934.6	932.3	929.9	926.4	921.8	918.4	915.0	912.7	912.7
5°	947.2	943.8	939.2	931.1	923.0	916.1	909.2	905.8	905.8
7.5°	956.4	951.8	942.6	931.1	917.3	906.9	896.5	891.9	889.6
10°	957.5	952.9	940.3	923.0	904.6	888.5	877.0	870.1	869.0
12.5°	959.8	954.1	938.0	913.8	889.6	870.1	857.4	850.5	848.2
15°	965.7	957.5	935.7	904.6	874.7	851.6	837.9	832.1	829.9
17.5°	959.8	948.3	921.8	885.0	851.6	826.3	812.5	806.8	806.8
20°	936.9	925.3	894.2	853.9	818.3	794.1	780.3	776.9	774.6
22.5°	904.6	891.9	858.5	816.0	780.3	758.4	749.2	744.6	743.5
25°	865.5	852.8	817.1	773.4	738.9	720.4	712.4	712.4	711.3
27.5°	821.7	805.7	768.8	730.9	697.5	683.6	680.2	680.2	681.3
30°	760.7	749.2	718.1	681.3	650.2	641.1	641.1	643.4	643.4
32.5°	695.2	687.1	659.4	627.3	603.1	597.4	599.7	604.2	605.4
35°	633.0	623.7	605.4	576.6	558.1	555.8	559.4	562.8	562.8
37.5°	572.0	562.8	550.1	527.2	513.3	514.4	519.0	523.6	527.2
40°	512.1	505.3	496.1	477.6	467.3	471.9	477.6	482.2	486.8
42.5°	459.3	452.3	445.4	431.6	424.7	430.5	437.4	441.9	446.5
45°	410.9	406.3	399.4	387.8	383.2	388.9	397.1	401.7	406.3
47.5°	369.4	367.2	358.0	347.5	345.2	351.0	358.0	363.7	367.2
50°	331.5	328.0	319.9	309.6	307.3	316.5	321.0	324.6	328.0
52.5°	294.7	291.2	281.9	272.8	272.8	279.6	283.1	284.2	287.8
55°	262.4	259.0	249.7	242.8	240.5	246.3	248.6	248.6	250.8
57.5°	232.5	229.1	219.8	211.7	210.6	214.0	214.0	214.0	215.2
60°	203.7	200.3	191.1	184.1	181.8	182.9	181.8	180.7	181.8
62.5°	177.2	173.8	164.6	156.6	154.3	154.3	150.7	149.6	150.7
65°	153.1	147.3	140.4	132.4	127.8	124.3	119.7	119.7	119.7
67.5°	128.9	124.3	116.2	108.2	102.4	96.7	89.8	92.1	93.3
70°	107.0	103.6	94.4	86.4	78.2	71.3	65.6	67.9	69.0
72.5°	87.5	82.8	74.8	65.6	58.7	49.4	46.0	48.3	48.3
75°	67.9	63.3	56.4	47.1	39.1	31.1	31.1	32.2	32.2
77.5°	50.6	46.0	39.1	31.1	24.2	18.5	19.6	19.6	19.6
80°	34.5	31.1	25.3	18.5	12.6	10.3	10.3	10.3	11.5
82.5°	19.6	17.3	13.8	9.2	5.7	5.7	5.7	5.7	5.7
85°	9.2	6.9	5.7	3.4	2.3	2.3	2.3	2.3	2.3
87.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)