

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580073

Luminaire Tested: **HCC4W20D010MB-HM40525930-41WWW**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580073  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W20D010MB-HM40525930-41WWW  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1747.5 lumens  
Efficiency: N/A  
Efficacy: 87.4 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580073  
CATALOG NUMBER: HCC4W20D010MB-HM40525930-41WWW

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580073

CATALOG NUMBER: HCC4W20D010MB-HM40525930-41WWW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	120694	120694	120694
5°	125996	120164	114605
10°	129194	117658	107413
15°	131860	114518	99667
20°	131170	108960	91266
25°	125645	100752	83033
30°	116092	91994	75259
35°	101760	81809	68121
40°	88607	72280	61347
45°	77119	63059	54826
50°	68697	54344	48376
55°	61396	47783	41827
60°	54815	41740	36066
65°	48712	36629	34294
70°	42772	31556	31989
75°	36172	26879	29643
80°	27773	22872	26992
85°	16275	17832	22927



TEST NUMBER: P580073  
 CATALOG NUMBER: HCC4W20D010MB-HM40525930-41WWW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.7	5.2
10°-20°	253.0	14.5
20°-30°	345.7	19.8
30°-40°	347.1	19.9
40°-50°	287.1	16.4
50°-60°	208.1	11.9
60°-70°	131.8	7.5
70°-80°	66.6	3.8
80°-90°	16.3	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	690.4	39.5
0°-40°	1037.5	59.4
0°-60°	1532.7	87.7
0°-90°	1747.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1747.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	978	978	978	978	978	
5°	1018	1003	970	938	926	98
15°	1033	992	897	814	780	290
25°	923	862	740	647	610	422
35°	676	635	543	477	452	424
45°	442	417	362	326	314	344
55°	286	260	222	203	194	257
65°	167	148	126	113	118	166
75°	76	66	56	59	62	81
85°	12	12	13	15	16	16
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580073

CATALOG NUMBER: HCC4W20D010MB-HM40525930-41WWW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5
2.5°	997.0	993.5	987.8	980.8	972.8	963.6	955.6	950.9	948.6
5°	1017.6	1013.0	1002.7	987.8	970.5	953.2	938.2	929.1	925.6
7.5°	1030.4	1023.5	1008.4	985.4	959.0	933.7	911.8	899.1	895.7
10°	1031.5	1023.5	1003.9	972.8	939.4	906.0	879.5	861.1	857.6
12.5°	1032.6	1022.3	998.1	961.3	919.8	878.4	846.1	824.2	818.5
15°	1032.6	1022.3	992.4	948.6	896.8	849.6	813.9	788.6	780.5
17.5°	1023.5	1011.9	976.2	925.6	869.2	816.2	774.8	748.3	740.3
20°	999.3	986.6	946.3	891.0	830.1	774.8	733.3	705.7	695.3
22.5°	964.7	949.7	907.2	847.3	786.3	729.8	689.6	660.8	651.6
25°	923.2	908.3	862.3	803.6	740.3	687.3	647.0	620.5	610.1
27.5°	872.6	856.5	811.6	752.9	694.2	641.2	604.4	580.3	569.8
30°	815.1	797.7	755.2	698.8	645.9	595.2	559.5	539.9	528.4
32.5°	748.3	733.3	695.3	644.7	595.2	546.8	517.0	499.6	490.5
35°	675.8	667.7	635.4	591.7	543.3	503.1	476.6	460.5	452.4
37.5°	611.4	603.2	575.6	538.7	496.2	459.4	437.5	423.7	416.7
40°	550.3	543.3	517.0	485.9	448.9	416.7	398.4	387.9	381.0
42.5°	490.5	487.0	465.1	436.3	404.1	376.4	361.5	353.4	347.7
45°	442.1	437.5	416.7	389.1	361.5	338.5	325.7	320.0	314.3
47.5°	399.5	393.8	371.9	347.7	322.3	301.7	290.1	284.3	282.0
50°	358.0	352.2	332.7	308.5	283.2	268.3	259.0	253.3	252.1
52.5°	321.2	315.4	293.5	270.6	251.0	238.3	230.2	224.5	222.2
55°	285.5	278.6	260.1	238.3	222.2	210.7	202.6	196.8	194.5
57.5°	253.3	246.4	230.2	209.6	194.5	184.2	177.3	171.5	169.2
60°	222.2	216.4	201.4	181.9	169.2	160.0	153.1	148.5	146.2
62.5°	193.4	188.8	173.9	156.6	146.2	138.1	132.4	127.8	130.1
65°	166.9	162.3	148.5	133.5	125.5	117.5	112.9	112.9	117.5
67.5°	141.7	137.0	125.5	112.9	105.9	100.1	96.7	100.1	103.6
70°	118.6	114.0	103.6	93.3	87.5	82.9	82.9	86.4	88.7
72.5°	96.7	92.1	84.1	75.9	71.3	67.9	71.3	73.6	75.9
75°	75.9	72.5	65.6	59.9	56.4	55.3	58.7	61.0	62.2
77.5°	56.4	54.1	49.6	44.8	42.6	43.7	47.3	48.4	49.6
80°	39.1	38.0	34.5	32.2	32.2	33.4	35.7	36.8	38.0
82.5°	24.2	24.2	21.9	20.8	21.9	24.2	25.3	26.5	26.5
85°	11.5	12.6	11.5	11.5	12.6	14.9	14.9	16.2	16.2
87.5°	3.4	3.4	4.6	4.6	5.7	5.7	5.7	5.7	6.9
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)