

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580110

Luminaire Tested: **HCC4S20D010SL-HM40525940-41WWWB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580110  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S20D010SL-HM40525940-41WWWB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1898.5 lumens  
Efficiency: N/A  
Efficacy: 94.9 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 20  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580110  
CATALOG NUMBER: HCC4S20D010SL-HM40525940-41WWWB

### Luminous Intensity Polar Plot





TEST NUMBER: P580110

CATALOG NUMBER: HCC4S20D010SL-HM40525940-41WWWB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87			
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66			
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58			
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51			
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46			
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34			
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	120755	120755	120755
5°	126962	120585	116066
10°	131423	119149	110807
15°	135435	116983	106078
20°	135593	112163	99956
25°	130503	104835	93730
30°	121163	96466	87536
35°	108611	86853	80980
40°	95306	77497	74873
45°	83294	68606	69042
50°	73552	60043	62230
55°	64837	53224	55934
60°	57972	47118	48968
65°	51338	41444	41444
70°	44863	35379	35379
75°	38316	29976	33551
80°	30402	26779	30402
85°	19672	23068	28446



TEST NUMBER: P580110

CATALOG NUMBER: HCC4S20D010SL-HM40525940-41WWWB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.8	4.9
10°-20°	261.2	13.8
20°-30°	365.9	19.3
30°-40°	377.0	19.9
40°-50°	321.0	16.9
50°-60°	237.8	12.5
60°-70°	149.3	7.9
70°-80°	74.2	3.9
80°-90°	19.5	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	719.9	37.9
0°-40°	1096.9	57.8
0°-60°	1655.7	87.2
0°-90°	1898.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1898.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	979	979	979	979	979	
5°	1025	1008	974	946	937	99
15°	1061	1013	916	850	831	298
25°	959	892	770	704	689	439
35°	721	667	577	539	538	450
45°	478	445	393	386	396	371
55°	302	278	248	253	260	273
65°	176	158	142	140	142	176
75°	80	72	63	68	70	86
85°	14	14	16	19	20	18
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580110

CATALOG NUMBER: HCC4S20D010SL-HM40525940-41WWWB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	979.0	979.0	979.0	979.0	979.0	979.0	979.0	979.0	979.0
2.5°	1000.3	996.5	991.5	982.7	973.9	966.3	958.9	955.1	953.8
5°	1025.4	1018.0	1007.9	991.5	973.9	958.9	946.3	940.0	937.4
7.5°	1043.1	1035.5	1019.1	994.0	968.9	946.3	926.2	917.4	914.8
10°	1049.3	1040.6	1018.0	984.0	951.3	923.7	901.1	889.7	884.7
12.5°	1054.3	1043.1	1014.2	973.9	933.7	899.8	875.8	860.8	857.0
15°	1060.6	1048.0	1012.9	963.8	916.1	875.8	849.5	835.7	830.7
17.5°	1054.3	1040.6	999.0	943.8	889.7	845.8	816.9	804.3	799.2
20°	1033.0	1018.0	971.4	912.3	854.5	809.3	780.4	767.8	761.5
22.5°	1000.3	984.0	936.2	873.4	814.4	770.3	742.7	730.2	726.4
25°	958.9	942.5	892.3	828.1	770.3	727.7	703.7	692.4	688.7
27.5°	909.8	893.5	844.5	781.7	726.4	686.1	667.3	656.0	653.4
30°	850.7	834.4	786.7	728.9	677.3	639.7	624.5	615.8	614.6
32.5°	785.5	771.6	727.7	674.8	625.8	594.4	583.1	576.8	575.6
35°	721.3	706.2	667.3	619.5	576.8	549.2	539.1	537.8	537.8
37.5°	656.0	640.9	609.5	565.5	529.1	503.9	500.2	501.5	501.5
40°	591.9	578.1	550.4	514.0	481.3	462.5	461.2	463.7	465.0
42.5°	531.5	520.3	495.2	463.7	436.1	420.9	422.2	427.3	431.0
45°	477.5	467.5	444.8	417.2	393.3	382.1	385.9	392.0	395.8
47.5°	428.5	419.7	398.4	373.2	353.2	345.6	350.6	358.2	363.1
50°	383.3	375.8	355.7	329.3	312.9	307.9	314.2	321.7	324.3
52.5°	343.1	335.5	314.2	291.6	279.0	276.4	282.7	289.0	292.8
55°	301.5	295.4	277.7	257.6	247.5	246.3	252.6	257.6	260.1
57.5°	267.7	261.4	245.0	227.5	218.6	217.4	223.7	227.5	228.7
60°	235.0	228.7	213.7	197.3	191.0	191.0	194.8	197.3	198.5
62.5°	204.9	198.5	184.8	170.9	165.9	165.9	165.9	167.1	170.9
65°	175.9	170.9	158.3	145.8	142.0	139.5	139.5	139.5	142.0
67.5°	149.6	144.5	134.4	123.2	119.4	115.6	114.4	116.9	116.9
70°	124.4	120.7	110.6	101.7	98.1	94.3	93.0	98.1	98.1
72.5°	101.7	98.1	91.8	82.9	79.1	77.9	80.4	82.9	84.2
75°	80.4	76.6	71.7	66.6	62.9	64.1	67.9	69.2	70.4
77.5°	60.3	59.1	54.0	50.2	50.2	51.5	54.0	56.5	57.8
80°	42.8	41.5	39.0	36.5	37.7	40.3	41.5	43.9	42.8
82.5°	26.4	26.4	25.1	25.1	26.4	28.9	30.2	31.4	32.7
85°	13.9	13.9	13.9	15.0	16.3	17.5	18.8	20.1	20.1
87.5°	3.8	5.0	5.0	6.3	7.6	7.6	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)