

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580143

Luminaire Tested: **HCC4S25D010MB-HM40525830-41RWWH**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580143  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4S25D010MB-HM40525830-41RWWH  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2452.9 lumens  
Efficiency: N/A  
Efficacy: 91.5 lumens/watt  
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580143  
CATALOG NUMBER: HCC4S25D010MB-HM40525830-41RWWH

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580143

CATALOG NUMBER: HCC4S25D010MB-HM40525830-41RWWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77					77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	158733	158733	158733
5°	162906	158746	155786
10°	166593	157387	151175
15°	171280	155152	147183
20°	170811	149205	141224
25°	163616	139690	134464
30°	150503	128640	127273
35°	132403	116758	117706
40°	114547	104516	108895
45°	99551	92853	98435
50°	88347	81919	87445
55°	78363	71847	74944
60°	69789	62314	62314
65°	62050	51805	48536
70°	53627	39201	34621
75°	44941	25878	21303
80°	34095	12502	11365
85°	18115	4529	4529



TEST NUMBER: P580143  
 CATALOG NUMBER: HCC4S25D010MB-HM40525830-41RWWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.9	5.0
10°-20°	345.5	14.1
20°-30°	487.3	19.9
30°-40°	503.4	20.5
40°-50°	426.7	17.4
50°-60°	310.5	12.7
60°-70°	181.4	7.4
70°-80°	67.4	2.7
80°-90°	8.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	954.7	38.9
0°-40°	1458.1	59.4
0°-60°	2195.3	89.5
0°-90°	2452.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2452.9	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1287	1287	1287	1287	1287	
5°	1316	1305	1282	1263	1258	126
15°	1341	1300	1215	1164	1153	377
25°	1202	1135	1026	990	988	550
35°	879	841	775	777	782	549
45°	571	555	532	552	564	444
55°	364	347	334	345	348	328
65°	213	195	178	166	166	211
75°	94	78	54	43	45	101
85°	13	8	3	3	3	18
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580143

CATALOG NUMBER: HCC4S25D010MB-HM40525830-41RWWH

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1286.9	1286.9	1286.9	1286.9	1286.9	1286.9	1286.9	1286.9	1286.9
2.5°	1298.1	1295.0	1291.7	1286.9	1280.5	1275.8	1270.9	1267.8	1267.8
5°	1315.7	1310.9	1304.6	1293.3	1282.1	1272.5	1262.9	1258.2	1258.2
7.5°	1328.5	1322.1	1309.3	1293.3	1274.2	1259.7	1245.4	1239.0	1235.8
10°	1330.1	1323.6	1306.1	1282.1	1256.6	1234.2	1218.2	1208.6	1207.0
12.5°	1333.2	1325.3	1302.9	1269.3	1235.8	1208.6	1191.0	1181.4	1178.2
15°	1341.3	1330.1	1299.7	1256.6	1215.0	1183.0	1163.8	1155.9	1152.6
17.5°	1333.2	1317.3	1280.5	1229.4	1183.0	1147.9	1128.7	1120.6	1120.6
20°	1301.3	1285.4	1242.1	1186.2	1136.7	1103.0	1083.8	1079.1	1075.9
22.5°	1256.6	1239.0	1192.6	1133.4	1083.8	1053.5	1040.7	1034.4	1032.7
25°	1202.2	1184.7	1135.1	1074.4	1026.4	1000.7	989.6	989.6	988.0
27.5°	1141.4	1119.1	1067.9	1015.2	968.8	949.6	944.9	944.9	946.4
30°	1056.7	1040.7	997.6	946.4	903.2	890.4	890.4	893.6	893.6
32.5°	965.6	954.5	916.1	871.2	837.7	829.7	832.9	839.3	840.9
35°	879.3	866.5	840.9	800.9	775.4	772.1	777.0	781.7	781.7
37.5°	794.6	781.7	764.1	732.2	713.0	714.7	721.0	727.4	732.2
40°	711.4	701.8	689.0	663.4	649.1	655.5	663.4	669.8	676.3
42.5°	637.9	628.3	618.7	599.5	589.9	597.9	607.5	613.8	620.3
45°	570.7	564.3	554.8	538.8	532.3	540.3	551.5	558.0	564.3
47.5°	513.1	510.0	497.2	482.8	479.6	487.6	497.2	505.2	510.0
50°	460.4	455.7	444.4	430.0	426.9	439.6	446.1	450.8	455.7
52.5°	409.3	404.4	391.7	378.9	378.9	388.5	393.2	394.9	399.7
55°	364.4	359.7	346.9	337.3	334.1	342.1	345.4	345.4	348.5
57.5°	322.9	318.2	305.4	294.1	292.5	297.4	297.4	297.4	299.0
60°	282.9	278.2	265.4	255.8	252.6	254.1	252.6	251.0	252.6
62.5°	246.2	241.4	228.6	217.4	214.2	214.2	209.4	207.8	209.4
65°	212.6	204.6	195.1	183.8	177.5	172.6	166.3	166.3	166.3
67.5°	179.1	172.6	161.4	150.3	142.3	134.2	124.6	127.9	129.5
70°	148.7	143.8	131.1	119.9	108.7	99.1	91.1	94.3	96.0
72.5°	121.5	115.2	103.9	91.1	81.5	68.8	63.9	67.2	67.2
75°	94.3	87.9	78.4	65.6	54.3	43.1	43.1	44.7	44.7
77.5°	70.3	63.9	54.3	43.1	33.5	25.6	27.2	27.2	27.2
80°	48.0	43.1	35.2	25.6	17.6	14.3	14.3	14.3	16.0
82.5°	27.2	23.9	19.2	12.8	8.0	8.0	8.0	8.0	8.0
85°	12.8	9.6	8.0	4.7	3.2	3.2	3.2	3.2	3.2
87.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)