

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580144

Luminaire Tested: **HCC4S25D010MB-HM40525830-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580144
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S25D010MB-HM40525830-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1941.2 lumens
Efficiency: N/A
Efficacy: 72.4 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580144
CATALOG NUMBER: HCC4S25D010MB-HM40525830-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580144

CATALOG NUMBER: HCC4S25D010MB-HM40525830-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	138616	138616	138616
5°	146859	138155	131233
10°	152978	135945	123545
15°	158816	132690	116153
20°	160323	126326	107438
25°	155123	116839	98344
30°	145048	105866	89487
35°	129271	94111	80393
40°	113001	81861	71556
45°	98435	69443	61890
50°	85891	58911	53077
55°	75288	48816	42966
60°	65867	39446	31552
65°	57409	29390	17716
70°	50165	19006	5770
75°	41176	9913	1525
80°	30615	4546	1137
85°	18115	2264	2264



TEST NUMBER: P580144
 CATALOG NUMBER: HCC4S25D010MB-HM40525830-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.1	5.5
10°-20°	296.9	15.3
20°-30°	410.4	21.1
30°-40°	412.7	21.3
40°-50°	333.0	17.2
50°-60°	225.2	11.6
60°-70°	114.6	5.9
70°-80°	36.7	1.9
80°-90°	5.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	813.4	41.9
0°-40°	1226.1	63.2
0°-60°	1784.3	91.9
0°-90°	1941.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1941.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1124	1124	1124	1124	1124	
5°	1186	1164	1116	1076	1060	114
15°	1244	1177	1039	940	910	350
25°	1140	1041	858	753	723	522
35°	858	775	625	547	534	536
45°	564	505	398	355	355	437
55°	350	302	227	198	200	315
65°	197	160	101	66	61	197
75°	86	61	21	5	3	93
85°	13	6	2	2	2	17
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580144

CATALOG NUMBER: HCC4S25D010MB-HM40525830-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1123.8	1123.8	1123.8	1123.8	1123.8	1123.8	1123.8	1123.8	1123.8
2.5°	1154.2	1147.9	1141.4	1130.2	1117.5	1104.6	1096.7	1090.3	1087.1
5°	1186.1	1178.2	1163.8	1139.8	1115.8	1093.4	1075.8	1064.6	1059.9
7.5°	1211.8	1200.6	1176.6	1143.0	1106.3	1071.1	1048.7	1032.7	1026.4
10°	1221.4	1208.6	1176.6	1131.8	1085.4	1042.3	1010.3	994.3	986.4
12.5°	1232.5	1218.2	1178.2	1122.2	1064.6	1013.5	976.8	955.9	948.0
15°	1243.7	1224.5	1176.6	1107.9	1039.1	980.0	940.0	919.2	909.6
17.5°	1243.7	1221.4	1163.8	1083.8	1005.5	943.2	898.5	874.4	866.5
20°	1221.4	1195.7	1133.4	1045.5	962.4	895.2	852.1	828.1	818.5
22.5°	1186.1	1157.5	1090.3	999.2	911.2	845.6	802.5	780.1	770.5
25°	1139.8	1111.0	1040.7	946.4	858.5	792.9	752.9	732.2	722.6
27.5°	1085.4	1053.5	983.1	888.9	802.5	740.2	703.4	684.2	676.3
30°	1018.4	988.0	919.2	826.5	743.3	685.9	652.2	634.6	628.3
32.5°	940.0	914.4	847.3	760.9	682.6	629.9	599.5	585.0	578.7
35°	858.5	834.4	775.3	695.4	625.0	575.5	546.8	537.2	533.9
37.5°	781.7	760.9	703.4	629.9	566.0	522.7	497.2	490.8	487.6
40°	701.8	687.4	634.6	567.5	508.4	470.0	449.2	444.4	444.4
42.5°	629.9	613.8	567.5	506.8	454.0	415.7	401.2	396.5	398.1
45°	564.3	548.4	505.1	449.2	398.1	366.1	354.8	354.8	354.8
47.5°	503.5	489.2	449.2	391.7	350.1	324.5	313.3	313.3	314.9
50°	447.6	438.1	393.2	343.7	307.0	282.9	274.9	273.3	276.6
52.5°	394.8	383.6	343.7	299.0	263.7	244.5	236.6	234.9	236.6
55°	350.1	337.3	302.1	259.0	227.0	207.8	198.3	196.7	199.8
57.5°	307.0	297.4	260.6	222.2	191.8	172.6	164.6	161.4	163.0
60°	267.0	257.4	223.8	187.1	159.9	140.7	129.5	126.3	127.9
62.5°	230.2	222.2	190.2	155.0	127.9	110.3	99.1	91.1	94.3
65°	196.7	188.7	159.9	124.6	100.7	81.5	65.6	59.2	60.7
67.5°	167.9	158.3	131.1	99.1	75.2	54.3	36.8	33.5	33.5
70°	139.1	129.5	105.6	76.8	52.7	28.8	16.0	16.0	16.0
72.5°	111.9	103.9	81.5	57.6	33.5	12.8	6.4	6.4	6.4
75°	86.4	79.9	60.7	40.0	20.8	6.4	4.7	3.2	3.2
77.5°	63.9	57.6	43.1	27.2	12.8	3.2	3.2	3.2	3.2
80°	43.1	38.4	28.8	16.0	6.4	1.6	1.6	1.6	1.6
82.5°	25.6	22.4	16.0	8.0	3.2	1.6	1.6	1.6	1.6
85°	12.8	9.6	6.4	3.2	1.6	1.6	1.6	1.6	1.6
87.5°	3.2	1.6	1.6	1.6	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)