

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580180

Luminaire Tested: **HCC4W25D010MW-HM40525840-41WWBB**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580180  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W25D010MW-HM40525840-41WWBB  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2067.7 lumens  
Efficiency: N/A  
Efficacy: 77.2 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580180  
CATALOG NUMBER: HCC4W25D010MW-HM40525840-41WWBB

### Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580180

CATALOG NUMBER: HCC4W25D010MW-HM40525840-41WWBB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	147657	147657	147657
5°	156443	147169	139789
10°	162936	144812	131586
15°	169173	141348	123725
20°	170758	134556	114434
25°	165235	124447	104740
30°	154477	112774	95312
35°	137688	100254	85648
40°	120360	87190	76225
45°	104854	73979	65937
50°	91494	62749	56531
55°	80191	51998	45762
60°	70159	42012	33624
65°	61116	31317	18883
70°	53411	20268	6131
75°	43797	10532	1620
80°	32675	4830	1208
85°	19389	2406	2406



TEST NUMBER: P580180  
 CATALOG NUMBER: HCC4W25D010MW-HM40525840-41WWBB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	113.0	5.5
10°-20°	316.2	15.3
20°-30°	437.2	21.1
30°-40°	439.6	21.3
40°-50°	354.7	17.2
50°-60°	239.8	11.6
60°-70°	122.1	5.9
70°-80°	39.1	1.9
80°-90°	6.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	866.4	41.9
0°-40°	1306.0	63.2
0°-60°	1900.5	91.9
0°-90°	2067.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2067.7	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1197	1197	1197	1197	1197	
5°	1264	1240	1189	1146	1129	122
15°	1325	1253	1107	1001	969	373
25°	1214	1109	914	802	770	556
35°	914	826	666	582	569	571
45°	601	538	424	378	378	466
55°	373	322	242	211	213	335
65°	209	170	107	70	65	210
75°	92	65	22	5	3	99
85°	14	7	2	2	2	18
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580180

CATALOG NUMBER: HCC4W25D010MW-HM40525840-41WWBB

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1197.1	1197.1	1197.1	1197.1	1197.1	1197.1	1197.1	1197.1	1197.1
2.5°	1229.4	1222.6	1215.8	1203.9	1190.3	1176.6	1168.2	1161.3	1157.9
5°	1263.5	1255.0	1239.6	1214.1	1188.6	1164.7	1145.9	1134.1	1129.0
7.5°	1290.7	1278.8	1253.3	1217.5	1178.3	1140.9	1117.0	1100.0	1093.2
10°	1300.9	1287.3	1253.3	1205.5	1156.2	1110.3	1076.2	1059.1	1050.6
12.5°	1312.9	1297.6	1255.0	1195.4	1134.1	1079.5	1040.4	1018.2	1009.8
15°	1324.8	1304.3	1253.3	1180.0	1106.9	1043.9	1001.2	979.1	968.9
17.5°	1324.8	1300.9	1239.6	1154.5	1071.1	1004.7	956.9	931.4	923.0
20°	1300.9	1273.7	1207.2	1113.6	1025.1	953.6	907.6	882.1	871.8
22.5°	1263.5	1232.9	1161.3	1064.2	970.6	900.8	854.8	830.9	820.8
25°	1214.1	1183.4	1108.6	1008.1	914.4	844.6	802.0	779.9	769.6
27.5°	1156.2	1122.1	1047.3	946.8	854.8	788.4	749.2	728.8	720.3
30°	1084.6	1052.3	979.1	880.4	791.8	730.5	694.8	676.0	669.2
32.5°	1001.2	974.0	902.5	810.5	727.1	670.9	638.6	623.2	616.4
35°	914.4	888.9	825.9	740.7	665.8	613.0	582.3	572.2	568.8
37.5°	832.6	810.5	749.2	670.9	602.8	556.8	529.6	522.7	519.3
40°	747.5	732.2	676.0	604.5	541.5	500.6	478.5	473.4	473.4
42.5°	670.9	653.9	604.5	539.8	483.6	442.7	427.4	422.2	424.1
45°	601.1	584.0	538.1	478.5	424.1	390.0	378.0	378.0	378.0
47.5°	536.4	521.0	478.5	417.2	372.9	345.7	333.7	333.7	335.4
50°	476.8	466.6	418.9	366.1	327.0	301.4	292.9	291.2	294.6
52.5°	420.6	408.7	366.1	318.4	281.0	260.6	252.0	250.3	252.0
55°	372.9	359.2	321.9	275.8	241.8	221.4	211.1	209.4	212.8
57.5°	327.0	316.7	277.5	236.6	204.3	183.9	175.3	171.9	173.6
60°	284.4	274.1	238.4	199.3	170.3	149.8	138.0	134.6	136.3
62.5°	245.2	236.6	202.7	165.2	136.3	117.5	105.6	97.1	100.5
65°	209.4	201.0	170.3	132.8	107.3	86.8	69.8	63.0	64.7
67.5°	178.8	168.6	139.7	105.6	80.0	57.9	39.2	35.8	35.8
70°	148.1	138.0	112.3	81.7	56.2	30.6	17.0	17.0	17.0
72.5°	119.2	110.6	86.8	61.3	35.8	13.7	6.8	6.8	6.8
75°	91.9	85.1	64.7	42.6	22.1	6.8	5.1	3.4	3.4
77.5°	68.1	61.3	46.0	28.9	13.7	3.4	3.4	3.4	3.4
80°	46.0	40.9	30.6	17.0	6.8	1.7	1.7	1.7	1.7
82.5°	27.2	23.8	17.0	8.5	3.4	1.7	1.7	1.7	1.7
85°	13.7	10.2	6.8	3.4	1.7	1.7	1.7	1.7	1.7
87.5°	3.4	1.7	1.7	1.7	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)