

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580200

Luminaire Tested: **HCC4S25D010MW-HM40525927-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580200
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S25D010MW-HM40525927-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1908.5 lumens
Efficiency: N/A
Efficacy: 71.2 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580200
CATALOG NUMBER: HCC4S25D010MW-HM40525927-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580200

CATALOG NUMBER: HCC4S25D010MW-HM40525927-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	121372	121372	121372
5°	127630	121229	116685
10°	132112	119775	111383
15°	136150	117596	106627
20°	136315	112767	100494
25°	131170	105393	94220
30°	121804	96979	87992
35°	109199	87320	81417
40°	95805	77900	75259
45°	83747	68972	69426
50°	73936	60350	62538
55°	65181	53504	56235
60°	58268	47365	49240
65°	51601	41649	41649
70°	45116	35559	35559
75°	38507	30072	33741
80°	30473	26921	30473
85°	19672	23210	28588



TEST NUMBER: P580200

CATALOG NUMBER: HCC4S25D010MW-HM40525927-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.2	4.9
10°-20°	262.6	13.8
20°-30°	367.8	19.3
30°-40°	379.0	19.9
40°-50°	322.7	16.9
50°-60°	239.1	12.5
60°-70°	150.0	7.9
70°-80°	74.5	3.9
80°-90°	19.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.6	37.9
0°-40°	1102.6	57.8
0°-60°	1664.3	87.2
0°-90°	1908.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1908.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	984	984	984	984	984	
5°	1031	1013	979	951	942	99
15°	1066	1018	921	854	835	300
25°	964	897	774	707	692	441
35°	725	671	580	542	541	452
45°	480	447	395	388	398	373
55°	303	279	249	254	262	274
65°	177	159	143	140	143	176
75°	81	72	63	68	71	86
85°	14	14	16	19	20	18
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580200

CATALOG NUMBER: HCC4S25D010MW-HM40525927-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	984.0	984.0	984.0	984.0	984.0	984.0	984.0	984.0	984.0
2.5°	1005.6	1001.8	996.7	987.9	979.1	971.5	963.8	960.1	958.9
5°	1030.8	1023.2	1013.2	996.7	979.1	963.8	951.2	945.0	942.4
7.5°	1048.5	1040.9	1024.5	999.3	974.0	951.2	931.0	922.2	919.7
10°	1054.8	1046.0	1023.2	989.1	956.3	928.5	905.8	894.4	889.3
12.5°	1059.9	1048.5	1019.5	979.1	938.7	904.4	880.5	865.4	861.5
15°	1066.2	1053.6	1018.2	968.9	920.9	880.5	854.0	840.1	835.0
17.5°	1059.9	1046.0	1004.2	948.7	894.4	850.1	821.1	808.5	803.4
20°	1038.5	1023.2	976.5	917.1	859.1	813.6	784.5	771.9	765.6
22.5°	1005.6	989.1	941.1	878.0	818.6	774.4	746.6	734.0	730.1
25°	963.8	947.5	896.9	832.5	774.4	731.5	707.4	696.0	692.3
27.5°	914.6	898.2	848.9	785.8	730.1	689.7	670.7	659.4	656.9
30°	855.2	838.8	790.8	732.7	680.9	643.0	627.8	619.0	617.8
32.5°	789.5	775.6	731.5	678.4	629.1	597.6	586.2	579.9	578.6
35°	725.2	709.9	670.7	622.8	579.9	552.1	541.9	540.7	540.7
37.5°	659.4	644.3	612.7	568.5	531.9	506.6	502.7	504.1	504.1
40°	595.0	581.1	553.3	516.6	483.8	464.9	463.6	466.2	467.4
42.5°	534.4	523.0	497.8	466.2	438.4	423.1	424.5	429.5	433.3
45°	480.1	469.9	447.2	419.4	395.4	384.1	387.8	394.1	398.0
47.5°	430.8	421.9	400.5	375.2	355.0	347.4	352.5	360.0	365.1
50°	385.3	377.8	357.6	331.0	314.5	309.5	315.8	323.3	325.9
52.5°	344.9	337.3	315.8	293.1	280.4	278.0	284.3	290.6	294.3
55°	303.1	296.8	279.2	259.0	248.8	247.6	253.9	259.0	261.5
57.5°	269.0	262.7	246.3	228.6	219.8	218.6	224.9	228.6	229.9
60°	236.2	229.9	214.7	198.4	192.0	192.0	195.8	198.4	199.6
62.5°	205.9	199.6	185.7	171.8	166.8	166.8	166.8	168.0	171.8
65°	176.8	171.8	159.2	146.5	142.7	140.2	140.2	140.2	142.7
67.5°	150.4	145.3	135.1	123.9	120.0	116.2	114.9	117.5	117.5
70°	125.1	121.3	111.2	102.3	98.6	94.7	93.5	98.6	98.6
72.5°	102.3	98.6	92.2	83.3	79.6	78.4	80.8	83.3	84.7
75°	80.8	77.1	72.0	66.9	63.1	64.5	68.2	69.4	70.8
77.5°	60.6	59.4	54.3	50.6	50.6	51.8	54.3	56.9	58.1
80°	42.9	41.7	39.2	36.6	37.9	40.4	41.7	44.3	42.9
82.5°	26.5	26.5	25.3	25.3	26.5	29.0	30.4	31.6	32.9
85°	13.9	13.9	13.9	15.1	16.4	17.7	19.0	20.2	20.2
87.5°	3.8	5.1	5.1	6.3	7.6	7.6	8.8	8.8	8.8
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)