

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580196

Luminaire Tested: **HCC4S25D010SL-HM40525927-41RWWC**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580196
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S25D010SL-HM40525927-41RWWC
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1947.6 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580196
CATALOG NUMBER: HCC4S25D010SL-HM40525927-41RWWC

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580196

CATALOG NUMBER: HCC4S25D010SL-HM40525927-41RWWC

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88								
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76								
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52								
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46								
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41								
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37								
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	115279	115279	115279
5°	119941	116351	115100
10°	123858	117383	114853
15°	128220	117749	114825
20°	128650	114893	113397
25°	124107	109150	110021
30°	115480	101636	104513
35°	104019	92996	96430
40°	91715	84598	88462
45°	80189	76229	79979
50°	71019	68582	72228
55°	62471	60579	63009
60°	55752	51731	53285
65°	49033	41999	41298
70°	42844	30979	28274
75°	35505	18682	15060
80°	26921	7103	4475
85°	12454	1698	1698



TEST NUMBER: P580196

CATALOG NUMBER: HCC4S25D010SL-HM40525927-41RWWC

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.1	4.6
10°-20°	263.1	13.5
20°-30°	381.0	19.6
30°-40°	402.0	20.6
40°-50°	347.9	17.9
50°-60°	257.7	13.2
60°-70°	148.6	7.6
70°-80°	51.9	2.7
80°-90°	5.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	734.2	37.7
0°-40°	1136.2	58.3
0°-60°	1741.7	89.4
0°-90°	1947.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1947.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	935	935	935	935	935	
5°	969	956	940	932	930	93
15°	1004	971	922	900	899	282
25°	912	866	802	797	808	417
35°	691	659	618	631	640	431
45°	460	447	437	453	458	357
55°	290	284	282	292	293	262
65°	168	158	144	136	142	168
75°	74	63	39	32	32	80
85°	9	5	1	1	1	14
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580196

CATALOG NUMBER: HCC4S25D010SL-HM40525927-41RWWC

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	934.6	934.6	934.6	934.6	934.6	934.6	934.6	934.6	934.6
2.5°	948.5	946.0	942.2	937.2	932.1	928.3	927.0	925.8	925.8
5°	968.7	963.7	956.2	946.0	939.7	935.9	932.1	929.6	929.6
7.5°	982.6	977.6	966.2	952.3	943.5	935.9	930.9	927.0	927.0
10°	988.9	982.6	968.7	951.1	937.2	927.0	919.5	917.0	917.0
12.5°	996.6	988.9	970.0	947.2	929.6	917.0	909.4	906.8	906.8
15°	1004.1	995.2	971.3	944.7	922.1	906.8	900.5	899.2	899.2
17.5°	1000.3	988.9	961.1	929.6	904.3	889.2	882.9	882.9	884.1
20°	980.1	968.7	937.2	901.8	875.3	863.9	858.8	861.4	863.9
22.5°	949.8	935.9	901.8	867.6	839.9	829.8	829.8	833.5	837.4
25°	911.9	899.2	866.4	828.6	802.0	794.5	797.0	803.3	808.4
27.5°	869.0	855.1	821.0	785.6	759.0	755.3	761.6	770.4	772.9
30°	810.8	799.4	770.4	736.3	713.6	712.3	721.2	727.5	733.8
32.5°	755.3	742.7	714.9	682.0	665.7	666.9	676.9	684.5	688.4
35°	690.8	679.5	659.3	632.8	617.6	620.2	631.4	639.1	640.4
37.5°	630.2	622.6	602.4	582.2	570.9	575.9	586.1	594.9	594.9
40°	569.6	563.3	548.1	531.8	525.4	531.8	541.8	549.4	549.4
42.5°	511.5	507.7	495.1	483.8	479.9	488.7	497.7	504.0	502.6
45°	459.7	456.0	447.1	438.3	437.0	445.8	453.4	457.2	458.5
47.5°	413.0	410.5	402.9	396.6	396.6	405.4	411.7	415.6	416.8
50°	370.1	367.5	361.2	356.2	357.4	366.2	371.3	375.2	376.4
52.5°	327.1	325.8	320.7	314.5	318.3	324.6	330.9	333.4	334.7
55°	290.5	290.5	284.2	279.1	281.7	288.0	291.7	293.0	293.0
57.5°	257.6	256.4	248.8	243.8	245.0	251.3	253.9	255.2	255.2
60°	226.0	224.8	217.2	209.7	209.7	213.5	214.7	216.0	216.0
62.5°	195.8	194.5	185.6	179.4	176.8	175.6	175.6	178.0	183.1
65°	168.0	166.8	157.8	147.8	143.9	140.2	136.4	139.0	141.5
67.5°	142.7	140.2	131.3	122.5	113.7	107.4	101.0	104.9	109.9
70°	118.8	116.2	106.1	96.0	85.9	75.8	70.7	75.8	78.4
72.5°	96.0	93.5	83.3	73.3	60.6	50.5	49.2	50.5	51.8
75°	74.5	73.3	63.1	51.8	39.2	31.6	31.6	31.6	31.6
77.5°	55.5	53.1	42.9	32.9	22.7	17.7	16.4	16.4	16.4
80°	37.9	35.3	26.5	19.0	10.0	7.6	7.6	6.3	6.3
82.5°	21.5	20.2	13.9	7.6	3.8	2.5	2.5	2.5	2.5
85°	8.8	7.6	5.1	2.5	1.2	1.2	1.2	1.2	1.2
87.5°	1.2	1.2	1.2	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)