

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580197

Luminaire Tested: **HCC4W25D010MB-HM40525927-41RWWH**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580197
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-15)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MB-HM40525927-41RWWH
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, HAZE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1937.5 lumens
Efficiency: N/A
Efficacy: 72.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.08 / 1.16
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580197
CATALOG NUMBER: HCC4W25D010MB-HM40525927-41RWWH

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580197

CATALOG NUMBER: HCC4W25D010MB-HM40525927-41RWWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88					88			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77					77			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67					67			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59					59			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52					52			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47					47			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42					42			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38					38			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35					35			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32					32			

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	125393	125393	125393
5°	128670	125389	123037
10°	131586	124309	119412
15°	135295	122538	116255
20°	134911	117847	111546
25°	129238	110334	106210
30°	118884	101608	100539
35°	104591	92229	92981
40°	90475	82553	85999
45°	78636	73368	77747
50°	69791	64687	69062
55°	61912	56772	59202
60°	55135	49215	49215
65°	49033	40919	38321
70°	42339	30979	27336
75°	35505	20445	16823
80°	26921	9873	8950
85°	14152	3538	3538



TEST NUMBER: P580197

CATALOG NUMBER: HCC4W25D010MB-HM40525927-41RWWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.3	5.0
10°-20°	272.9	14.1
20°-30°	384.9	19.9
30°-40°	397.6	20.5
40°-50°	337.1	17.4
50°-60°	245.2	12.7
60°-70°	143.3	7.4
70°-80°	53.3	2.7
80°-90°	6.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.1	38.9
0°-40°	1151.7	59.4
0°-60°	1734.0	89.5
0°-90°	1937.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1937.5	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1017	1017	1017	1017	1017	
5°	1039	1030	1013	998	994	100
15°	1060	1027	960	919	910	298
25°	950	896	811	782	780	434
35°	695	664	612	614	618	434
45°	451	438	421	436	446	351
55°	288	274	264	273	275	259
65°	168	154	140	131	131	167
75°	74	62	43	34	35	80
85°	10	6	2	2	2	14
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580197

CATALOG NUMBER: HCC4W25D010MB-HM40525927-41RWWH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1016.6	1016.6	1016.6	1016.6	1016.6	1016.6	1016.6	1016.6	1016.6
2.5°	1025.4	1022.9	1020.3	1016.6	1011.5	1007.7	1003.9	1001.4	1001.4
5°	1039.2	1035.5	1030.4	1021.6	1012.7	1005.1	997.6	993.7	993.7
7.5°	1049.4	1044.3	1034.2	1021.6	1006.4	995.1	983.7	978.6	976.1
10°	1050.6	1045.6	1031.7	1012.7	992.5	974.9	962.2	954.7	953.4
12.5°	1053.1	1046.8	1029.2	1002.7	976.1	954.7	940.8	933.2	930.6
15°	1059.5	1050.6	1026.6	992.5	959.6	934.5	919.3	913.0	910.4
17.5°	1053.1	1040.5	1011.5	971.1	934.5	906.7	891.6	885.2	885.2
20°	1027.8	1015.3	981.2	937.0	897.8	871.4	856.1	852.4	849.8
22.5°	992.5	978.6	942.0	895.3	856.1	832.2	822.0	817.1	815.7
25°	949.6	935.7	896.5	848.6	810.7	790.5	781.6	781.6	780.4
27.5°	901.6	883.9	843.5	801.8	765.2	750.1	746.3	746.3	747.5
30°	834.7	822.0	787.9	747.5	713.4	703.4	703.4	705.9	705.9
32.5°	762.8	753.8	723.6	688.2	661.7	655.4	657.9	662.9	664.2
35°	694.6	684.4	664.2	632.7	612.5	609.9	613.7	617.5	617.5
37.5°	627.6	617.5	603.6	578.4	563.1	564.5	569.5	574.5	578.4
40°	561.9	554.3	544.3	524.1	512.7	517.8	524.1	529.0	534.1
42.5°	503.9	496.3	488.7	473.5	465.9	472.3	479.8	484.9	490.0
45°	450.8	445.7	438.2	425.5	420.6	426.8	435.7	440.8	445.7
47.5°	405.3	402.8	392.7	381.4	378.8	385.1	392.7	399.0	402.8
50°	363.7	359.9	351.0	339.7	337.1	347.3	352.4	356.1	359.9
52.5°	323.2	319.5	309.3	299.3	299.3	306.9	310.6	311.9	315.7
55°	287.9	284.2	274.0	266.4	264.0	270.3	272.8	272.8	275.3
57.5°	255.0	251.3	241.2	232.3	231.1	234.8	234.8	234.8	236.2
60°	223.5	219.7	209.7	202.1	199.5	200.7	199.5	198.3	199.5
62.5°	194.4	190.7	180.5	171.7	169.2	169.2	165.4	164.2	165.4
65°	168.0	161.7	154.1	145.2	140.2	136.4	131.3	131.3	131.3
67.5°	141.5	136.4	127.6	118.7	112.3	106.1	98.4	101.0	102.3
70°	117.4	113.7	103.5	94.7	85.9	78.2	72.0	74.5	75.8
72.5°	96.0	90.9	82.1	72.0	64.4	54.3	50.5	53.1	53.1
75°	74.5	69.4	61.9	51.8	42.9	34.1	34.1	35.3	35.3
77.5°	55.5	50.5	42.9	34.1	26.5	20.2	21.5	21.5	21.5
80°	37.9	34.1	27.8	20.2	13.9	11.4	11.4	11.4	12.6
82.5°	21.5	19.0	15.1	10.0	6.3	6.3	6.3	6.3	6.3
85°	10.0	7.6	6.3	3.8	2.5	2.5	2.5	2.5	2.5
87.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)