

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580199

Luminaire Tested: **HCC4W25D010SL-HM40525927-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010SL-HM40525927-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1917.3 lumens
Efficiency: N/A
Efficacy: 71.5 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580199
CATALOG NUMBER: HCC4W25D010SL-HM40525927-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580199

CATALOG NUMBER: HCC4W25D010SL-HM40525927-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	132436	132436	132436
5°	138254	131840	125736
10°	141744	129094	117859
15°	144693	125641	109347
20°	143915	119540	100140
25°	137880	110538	91117
30°	127373	100924	82565
35°	111638	89774	74747
40°	97222	79317	67321
45°	84602	69182	60146
50°	75375	59621	53077
55°	67374	52428	45912
60°	60143	45811	39569
65°	53440	40160	37592
70°	46919	34621	35054
75°	39698	29500	32502
80°	30473	25074	29620
85°	17832	19672	25050



TEST NUMBER: P580199
 CATALOG NUMBER: HCC4W25D010SL-HM40525927-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.6	5.2
10°-20°	277.6	14.5
20°-30°	379.3	19.8
30°-40°	380.8	19.9
40°-50°	315.0	16.4
50°-60°	228.3	11.9
60°-70°	144.6	7.5
70°-80°	73.1	3.8
80°-90°	17.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	757.5	39.5
0°-40°	1138.3	59.4
0°-60°	1681.7	87.7
0°-90°	1917.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1917.3	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1074	1074	1074	1074	1074	
5°	1117	1100	1065	1029	1016	107
15°	1133	1089	984	893	856	319
25°	1013	946	812	710	670	463
35°	741	697	596	523	496	465
45°	485	457	397	357	345	377
55°	313	285	244	222	214	282
65°	183	163	138	124	129	182
75°	83	72	62	64	68	89
85°	13	13	14	16	18	17
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580199

CATALOG NUMBER: HCC4W25D010SL-HM40525927-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1073.7	1073.7	1073.7	1073.7	1073.7	1073.7	1073.7	1073.7	1073.7
2.5°	1093.9	1090.0	1083.7	1076.2	1067.4	1057.2	1048.4	1043.3	1040.8
5°	1116.6	1111.5	1100.2	1083.7	1064.8	1045.9	1029.4	1019.4	1015.5
7.5°	1130.5	1122.9	1106.5	1081.2	1052.2	1024.3	1000.4	986.5	982.7
10°	1131.7	1122.9	1101.5	1067.4	1030.7	994.1	965.1	944.9	941.0
12.5°	1133.1	1121.7	1095.1	1054.7	1009.2	963.7	928.4	904.4	898.1
15°	1133.1	1121.7	1088.8	1040.8	983.9	932.2	893.0	865.3	856.3
17.5°	1122.9	1110.3	1071.1	1015.5	953.7	895.5	850.0	821.0	812.2
20°	1096.4	1082.5	1038.2	977.6	910.7	850.0	804.6	774.3	762.9
22.5°	1058.4	1042.1	995.3	929.6	862.7	800.8	756.7	725.0	714.9
25°	1013.1	996.6	946.1	881.6	812.2	754.1	709.9	680.8	669.5
27.5°	957.4	939.8	890.4	826.1	761.6	703.6	663.2	636.6	625.2
30°	894.3	875.3	828.6	766.7	708.6	653.0	613.8	592.4	579.7
32.5°	821.0	804.6	762.9	707.3	653.0	600.0	567.1	548.2	538.1
35°	741.4	732.6	697.3	649.3	596.2	552.0	523.0	505.2	496.4
37.5°	670.7	661.8	631.6	591.1	544.4	504.0	479.9	464.8	457.2
40°	603.8	596.2	567.1	533.0	492.6	457.2	437.0	425.6	418.1
42.5°	538.1	534.2	510.3	478.7	443.4	413.0	396.6	387.8	381.5
45°	485.0	479.9	457.2	427.0	396.6	371.3	357.4	351.1	344.8
47.5°	438.3	432.0	408.0	381.5	353.7	330.9	318.3	311.9	309.5
50°	392.8	386.5	365.0	338.5	310.7	294.3	284.2	277.8	276.6
52.5°	352.4	346.0	322.1	296.8	275.4	261.5	252.7	246.3	243.8
55°	313.3	305.6	285.4	261.5	243.8	231.1	222.3	216.0	213.5
57.5°	277.8	270.3	252.7	229.9	213.5	202.1	194.5	188.2	185.7
60°	243.8	237.4	221.1	199.6	185.7	175.6	168.0	162.9	160.4
62.5°	212.3	207.2	190.7	171.8	160.4	151.6	145.3	140.2	142.7
65°	183.1	178.0	162.9	146.5	137.6	128.8	123.7	123.7	128.8
67.5°	155.4	150.3	137.6	123.7	116.2	109.9	106.1	109.9	113.7
70°	130.1	125.1	113.7	102.3	96.0	91.0	91.0	94.7	97.2
72.5°	106.1	101.0	92.2	83.3	78.4	74.5	78.4	80.8	83.3
75°	83.3	79.6	72.0	65.7	61.9	60.6	64.5	66.9	68.2
77.5°	61.9	59.4	54.3	49.2	46.7	48.0	51.8	53.1	54.3
80°	42.9	41.7	37.9	35.3	35.3	36.6	39.2	40.4	41.7
82.5°	26.5	26.5	24.0	22.7	24.0	26.5	27.8	29.0	29.0
85°	12.6	13.9	12.6	12.6	13.9	16.4	16.4	17.7	17.7
87.5°	3.8	3.8	5.1	5.1	6.3	6.3	6.3	6.3	7.6
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)