

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580217

Luminaire Tested: **HCC4S25D010MB-HM40525930-41WWW**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4S25D010MB-HM40525930-41WWW
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2133.1 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.03 / 1.1
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580217
CATALOG NUMBER: HCC4S25D010MB-HM40525930-41WWW

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580217

CATALOG NUMBER: HCC4S25D010MB-HM40525930-41WWW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	106	103	100	108	104	101	98	100	97	95	96	94	92	93	91	89	87								
2	102	95	89	84	100	93	88	83	90	85	81	87	83	80	84	81	78	76								
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66								
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58								
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52								
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47								
7	71	58	50	45	69	58	50	45	56	49	44	55	49	44	53	48	44	42								
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38								
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35								
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	147336	147336	147336
5°	153805	146686	139901
10°	157713	143622	131123
15°	160962	139790	121670
20°	160113	133007	111415
25°	153395	122991	101365
30°	141715	112290	91866
35°	124226	99878	83164
40°	108171	88237	74889
45°	94144	76962	66914
50°	83857	66337	59064
55°	74944	58321	51074
60°	66903	50966	44034
65°	59481	44713	41853
70°	52184	38516	39021
75°	44226	32836	36172
80°	33953	27987	32959
85°	19813	21936	27739



TEST NUMBER: P580217
 CATALOG NUMBER: HCC4S25D010MB-HM40525930-41WWW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	112.0	5.2
10°-20°	308.8	14.5
20°-30°	422.0	19.8
30°-40°	423.7	19.9
40°-50°	350.5	16.4
50°-60°	254.0	11.9
60°-70°	160.9	7.5
70°-80°	81.3	3.8
80°-90°	19.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	842.8	39.5
0°-40°	1266.5	59.4
0°-60°	1871.0	87.7
0°-90°	2133.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2133.1	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1194	1194	1194	1194	1194	
5°	1242	1224	1185	1145	1130	119
15°	1260	1211	1095	994	953	355
25°	1127	1053	904	790	745	515
35°	825	776	663	582	552	517
45°	540	509	441	398	384	420
55°	348	318	271	247	238	313
65°	204	181	153	138	143	203
75°	93	80	69	72	76	99
85°	14	14	16	18	20	19
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580217

CATALOG NUMBER: HCC4S25D010MB-HM40525930-41WWW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5	1194.5
2.5°	1216.9	1212.8	1205.8	1197.3	1187.5	1176.2	1166.4	1160.7	1158.0
5°	1242.2	1236.7	1224.1	1205.8	1184.7	1163.5	1145.4	1134.1	1129.9
7.5°	1257.7	1249.4	1231.1	1202.9	1170.7	1139.7	1113.0	1097.5	1093.3
10°	1259.2	1249.4	1225.4	1187.5	1146.7	1106.0	1073.7	1051.2	1046.9
12.5°	1260.5	1247.9	1218.4	1173.4	1122.8	1072.2	1032.9	1006.2	999.2
15°	1260.5	1247.9	1211.4	1158.0	1094.7	1037.1	993.5	962.6	952.8
17.5°	1249.4	1235.2	1191.7	1129.9	1061.0	996.3	945.8	913.5	903.7
20°	1219.8	1204.3	1155.2	1087.7	1013.3	945.8	895.2	861.4	848.8
22.5°	1177.7	1159.4	1107.3	1034.3	959.9	891.0	841.8	806.7	795.4
25°	1127.1	1108.8	1052.6	980.9	903.7	839.0	789.7	757.4	744.8
27.5°	1065.2	1045.6	990.7	919.1	847.4	782.7	737.8	708.2	695.6
30°	995.0	973.9	921.8	853.1	788.4	726.5	682.9	659.1	645.0
32.5°	913.5	895.2	848.8	786.9	726.5	667.5	631.0	609.9	598.7
35°	825.0	815.0	775.7	722.3	663.3	614.1	581.8	562.1	552.3
37.5°	746.3	736.3	702.7	657.6	605.7	560.7	534.0	517.2	508.7
40°	671.8	663.3	631.0	593.1	548.0	508.7	486.3	473.6	465.1
42.5°	598.7	594.4	567.8	532.7	493.3	459.5	441.2	431.4	424.4
45°	539.7	534.0	508.7	475.0	441.2	413.2	397.7	390.6	383.6
47.5°	487.6	480.6	453.9	424.4	393.5	368.2	354.2	347.1	344.3
50°	437.0	430.0	406.1	376.6	345.7	327.4	316.2	309.1	307.8
52.5°	392.1	385.1	358.3	330.2	306.4	290.9	281.0	274.0	271.2
55°	348.5	340.1	317.6	290.9	271.2	257.2	247.4	240.3	237.5
57.5°	309.1	300.8	281.0	255.7	237.5	224.9	216.4	209.4	206.6
60°	271.2	264.2	245.9	222.1	206.6	195.3	186.8	181.3	178.5
62.5°	236.1	230.4	212.3	191.1	178.5	168.7	161.6	156.0	158.9
65°	203.8	198.1	181.3	163.0	153.2	143.4	137.7	137.7	143.4
67.5°	172.8	167.2	153.2	137.7	129.3	122.3	118.1	122.3	126.4
70°	144.7	139.1	126.4	113.8	106.8	101.2	101.2	105.4	108.2
72.5°	118.1	112.4	102.6	92.8	87.2	82.9	87.2	90.0	92.8
75°	92.8	88.5	80.0	73.0	68.9	67.4	71.7	74.5	75.9
77.5°	68.9	66.0	60.4	54.8	52.0	53.4	57.6	59.0	60.4
80°	47.8	46.4	42.1	39.4	39.4	40.8	43.6	44.9	46.4
82.5°	29.5	29.5	26.6	25.3	26.6	29.5	30.9	32.3	32.3
85°	14.0	15.5	14.0	14.0	15.5	18.3	18.3	19.6	19.6
87.5°	4.2	4.2	5.6	5.6	7.0	7.0	7.0	7.0	8.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)