

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580216

Luminaire Tested: **HCC4W25D010MW-HM40525930-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580216
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MW-HM40525930-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1705.9 lumens
Efficiency: N/A
Efficacy: 63.7 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580216
CATALOG NUMBER: HCC4W25D010MW-HM40525930-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580216

CATALOG NUMBER: HCC4W25D010MW-HM40525930-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	121816	121816	121816
5°	129067	121415	115323
10°	134429	119474	108565
15°	139573	116600	102068
20°	140883	111008	94417
25°	136315	102671	86435
30°	127472	93033	78634
35°	113595	82712	70651
40°	99315	71926	62877
45°	86521	61018	54389
50°	75471	51753	46649
55°	66170	42902	37762
60°	57874	34635	27703
65°	50434	25830	15585
70°	44106	16734	5049
75°	36172	8721	1334
80°	26921	3978	994
85°	15992	1981	1981



TEST NUMBER: P580216

CATALOG NUMBER: HCC4W25D010MW-HM40525930-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.2	5.5
10°-20°	260.9	15.3
20°-30°	360.7	21.1
30°-40°	362.7	21.3
40°-50°	292.7	17.2
50°-60°	197.9	11.6
60°-70°	100.7	5.9
70°-80°	32.2	1.9
80°-90°	4.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.8	41.9
0°-40°	1077.5	63.2
0°-60°	1568.0	91.9
0°-90°	1705.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1705.9	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	988	988	988	988	988	
5°	1042	1023	981	946	931	100
15°	1093	1034	913	826	799	308
25°	1002	915	754	662	635	458
35°	754	681	549	480	469	471
45°	496	444	350	312	312	384
55°	308	266	200	174	176	276
65°	173	140	88	58	53	173
75°	76	53	18	4	3	82
85°	11	6	1	1	1	15
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580216

CATALOG NUMBER: HCC4W25D010MW-HM40525930-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	987.6	987.6	987.6	987.6	987.6	987.6	987.6	987.6	987.6
2.5°	1014.3	1008.8	1003.1	993.3	982.0	970.8	963.7	958.2	955.4
5°	1042.4	1035.4	1022.8	1001.6	980.6	960.9	945.5	935.6	931.4
7.5°	1064.9	1055.1	1034.1	1004.5	972.2	941.2	921.6	907.6	902.0
10°	1073.3	1062.1	1034.1	994.6	953.9	916.0	887.8	873.8	866.8
12.5°	1083.2	1070.5	1035.4	986.2	935.6	890.7	858.4	840.1	833.1
15°	1093.0	1076.2	1034.1	973.5	913.1	861.2	826.1	807.8	799.3
17.5°	1093.0	1073.3	1022.8	952.5	883.7	828.9	789.5	768.5	761.4
20°	1073.3	1050.9	996.1	918.8	845.7	786.7	748.8	727.8	719.3
22.5°	1042.4	1017.1	958.2	878.0	800.8	743.2	705.3	685.5	677.2
25°	1001.6	976.4	914.6	831.7	754.4	696.8	661.7	643.4	635.1
27.5°	953.9	925.8	864.0	781.2	705.3	650.4	618.1	601.3	594.3
30°	895.0	868.2	807.8	726.3	653.2	602.7	573.2	557.7	552.1
32.5°	826.1	803.6	744.6	668.7	599.8	553.5	526.8	514.1	508.6
35°	754.4	733.4	681.4	611.1	549.3	505.8	480.5	472.0	469.2
37.5°	687.0	668.7	618.1	553.5	497.3	459.4	436.9	431.3	428.5
40°	616.8	604.1	557.7	498.7	446.7	413.0	394.8	390.5	390.5
42.5°	553.5	539.4	498.7	445.4	399.0	365.2	352.6	348.4	349.8
45°	496.0	481.9	443.9	394.8	349.8	321.8	311.8	311.8	311.8
47.5°	442.6	429.9	394.8	344.2	307.7	285.2	275.4	275.4	276.7
50°	393.3	385.0	345.6	302.0	269.7	248.7	241.6	240.3	243.1
52.5°	347.1	337.1	302.0	262.7	231.8	215.0	208.0	206.5	208.0
55°	307.7	296.5	265.5	227.6	199.5	182.7	174.2	172.8	175.6
57.5°	269.7	261.4	229.0	195.3	168.6	151.7	144.7	141.9	143.3
60°	234.6	226.1	196.7	164.4	140.4	123.6	113.8	111.0	112.3
62.5°	202.3	195.3	167.2	136.3	112.3	97.0	87.2	80.0	82.9
65°	172.8	165.7	140.4	109.6	88.5	71.7	57.6	51.9	53.4
67.5°	147.6	139.1	115.2	87.2	66.0	47.8	32.3	29.5	29.5
70°	122.3	113.8	92.7	67.4	46.4	25.3	14.0	14.0	14.0
72.5°	98.3	91.3	71.7	50.6	29.5	11.3	5.6	5.6	5.6
75°	75.9	70.2	53.4	35.1	18.3	5.6	4.2	2.8	2.8
77.5°	56.2	50.6	37.9	23.9	11.3	2.8	2.8	2.8	2.8
80°	37.9	33.8	25.3	14.0	5.6	1.4	1.4	1.4	1.4
82.5°	22.5	19.6	14.0	7.0	2.8	1.4	1.4	1.4	1.4
85°	11.3	8.5	5.6	2.8	1.4	1.4	1.4	1.4	1.4
87.5°	2.8	1.4	1.4	1.4	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)