

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580234

Luminaire Tested: **HCC4W25D010BZ-HM40525935-41WWBB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580234
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-17)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010BZ-HM40525935-41WWBB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, WHITE BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1797.0 lumens
Efficiency: N/A
Efficacy: 67.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.04 / 1.12
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580234
CATALOG NUMBER: HCC4W25D010BZ-HM40525935-41WWBB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580234

CATALOG NUMBER: HCC4W25D010BZ-HM40525935-41WWBB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	111	108	104	101	109	105	102	100	101	99	97	97	95	94	94	92	91	89								
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78								
3	96	87	80	75	94	86	79	74	83	78	73	80	76	72	78	74	71	69								
4	89	79	72	66	87	78	71	65	75	69	65	73	68	64	71	67	63	61								
5	83	72	64	58	81	71	64	58	69	62	58	67	61	57	65	60	56	55								
6	77	66	58	52	75	65	57	52	63	57	52	61	56	51	60	55	51	49								
7	72	60	53	47	71	59	52	47	58	51	47	57	51	46	55	50	46	44								
8	68	56	48	43	66	55	48	43	54	47	42	53	47	42	51	46	42	40								
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37								
10	60	48	41	36	59	47	41	36	46	40	36	46	40	36	45	39	36	34								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	128329	128329	128329
5°	135963	127890	121477
10°	141606	125850	114352
15°	147030	122832	107521
20°	148404	116941	99457
25°	143609	108156	91035
30°	134266	98004	82821
35°	119664	87124	74430
40°	104596	75774	66242
45°	91126	64280	57303
50°	79501	54536	49143
55°	69697	45181	39762
60°	60957	36510	29208
65°	53119	27231	16403
70°	46414	17635	5337
75°	38078	9150	1382
80°	28413	4191	1065
85°	16841	2123	2123



TEST NUMBER: P580234
 CATALOG NUMBER: HCC4W25D010BZ-HM40525935-41WWBB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.2	5.5
10°-20°	274.8	15.3
20°-30°	379.9	21.1
30°-40°	382.0	21.3
40°-50°	308.3	17.2
50°-60°	208.5	11.6
60°-70°	106.1	5.9
70°-80°	34.0	1.9
80°-90°	5.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	752.9	41.9
0°-40°	1135.0	63.2
0°-60°	1651.7	91.9
0°-90°	1797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1797.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1040	1040	1040	1040	1040	
5°	1098	1077	1033	996	981	106
15°	1151	1089	962	870	842	324
25°	1055	963	795	697	669	483
35°	795	718	579	506	494	497
45°	522	468	368	328	328	405
55°	324	280	210	184	185	291
65°	182	148	93	61	56	182
75°	80	56	19	4	3	86
85°	12	6	2	2	2	16
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580234

CATALOG NUMBER: HCC4W25D010BZ-HM40525935-41WWBB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1040.4	1040.4	1040.4	1040.4	1040.4	1040.4	1040.4	1040.4	1040.4
2.5°	1068.5	1062.5	1056.6	1046.2	1034.4	1022.5	1015.2	1009.2	1006.3
5°	1098.1	1090.6	1077.3	1055.2	1032.9	1012.3	995.9	985.6	981.1
7.5°	1121.8	1111.4	1089.1	1058.1	1024.0	991.5	970.8	956.0	950.1
10°	1130.6	1118.7	1089.1	1047.7	1004.8	964.8	935.3	920.5	913.0
12.5°	1141.0	1127.6	1090.6	1038.9	985.6	938.2	904.2	884.9	877.6
15°	1151.4	1133.5	1089.1	1025.6	961.9	907.2	870.1	850.9	842.0
17.5°	1151.4	1130.6	1077.3	1003.3	930.9	873.2	831.6	809.5	802.0
20°	1130.6	1107.0	1049.2	967.8	890.9	828.7	788.7	766.6	757.7
22.5°	1098.1	1071.4	1009.2	924.9	843.5	782.8	742.9	722.2	713.3
25°	1055.2	1028.5	963.4	876.1	794.7	734.0	697.0	677.7	668.9
27.5°	1004.8	975.2	910.1	822.8	742.9	685.2	651.1	633.4	626.0
30°	942.7	914.6	850.9	765.1	688.1	634.8	603.8	587.5	581.5
32.5°	870.1	846.5	784.3	704.4	631.9	583.0	554.9	541.6	535.7
35°	794.7	772.5	717.7	643.8	578.6	532.8	506.1	497.2	494.3
37.5°	723.7	704.4	651.1	583.0	523.9	483.9	460.2	454.3	451.4
40°	649.6	636.3	587.5	525.3	470.6	435.1	415.8	411.4	411.4
42.5°	583.0	568.2	525.3	469.1	420.3	384.8	371.4	367.0	368.5
45°	522.4	507.6	467.6	415.8	368.5	338.9	328.5	328.5	328.5
47.5°	466.2	452.8	415.8	362.5	324.1	300.4	290.0	290.0	291.5
50°	414.3	405.4	364.0	318.2	284.2	261.9	254.6	253.0	256.1
52.5°	365.6	355.2	318.2	276.7	244.2	226.4	219.0	217.6	219.0
55°	324.1	312.3	279.7	239.7	210.1	192.4	183.5	182.0	184.9
57.5°	284.2	275.3	241.3	205.7	177.6	159.9	152.4	149.5	150.9
60°	247.1	238.2	207.2	173.2	148.0	130.2	119.9	117.0	118.4
62.5°	213.0	205.7	176.1	143.5	118.4	102.1	91.8	84.3	87.3
65°	182.0	174.7	148.0	115.4	93.3	75.4	60.6	54.8	56.2
67.5°	155.4	146.5	121.4	91.8	69.5	50.4	34.0	31.0	31.0
70°	128.7	119.9	97.7	71.0	48.9	26.6	14.8	14.8	14.8
72.5°	103.6	96.2	75.4	53.3	31.0	11.9	5.9	5.9	5.9
75°	79.9	73.9	56.2	37.0	19.2	5.9	4.4	2.9	2.9
77.5°	59.2	53.3	40.0	25.2	11.9	2.9	2.9	2.9	2.9
80°	40.0	35.6	26.6	14.8	5.9	1.5	1.5	1.5	1.5
82.5°	23.7	20.8	14.8	7.5	2.9	1.5	1.5	1.5	1.5
85°	11.9	8.9	5.9	2.9	1.5	1.5	1.5	1.5	1.5
87.5°	2.9	1.5	1.5	1.5	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)