

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580236

Luminaire Tested: **HCC4W25D010MB-HM40525935-41WWWB**

Issue Date: 9/9/2021

Test Information

Test Method: LM-41-14
Report Number: P580236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-18)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 9/9/2021
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: HCC4W25D010MB-HM40525935-41WWWB
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, BLACK BAFFLE TRIM
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
CYLINDER
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2236.6 lumens
Efficiency: N/A
Efficacy: 83.5 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.07 / 1.15
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 26.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P580236
CATALOG NUMBER: HCC4W25D010MB-HM40525935-41WWWB

Luminous Intensity Polar Plot



Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580236

CATALOG NUMBER: HCC4W25D010MB-HM40525935-41WWWB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87								
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75								
3	94	85	77	72	92	83	76	71	80	75	70	78	73	69	75	71	68	66								
4	87	76	68	62	85	75	68	62	72	66	61	70	65	60	68	63	60	58								
5	81	69	61	55	79	68	60	55	66	59	54	64	58	53	62	57	53	51								
6	75	63	55	49	73	62	54	49	60	53	48	59	53	48	57	52	47	46								
7	70	58	50	44	68	57	49	44	55	48	43	54	48	43	53	47	43	41								
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37								
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34								
10	58	45	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31								

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	142255	142255	142255
5°	149571	142067	136743
10°	154820	140378	130546
15°	159557	137810	124964
20°	159732	132141	117768
25°	153735	123508	110415
30°	142755	113657	103103
35°	127961	102317	95406
40°	112277	91296	88205
45°	98138	80817	81357
50°	86639	70731	73283
55°	76406	62708	65890
60°	68284	55506	57701
65°	60503	48828	48828
70°	52834	41654	41654
75°	45131	35314	39508
80°	35800	31538	35800
85°	23068	27172	33541



TEST NUMBER: P580236
 CATALOG NUMBER: HCC4W25D010MB-HM40525935-41WWWB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.3	4.9
10°-20°	307.7	13.8
20°-30°	431.1	19.3
30°-40°	444.1	19.9
40°-50°	378.1	16.9
50°-60°	280.2	12.5
60°-70°	175.8	7.9
70°-80°	87.4	3.9
80°-90°	22.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	848.1	37.9
0°-40°	1292.2	57.8
0°-60°	1950.5	87.2
0°-90°	2236.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2236.6	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	1153	1153	1153	1153	1153	
5°	1208	1187	1147	1115	1104	116
15°	1250	1193	1079	1001	979	351
25°	1130	1051	908	829	811	517
35°	850	786	680	635	634	530
45°	563	524	463	454	466	437
55°	355	327	292	298	306	321
65°	207	186	167	164	167	207
75°	95	84	74	80	83	101
85°	16	16	19	22	24	21
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab
 1121 Highway 74 South
 Peachtree City, GA 30269



TEST NUMBER: P580236

CATALOG NUMBER: HCC4W25D010MB-HM40525935-41WWWB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1153.3	1153.3	1153.3	1153.3	1153.3	1153.3	1153.3	1153.3	1153.3
2.5°	1178.5	1174.0	1168.1	1157.7	1147.4	1138.5	1129.6	1125.2	1123.7
5°	1208.0	1199.2	1187.4	1168.1	1147.4	1129.6	1114.8	1107.4	1104.4
7.5°	1228.8	1219.9	1200.7	1171.0	1141.4	1114.8	1091.1	1080.8	1077.7
10°	1236.1	1225.9	1199.2	1159.3	1120.8	1088.1	1061.5	1048.2	1042.3
12.5°	1242.1	1228.8	1194.7	1147.4	1100.0	1060.0	1031.9	1014.1	1009.7
15°	1249.5	1234.7	1193.2	1135.5	1079.2	1031.9	1000.7	984.5	978.6
17.5°	1242.1	1225.9	1177.0	1111.8	1048.2	996.3	962.2	947.5	941.6
20°	1216.9	1199.2	1144.4	1074.8	1006.7	953.4	919.3	904.6	897.2
22.5°	1178.5	1159.3	1102.9	1029.0	959.3	907.5	875.0	860.2	855.7
25°	1129.6	1110.4	1051.1	975.7	907.5	857.1	829.0	815.7	811.3
27.5°	1071.9	1052.6	994.9	920.8	855.7	808.4	786.1	772.8	769.9
30°	1002.3	983.0	926.8	858.7	798.0	753.6	735.8	725.4	723.9
32.5°	925.3	909.0	857.1	795.0	737.2	700.2	686.9	679.5	678.1
35°	849.8	832.1	786.1	729.9	679.5	646.9	635.1	633.6	633.6
37.5°	772.8	755.1	718.0	666.2	623.3	593.6	589.2	590.7	590.7
40°	697.3	681.0	648.5	605.5	567.0	544.9	543.3	546.3	547.8
42.5°	626.3	612.9	583.4	546.3	513.7	496.0	497.4	503.3	507.8
45°	562.6	550.7	524.1	491.6	463.3	450.0	454.5	461.9	466.4
47.5°	504.9	494.5	469.3	439.7	416.0	407.1	413.1	421.9	427.9
50°	451.5	442.7	419.0	387.9	368.6	362.7	370.1	379.0	381.9
52.5°	404.2	395.3	370.1	343.4	328.7	325.7	333.1	340.5	344.9
55°	355.3	348.0	327.2	303.5	291.6	290.2	297.6	303.5	306.4
57.5°	315.3	308.0	288.7	267.9	257.6	256.2	263.5	267.9	269.5
60°	276.8	269.5	251.7	232.5	225.0	225.0	229.5	232.5	233.9
62.5°	241.3	233.9	217.7	201.3	195.4	195.4	195.4	196.9	201.3
65°	207.3	201.3	186.5	171.7	167.3	164.4	164.4	164.4	167.3
67.5°	176.1	170.3	158.4	145.1	140.7	136.2	134.7	137.7	137.7
70°	146.5	142.1	130.3	119.9	115.5	111.0	109.5	115.5	115.5
72.5°	119.9	115.5	108.0	97.7	93.3	91.8	94.7	97.7	99.2
75°	94.7	90.3	84.3	78.5	74.1	75.5	79.9	81.4	82.9
77.5°	71.0	69.5	63.7	59.3	59.3	60.7	63.7	66.6	68.1
80°	50.4	48.9	46.0	42.9	44.4	47.4	48.9	51.8	50.4
82.5°	31.0	31.0	29.6	29.6	31.0	34.1	35.6	37.0	38.5
85°	16.3	16.3	16.3	17.7	19.2	20.8	22.2	23.7	23.7
87.5°	4.4	5.9	5.9	7.5	8.9	8.9	10.4	10.4	10.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180° - - 45°-225° - - - - 90°-270°

Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Classified
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)