

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P580232

Luminaire Tested: **HCC4W25D010MW-HM40525935-41RWWC**

Issue Date: 9/9/2021

**Test Information**

Test Method: LM-41-14  
Report Number: P580232  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2106-266-14)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 9/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: HCC4W25D010MW-HM40525935-41RWWC  
Description: HALO COMMERCIAL 4" ROUND, NEW CONSTRUCTION FRAME, WITH 4" WALLWASH DISTRIBUTION, SPECULAR TRIM  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
CYLINDER  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2282.5 lumens  
Efficiency: N/A  
Efficacy: 85.2 lumens/watt  
Spacing Criteria (0/90/45): 1.21 / 1.15 / 1.21  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 26.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P580232  
CATALOG NUMBER: HCC4W25D010MW-HM40525935-41RWWC

### Luminous Intensity Polar Plot





TEST NUMBER: P580232

CATALOG NUMBER: HCC4W25D010MW-HM40525935-41RWWC

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88	88	88	88
2	102	95	90	85	100	94	88	84	90	86	82	87	83	80	84	81	78	76	76	76	76
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67	67	67	67
4	87	77	69	63	85	76	68	63	73	67	62	71	66	61	69	64	60	58	58	58	58
5	81	70	61	56	79	68	61	55	66	60	55	65	59	54	63	58	54	52	52	52	52
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46	46	46	46
7	70	58	50	44	69	57	49	44	56	49	44	54	48	44	53	47	43	41	41	41	41
8	66	53	45	40	64	53	45	40	51	44	40	50	44	39	49	43	39	37	37	37	37
9	62	49	42	36	60	49	41	36	47	41	36	46	40	36	45	40	36	34	34	34	34
10	58	46	38	33	57	45	38	33	44	38	33	43	37	33	42	37	33	31	31	31	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°
0°	135113	135113	135113
5°	140569	136347	134886
10°	145150	137560	134592
15°	150274	137989	134580
20°	150767	134648	132902
25°	145447	127917	128925
30°	135349	119112	122487
35°	121907	108988	112993
40°	107494	99154	103678
45°	93987	89329	93725
50°	83204	80383	84643
55°	73202	70987	73847
60°	65373	60612	62438
65°	57467	49266	48361
70°	50165	36316	33107
75°	41652	21827	17633
80°	31538	8453	5327
85°	14718	2123	2123



TEST NUMBER: P580232

CATALOG NUMBER: HCC4W25D010MW-HM40525935-41RWWC

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.6	4.6
10°-20°	308.3	13.5
20°-30°	446.5	19.6
30°-40°	471.1	20.6
40°-50°	407.7	17.9
50°-60°	302.0	13.2
60°-70°	174.1	7.6
70°-80°	60.8	2.7
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	860.5	37.7
0°-40°	1331.5	58.3
0°-60°	2041.2	89.4
0°-90°	2282.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2282.5	100.0

**CANDELA DISTRIBUTION:**

	0°	45°	90°	135°	180°	Flux
0°	1095	1095	1095	1095	1095	
5°	1135	1120	1101	1092	1089	109
15°	1177	1138	1081	1055	1054	331
25°	1069	1015	940	934	947	489
35°	810	773	724	740	750	506
45°	539	524	512	531	537	418
55°	340	333	330	342	343	307
65°	197	185	169	160	166	197
75°	87	74	46	37	37	94
85°	10	6	2	2	2	16
90°	0	0	0	0	0	

Cooper Lighting Solutions Photometric Lab  
 1121 Highway 74 South  
 Peachtree City, GA 30269



TEST NUMBER: P580232

CATALOG NUMBER: HCC4W25D010MW-HM40525935-41RWWC

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°	112.5°	135°	157.5°	180°
0°	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4	1095.4
2.5°	1111.6	1108.7	1104.2	1098.3	1092.3	1087.9	1086.4	1085.0	1085.0
5°	1135.3	1129.3	1120.5	1108.7	1101.2	1096.8	1092.3	1089.4	1089.4
7.5°	1151.6	1145.6	1132.3	1116.0	1105.6	1096.8	1090.8	1086.4	1086.4
10°	1158.9	1151.6	1135.3	1114.5	1098.3	1086.4	1077.5	1074.6	1074.6
12.5°	1167.8	1158.9	1136.8	1110.1	1089.4	1074.6	1065.8	1062.7	1062.7
15°	1176.8	1166.4	1138.3	1107.2	1080.6	1062.7	1055.4	1053.9	1053.9
17.5°	1172.2	1158.9	1126.4	1089.4	1059.8	1042.1	1034.6	1034.6	1036.1
20°	1148.6	1135.3	1098.3	1056.9	1025.8	1012.5	1006.5	1009.4	1012.5
22.5°	1113.1	1096.8	1056.9	1016.9	984.3	972.5	972.5	976.9	981.3
25°	1068.7	1053.9	1015.4	970.9	939.9	931.0	934.0	941.4	947.3
27.5°	1018.4	1002.1	962.1	920.7	889.5	885.1	892.6	902.9	905.9
30°	950.3	937.0	902.9	862.9	836.3	834.8	845.2	852.6	860.0
32.5°	885.1	870.3	837.8	799.3	780.0	781.5	793.3	802.3	806.7
35°	809.6	796.3	772.7	741.5	723.8	726.7	740.1	749.0	750.4
37.5°	738.6	729.7	706.1	682.4	669.0	674.9	686.8	697.2	697.2
40°	667.6	660.1	642.4	623.1	615.8	623.1	634.9	643.9	643.9
42.5°	599.5	595.0	580.2	566.9	562.5	572.9	583.2	590.6	589.1
45°	538.8	534.4	524.0	513.6	512.1	522.5	531.4	535.8	537.3
47.5°	484.0	481.1	472.1	464.8	464.8	475.1	482.5	486.9	488.4
50°	433.6	430.7	423.4	417.4	418.9	429.2	435.1	439.6	441.1
52.5°	383.4	381.8	376.0	368.5	373.0	380.4	387.8	390.7	392.2
55°	340.4	340.4	333.1	327.1	330.1	337.5	342.0	343.4	343.4
57.5°	302.0	300.4	291.6	285.6	287.1	294.6	297.5	299.0	299.0
60°	265.0	263.5	254.6	245.7	245.7	250.2	251.7	253.1	253.1
62.5°	229.4	227.9	217.6	210.2	207.2	205.7	205.7	208.8	214.6
65°	196.9	195.4	185.0	173.2	168.8	164.3	159.9	162.8	165.7
67.5°	167.2	164.3	153.9	143.6	133.2	125.8	118.4	122.8	128.8
70°	139.1	136.2	124.3	112.4	100.7	88.9	82.9	88.9	91.8
72.5°	112.4	109.5	97.7	85.8	71.0	59.2	57.7	59.2	60.7
75°	87.4	85.8	74.1	60.7	45.8	37.0	37.0	37.0	37.0
77.5°	65.1	62.2	50.4	38.5	26.6	20.8	19.2	19.2	19.2
80°	44.4	41.4	31.0	22.2	11.9	8.9	8.9	7.5	7.5
82.5°	25.2	23.7	16.3	8.9	4.4	2.9	2.9	2.9	2.9
85°	10.4	8.9	5.9	2.9	1.5	1.5	1.5	1.5	1.5
87.5°	1.5	1.5	1.5	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°    - - 45°-225°    - - - - 90°-270°

Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Classified  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)